

Rittal – The System.

Faster – better – everywhere.

PDU metered – DK 7979.204

Date : Dec 17, 2020

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PDU metered – DK 7979.204

created: 17.12.2020 on www.rittal.com/com-en



Product description

Design: 482.6 mm (19") version

Description: High-end power distribution in a compact design for IT network and server racks. With power measurement at the infeed or per phase.

Benefits:

- For vertical mounting, it may be attached in the zero-U space of the Rittal VX IT or TS IT rack with no need for tools
- Colour coding of phases and fuse circuits (L1=pink, L2=black, L3=white)
- Tool-free divider kit for VX IT
- PDU self-supplied, no external power supply required
- Measurement accuracy $\pm 1\%$ (kWh) to IEC 50430-1
- Integral real-time clock with battery buffering (max. 10 years, battery replaceable)
- Integral electromagnetic buzzer for acoustic alarms
- Adjustable limit values (warning/alarm) for voltage, current, output
- Operating hours meter, total and cyclical, resettable
- Power-saving design, minimal intrinsic power consumption

Technical specifications:

- Display/controller unit in the PDU enclosure rotatable through 180° and replaceable
- Compact circuit-breaker (16 A - Carling type)
- Integral, fully-redundant power pack, power supply from all phases
- Error-tolerant PDU power supply redundant across all phases
- Voltage V, current A, frequency Hz
- Active power, active energy, apparent power, apparent energy
- Power factor (cosPhi) and phase angle
- Zero conductor current measurement/load imbalance detection
- Fuse monitoring for PDUs with integral fuse
- Bright TFT display, 128 x 128 pixels (RGB) with back-lighting and energy-saving mode to display output data and basic PDU configuration
- Position sensors for display rotation and correct PDU representation on the website
- Power LED to indicate voltage

Measurement functions:

- Measurement per phase or infeed
- Powerful CPU (ARM Cortex A8)
- Digital input (floating contact)
- Additional alarm output/relay output (changeover contact)

| | |
|--|---|
| Material: | Aluminium section, black anodised Slots: Plastic |
| Protection category IP to IEC 60 529: | IP 20 |
| Standards: | EN 62368-1 EN 61000-3 EN 61000-4 EN 61000-6 EN 62053-21 |
| Directives: | EMC Directive 2014/30/EU Low Voltage Directive 2014/35/EU |
| Supply includes: | Assembly parts |
| Options: | Type 3 overvoltage protection with interchangeable arresters while operational, with status monitoring, suitable for integration into PDU enclosure Residual current measurement (type B) per infeed/phase/fuse Monitoring of the optionally available overvoltage protection CMC III CAN bus sensors may be connected for ambient monitoring, max. 8 sensors Other enclosure colours are available |
| Product features | |
| Variant: | Measurement per phase |
| Sockets: | 4 x C 13 2 x C 19 |
| To fit: | Enclosure type: VX IT enclosure frame Enclosure type: VX IT 19" mounting angles Height: ≥ 800 mm Height: ≥ 800 mm |
| Dimensions: | Height: 44 mm Depth: 144 mm Length: 450 mm |
| Rated operating voltage: | 230 V (AC) |
| Infeeds: | Qty.: 1 Phases per infeed: 1~ |
| Length of connection cable: | 3 m |
| Ambient conditions: | Operating temperature: +5 °C...+50 °C Storage temperature: -20 °C...+70 °C Ambient humidity (non-condensing): 10 % - 95 % |
| Circuit-breaker 16 A (qty.): | 2 |

| | |
|---------------------------------------|---|
| Type of electrical connection: | CEE |
| Rated current (max.): | 32 A |
| Output: | 7.4 kW |
| Interfaces: | USB 2.0 port (USB-A) for mass configuration, firmware updates & data logging CAN bus interface (RJ 45) for a maximum of 8 ambient sensors Serial interface RS232 (RJ12) for LTE unit, scripting, CLI Use of own certificates/TLS 1.2 E-mail forwarding in case of alarm (SMTP) User administration including rights management LDAP(S)/Radius/Active Directory connection Syslog server connection (max. 2 servers) Fully redundant monitoring via 2nd network Network protocol: Web server (HTTP, HTTPS, SSL) SSH, Telnet, NTP Network protocol: TCP/IP v4 & v6, DHCP, DNS Network protocol: SNMP v1, v2c & v3, Modbus/TCP, OPC-UA Network protocol: MIB for linking into 3rd party DCIM software Network protocol: FTP/SFTP (update/file transfer) |
| Packs of: | 1 pc(s). |
| Copper weight (kg per piece): | 0 |
| EAN: | 4028177947627 |
| Customs tariff number: | 85369095 |
| ETIM 7.0: | EC000330 |
| ETIM 6.0: | EC000330 |
| eCl@ss 8.0/8.1: | 27142604 |
| eCl@ss 6.0/6.1: | 27142604 |
| Product description: | PDU metered 32A/1P CEE 4xC13+2xC19, DK PDU metered, Compact basic power distributor incl. energy measurement per phase, with network interface and display, WHD: 44x450x70 mm |
| Approvals | |
| Declarations: | Declaration of conformity |