

Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

High-Speed Armored HDMI Fiber Active Optical Cable (AOC) with Hooded Connectors - 4K @ 60 Hz, HDR, IP68, M/M, Black, 30 m

MODEL NUMBER: P568FA-30M-W











Fiber HDMI cable with durable TPU jacket carries 4K video/audio in industrial environments where protection against dust and moisture is needed.

Features

4K HDMI Cable Connects Industrial and Outdoor Security and Digital Signage Components

This high-speed HDMI cable securely connects HDMI-enabled laptops, tablets, Blu-ray players, game consoles, media servers or security cameras to 4K-ready HDTVs, HD monitors, projectors or home theater receivers. Because the cable uses optical fiber, it can transmit HDMI signals longer distances with no latency or loss. It also eliminates any EMI/RFI line noise that can interfere with your audio/video signal and disrupt the performance of your connected equipment.

Transmits Crystal-Clear 4K Video with HDR and 4:4:4 Color

The P568FA-30M-W is rated up to 18 Gbps and supports Ultra HD resolutions up to 3840×2160 (4K x 2K) at 60 Hz, as specified in HDMI 2.0, with Dolby 5.1-channel surround sound. High Dynamic Range (HDR) provides a wide range of vibrant colors with richer contrast, brighter whites and deeper blacks that pop on your 4K display. HDCP 2.2 compliance allows you to stream 4K Amazon and Netflix content with no complications. The cable also supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor, as well as other current HDMI standards, including 3D, 48-bit Deep Color and Dolby 5.1-channel surround sound.

IP68-Rated Ends Resist Dust and Water

Both HDMI connectors are protected by a molded, dust-resistant, IP68-rated watertight hood and caps. The IP68 rating means the connectors can endure immersion in 1.5 meters of water for up to 60 minutes with no damage or decline in performance. The P568FA-30M-W is ideal for industrial areas, such as factories and warehouses, and unforgiving outdoor installations, including malls, bus stops and stadiums, where dust, debris and water are present.

Armored Cable Jacket Ideal for Areas Where Extra Protection Is Needed

The outer thermoplastic polyurethane (TPU) jacket offers UV protection for applications in which the cable is installed outdoors. The crush-resistant stainless steel armored tube protects the cabling against excessive force. The DuPont Kevlar resists heat and provides tensile strength to the cable when it is being bent or pulled. This type of cable construction provides ideal protection in outdoor applications where the cable is exposed to crushing, cuts and abrasion.

Advanced Fiber Cable Is Easier to Install than Copper

Highlights

- Supports 4K @ 60 Hz video resolutions (4:4:4) as specified in HDMI 2.0
- Carries High Dynamic Range (HDR) signals for rich contrast and expanded color accuracy
- Fiber optic strands transmit audio/video over longer distances than standard copper
- IP68-rated ends resist dust and endure immersion in 1.5 m of water up to 60 min.
- Armored cable with TPU jacket for outdoor use resists crushing, cutting and abrasions

Applications

- Connect digital signage in factories, warehouses, recycling plants, machine shops and other industrial environments
- Provide 4K video connectivity in outdoor environments susceptible to rain, such as malls, bus stops and theater marguees
- Build high-speed A/V and Ethernet infrastructure in basements, factories, warehouses and other indoor areas prone to flooding
- Watch 4K video content from a Blu-ray player, game console, laptop or tablet on an Ultra HD television, monitor or projector
- Connect a security camera or other A/V surveillance equipment to a central 4K display

Package Includes

P568FA-30M-W High-Speed Armored HDMI Fiber Active Optical Cable, M/M, Black, 30 m (98 ft.)



Because the fiber cable is slimmer and more flexible than standard copper HDMI cables, the P568FA-30M-W is easier to install around corners and in hard-to-reach spaces behind equipment. It draws power from the connected device, so no external power supply is needed to transmit the HDMI signal across the longer distances unique to fiber optic cabling. **Note**: the cable must be installed in the correct direction to function properly, so please check the Source and Display labels on the connectors before installation.

Specifications

OVERVIEW		
UPC Code	037332260994	
Product Type	Active Optical Cable (AOC)	
Technology	HDMI	
VIDEO		
Video Input	HDMI (MALE)	
Video Output	HDMI (MALE)	
Max Supported Video Resolution	3840x2160 (4K @ 60Hz)	
Max 1280 x 720 (720p) Range (ft)	98	
Max 1920 x 1080 (1080p) Range (ft)	98	
Max 1920 x 1200 Range (ft)	98	
Max 2560 x 1600 Range (ft)	98	
Max 3840 x 2160 (4K@30Hz) Range (ft)	98	
Max 3840 x 2160 (4K@60Hz) Range (ft)	98	
Signal Range (ft)	98	
Signal Range (m)	30	
Max Supported Color Depth	48-bit	
HDR Support	Yes	
3D Video Supported	Yes	
Chroma Sub Sampling	4:4:4	
Maximum Signal Range (ft)	100	
Maximum Signal Range (m)	30	
INPUT		
Bus Powered	No	
POWER		
Power Over Cable (PoC) Support	No	





PHYSICAL		
Color	Black	
Material of Construction	TPU	
Cable Jacket Material	TPU	
Cable Jacket Rating	Armored	
Cable Outer Diameter (OD)	5.8mm	
Cable Length (ft.)	98	
Cable Length (m)	29.88	
Number of Displays	1	
Form Factor/Mounting Options	Cable	
ENVIRONMENTAL		
Operating Temperature Range	32 to 122°F (0 to 50°C)	
Storage Temperature Range	-40 to 158 °F (-40 to 70 °C)	
Operating Humidity Range	10% to 80% RH, Non-Condensing	
Storage Humidity Range	10% to 80% RH, Non-Condensing	
COMMUNICATIONS		
EDID Compatible	No	
IR Remote Extension Support	No	
RS-232 Serial Extension Support	No	
Consumer Electronics Control (CEC) Supported	No	
CONNECTIONS		
Side A - Connector 1	HDMI (MALE)	
Side B - Connector 1	HDMI (MALE)	
Contact Plating	Gold	
FEATURES & SPECIFICATIONS		
Driver Required	No	
EMI/RFI Line Noise Protection	Yes	
10/100 Ethernet Extension Support	No	
IP68 Rated	Yes	
Ingress Protection (IP) Rating	IP68	
Armored Cable	Yes	



Tripp Lite1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234

STANDARDS & COMPLIANCE		
Certifications	CE, FCC, RoHS, REACH	
Protection Rating	IP68	
WARRANTY		
Product Warranty Period (Worldwide)	3-year limited warranty	

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies