

Reboot Your Device Over IP









110V / 208V / 230V







Remote Reboot to Recover Your Device

- > When a complete restart is required MiniBoot provides a simple and easy way to reboot a hardware device.
- > In addition to manual on/off, MiniBoot provides 3 kinds of auto outlet control,:
 - IP-Ping automatically detects a failed system for timely reboot
 - Outlet on/off by sensor condition
 - Outlet on/off scheduling





Diversified Outlets & Inlets

- > Variety of outlets & inlets available for different regional power requirements
- > Outlet: US NEMA, IEC C13, UK BS1363, German Schuko CEE 7/3 or French CEE 7/5
- > Inlet: C20 for different regional power cords (Custom inlet available on request.)



Enterprise Level IP Authentication

- > Active Directory (AD), Lightweight Directory Access Protocol (LDAPv3 / LDAPS).
- > Remote Access Dial-In User Service (RADIUS) protocol, or local credential database.
- > Strong passwords and granular user/user group permissions.
- > Support high-speed network IP via 1000Base-T (Gigabit) Ethernet port



Save Manpower & Travel Costs

- > Restart the problem device by remotely power on & off, MiniBoot allow user to recover the equipment via network IP.
- > Reduce manpower and travel costs by negating the need for staff to actually be at the equipment location, improving uptime and productivity.



Power Monitoring via Network & Local Meter

- > Allows remote monitoring via the free Graphic User Interface (GUI).
- > Provides local current monitoring via MiniBoot blue LED ammeter.
- > Allows user to establish the remaining capacity prior to adding a new device to the MiniBoot, plus displays the current being drawn and receives threshold alerts remotely.



Remote Management

- > Simultaneous access via free management web GUI.
- > SNMP V2 / V3 integration to DCIM.
- > Remote management protocols: HTTP(S); SSH Command Line Interface; Telnet; SMTP; IPv6/IPv4.



Alerts / Alarms

- > Receive alerts via SNMP, email (SMTP), and syslog when predefined thresholds are exceeded for both MiniBoot and environmental sensor events.
- > Common SNMP MIBs (Management Information Base) for all MiniBoot models.



Sensors & WiFi

- > Variety of optional sensors : Temperature & Humidity, Temperature, Smoke, Door.
- > Option to connect via a WiFi kit (IPD-WIFI) complying with 802.11 g/n/ac.



Remote power reboot and monitoring functions are essential for hardware systems. MiniBoot offers a cost-efficient power solution for any environment with electronic devices or systems. Users can try to recover the crashed device by remote reboot, reducing the need to send engineers to site (less personnel and travel costs by negating the need for staff to be at the equipment location) therefore improving uptime and productivity.


Unlike a rack power strip which is mounted inside an IT server rack enclosure, MiniBoot can be applied in diversified applications. MiniBoot is designed for a variety of industries - Transportation (Air, Land and Sea), Broadcasting, Entertainment, Advertising, Manufacturing, Mining, Satellite, Defense, Education, Telecommunication, Finance & Banking, Commercial, etc.




- Universities
- Education Institutes
- Lecture Theatres
- Tutorial Classes
- Training Rooms











- 1 RMS current meter x 1
- 2 Sensor port x 2
- 3 Serial port x 1
- 4 1000Base-T (Gigabit) IP port x 1
- 5 USB Wifi port x 1
- 6 Switched outlets (US NEMA, C13, UK, Schuko or French)
- 7 C20 Inlet x 1
- 8 Resettable fuse x 1

MiniBoot - Single Feed / Single LAN				Amp	
Outlet	Inlet	Model	110V	208V	230V
NEMA x 2		MiniBoot-2US			
NEMA x 4	C20 x 1	MiniBoot-4US	15A		
NEMA x 8		MiniBoot-8US			
C13 x 2		MiniBoot-2C13			
C13 x 4	C20 x 1	MiniBoot-4C13		16A	10A/13A/16A
C13 x 8		MiniBoot-8C13			
UK x 4	C20 x 1	MiniBoot-4UK			10A/13A/16A
Schuko x 4	C20 x 1	MiniBoot-4SCH			10A / 16A
French x 4	C20 x 1	MiniBoot-4FR			10A / 16A



C€ F©







Hardware Specifications

Electrical				
Nominal input voltage	110V / 208V / 230V			
Acceptable input voltage	±10% nominal			
Input frequency	50 / 60Hz			
Inlet	C20			
Outlet	US NEMA, C13, UK BS1363, Schuko or French			
Local meter	3-digit RMS current meter			
Overload protection	Resettable fuse			
Electrical endurance	1 x 10 ⁵ operations			

Chassis		
Color White		
Material	Steel	

Environmental				
Operating temperature	-5 to 60°C degree (23 to 140°F)			
Storage temperature	-25 to 65°C degree (13 to 149°F)			
Operating humidity	0~95%, non-condensing			
Storage humidity	0~95%, non-condensing			

Physical (NEMA or C13)	2 x outlet	4 x outlet	8 x outlet		
Product (WxDxH)	180 x 140 >	44.45 mm	325 x 140 x 44.45 mm		
Packing (WxDxH)	300 x 196	x 81 mm	525 x 230 x 80 mm		
Net weight	0.9 kg	/ 2.0 lb	1.6 kg / 3.5 lb		
Gross weight	1.2 kg / 2.7 lb		2.54 kg / 5.6 lb		


Physical (UK, SCH or FR)	4 x outlet
Product (WxDxH)	220 x 150 x 55 mm
Packing (WxDxH)	300 x 196 x 81 mm
Net weight	1.23 kg / 2.7 lb
Gross weight	1.53 kg / 3.4 lb

Compliance				
EMC	FCC, CE/EMC certified			
Safety	UL 62368-1:2014, CE/LVD certified			
Environment	RoHS3, Reach & WEEE			
ISO	9001 / 14001			

^{*} Custom configuration available on request

^{**} Input cordset excluded









- 1 RMS current meter x 2
- 2 Sensor port x 2
- 3 Serial port x 1



- 1000Base-T (Gigabit) IP port x 2
- 5 USB Wifi port x 1
- 6 Switched outlets (US NEMA, C13)
- 7 C20 Inlet x 2
- 8 Resettable fuse x 2

8	7				6			
PDU A		"	L	 L		L	 L	F





























Mini Bott





MiniBoot - Dual Feed / Dual LAN				Amp	
Outlet	Inlet	Model	110V	208V	230V
NEMA x 8	C20 x 2	MiniBoot-D8US	15A		
C13 x 8	C20 x 2	MiniBoot-D8C13		16A	10A/13A/16A









- * Custom configuration available on request
- ** Input cordsets excluded











Hardware Specifications

Electrical			
Nominal input voltage	110V / 208V / 230V		
Acceptable input voltage	±10% nominal		
Input frequency	50 / 60Hz		
Inlet	C20 x 2		
Outlet	US NEMA, C13		
Local meter	3-digit RMS current meter x 2		
Overload protection	Resettable fuse x 2		
Electrical endurance	1 x 10 5 operations		

Physical (NEMA or C13)	8 x outlet			
Product (WxDxH)	437.5 x 140 x 44.45 mm			
Packing (WxDxH)	525 x 230 x 80 mm			
Net weight	1.8 kg / 4.0 lb			
Gross weight	2.8 kg / 6.2 lb			

Chassis	
Color	White
Material	Steel

Environmental		
Operating temperature	-5 to 60°C degree (23 to 140°F)	
Storage temperature	-25 to 65°C degree (13 to 149°F)	
Operating humidity	0~95%, non-condensing	
Storage humidity	0~95%, non-condensing	

Compliance	
EMC	FCC, CE/EMC certified
Safety	UL 62368-1:2014, CE/LVD certified
Environment	RoHS3, Reach & WEEE
ISO	9001 / 14001





Built-in MiniBoot GUI


User-friendly GUI is included with MiniBoot. The Administrator can remotely manage the MiniBoot via the web browser.

It provides individual outlet switching On/Off, current monitoring and alarm alert functions. With enterprise level IP authentication, the administrator can manage the MiniBoot remotely with high security.


Circuit Monitoring & Outlet Switching



Outlet Control



System Audit Trail



3rd Party DCIM via SNMP V2 / V3

MiniBoot supports SNMP V2 / V3 integration for clients requiring remote management of the MiniBoot using their existing DCIM (Data Center Infrastructure Management) in order to centralize the management for monitoring power, cooling and environmental factors across facilities and IT systems.

MiniBoot Software

FREE MiniBoot Web Power Reboot GUI	
Functions	Manual outlet on / off by GUI / SNMP Automatic outlet on / off by scheduling , IP Ping and sensor condition
	Aggregate current (Amp) monitoring Alarm alert
Enterprise Level IP Authentication	Active Directory (AD), Lightweight Directory Access Protocol (LDAPv3 / LDAPS) Remote Access Dial-In User Service (RADIUS) protocol, or local credential database
Remote Management	Protocols: HTTP(S); SSH Command Line Interface; Telnet; SMTP; IPv6/IPv4
Alarms / Alerts	Receive alerts via SNMP, email (SMTP), and syslog when predefi ned thresholds are exceeded for both MiniBoot and environmental sensor events
	Common SNMP MIBs (Management Information Base) for all MiniBoot models
SNMP	SNMPv1/v2 & SNMPv3 for integration to DCIM



Free Mounting Kit

Universal Open Frame Kit

- · Included with all MiniBoot models
- Enables easy installation into existing kiosks, walls, work panels and furniture



Rack Mount Kit

- Included with 8-port MiniBoot models
- 19" horizontal rack mount version



Sensors & Peripherals

WiFi Kit

- 802.11 g/n/ac WiFi
- · Low-profile design wireless athena
- Magnetic base design for tool-less installation
- 1M cord with USB port



Temperature & Humidity Sensor Temperature Sensor

- · Plug & play
- External sensor with 2M or 4M cord
- Low profile design with magnetic base for easily affix to the rack



Smoke Sensor

- Smoke Sensor with 1M or 3M cord
- When smoke alarm triggers the red LED light is visible on the sensor with continuous audio alert



Door Sensor

- Mechanical door sensor with 2M or 4M cord
- · Cost efficient integration into rack



Lockable IEC



Lockable C13 Outlet

- Lockable C13 outlet MiniBoot models are available to secure plugs and prevent accidental disconnection
- Supports standard or switched outlets
- Compatible with lockable C13 power cords for outlet locking features



Lockable Color C14-C13 Cord

- Connect to lockable C13 outlets to secure plugs and prevent accidental disconnection
- Selection:
 Black / Grey / Red / Blue / Orange / Green
 C14 C13: 0.5M / 1M / 2M











Founded in 1995, Austin Hughes is a design and manufacturing group that offers a broad range of solutions based around 19 inch rack mount technology: the UltraRack IT server rack series, InfraRack intelligent rack solutions, InfraPower intelligent remote management power solutions, InfraCool intelligent remote cooling systems, InfraGuard environmental sensors and peripherals, InfraSolution remote locking and access control, CyberView LCD KVM switches, UltraView professional displays and MiniBoot web reboot power.

Austin Hughes has ISO14001 and ISO9001 approved design, manufacturing, assembly and test facilities. We support a worldwide customer base through our global locations in the Americas, EMEA, APAC and ASEAN and through an extensive authorized channel partner network.





AUSTIN HUGHES

Americas

Austin Hughes Solutions Inc. 32900 Alvarado-Niles Rd, Suite 150 Union City, CA 94587 **United States**

inquiry@austin-hughes.com

EMEA

Austin Hughes Europe Ltd. Unit 1, Chancery Gate Business Centre Manor House Avenue Southampton, SO15 0AE **United Kingdom**

sales@austin-hughes.co.uk

APAC

Austin Hughes Electronics Ltd. Unit 3608-12, Cable TV Tower 9 Hoi Shing Road, Tsuen Wan Hong Kong

inquiry@austin-hughes.com

Distributed by:

ASEAN

Austin Hughes Pte. Ltd. 3 Ang Mo Kio Street 62 #07-03 Link@AMK Singapore 569139

inquiry@austin-hughes.com

Austin Hughes has an extensive distribution network, including the Americas, EMEA, APAC & ASEAN Contact your nearest sales office for details of local representation

Please ask for details of other products from Austin Hughes. Every effort has been made to ensure that the information contained herein is correct. There is a possibility that the image(s) shown may not be exactly the same as the final product. The company reserves the right to modify product specifications without prior notice and assumes no responsibility for any error which may appear in this publication.

Distributor by country on application

All brand names, logo and registered trademarks are properties of their respective owners. Copyright 2021 Austin Hughes Electronics Ltd. All rights reserved.

CA-MiniBoot-Q121V2