FL-PS6(C) & FL-PS10(C)

6 Amp and 10 Amp, 24 Volt Remote Power Supplies



Power Supplies/Accessories

General

The PS Series is a remote power supply line from Fire*Lite Alarms and is a direct replacement for the FCPS-24FS6/8 Series. The FL-PS6(C) is a 6 amp and the FL-PS10(C) is a 10 amp, remote power supply with battery charger that may be connected to any 12 or 24 volt fire alarm control panel (FACP) or used as a standalone power supply. The PS Series provides 24 VDC power for NACs (notification appliance circuits) configured as either Class B or Class A (requires the ZNAC-PS option card) with multiple sync protocol options. The PS Series also provides auxiliary power, constant or resettable, suited for detectors, annunciators, door holders, and other fire alarm system peripherals. The PS Series cabinet can hold two 7 AH or 18 AH batteries and can charge up to 33 AH batteries in a separate cabinet.

Features

- Up to five (6 amp model) or seven (10 amp model) independently-configurable, power-limited output circuits for:
 - Class B and/or Class A NACs
 - Class B and/or Class A resettable or non-resettable 24V auxiliary power
 - door holder power
- Converts from Class B to Class A wiring without losing any outputs using the ZNAC-PS converter card (sold separately)
- Optimal for powering four-wire smoke detectors, annunciators, and other system peripherals requiring regulated power
- · Configurable for ANSI® Temporal 3 or Temporal 4 coded output
- UL-Listed NAC synchronization using System Sensor®, Wheelock®, Gentex®, or AMSECO® appliances
- Synchronization can be triggered from FACP NAC/remote sync outputs, cascaded power supply, or a control module, single or multi, which may be housed within the power supply cabinet
- Ability to cascade up to four power supplies
- Two (6 amp model) or three (10 amp model) fully-isolated input/ control circuits which can be programmed to any output
- Two Form C normally-closed trouble relays for AC Trouble and General Trouble, Ground Fault relay available on Canadian models only
- 6 or 10 amp full load output, respectively, with 3 A maximum/circuit
- · Individual NAC power and trouble LEDs for diagnostic efficiency
- · Trouble history modes for diagnostic support
- Wide range end-of-line supervision value (normal: 2K-27K ohms)
- · Selectable earth fault detection (enable or disable)
- · AC trouble report delay timer
- Completely configurable via onboard DIP switches, no extra software required
- Self-contained in compact, locking cabinet constructed of heavy gauge steel with a corrosion-resistant powder coat chip and scratch-resistant finish
- Cabinet designed with ten double knockouts and a removable door for ease of installation and wiring
- Includes integral battery charger capable of charging up to 33 AH batteries
- Cabinet can house two 7 AH or 18 AH batteries



- Battery charger may be disabled via DIP switch for applications requiring larger batteries and external battery charger
- Removable terminal blocks accommodate up to 12 AWG (3.1mm²) wire
- Works with any UL 864 FACP which utilizes an industry-standard reverse-polarity notification circuit
- Optional devices include addressable control, monitor, and relay modules and power-supervision relay (EOLR-1)

Standards and Codes

The FL-PS Series comply with the following standards:

- NFPA 72 National Fire Alarm Code
- UL 864 Standard for Control Units for Fire Alarm Systems (NAC expander mode), 10th Edition
- UL 1481 Power Supplies for Fire Alarm Systems
- IBC 2009 (when using SEISKIT-MULTI-1)
- CBC 2007 (when using SEISKIT-MULTI-1)

Agency Listings and Approvals

These listings and approvals apply to the modules specified in this document. In some cases, certain modules or applications may not be listed by certain approval agencies, or listing may be in process. Consult factory for latest listing status.

UL Listed: S2424

ULC Listed: S2424 (FL-PS6/10C)CSFM Approved: 7315-0075:0510

FDNY Approved
FM Approved

SYSTEM SPECIFICATIONS

Primary (AC) Power:

• FL-PS6(C): 120 VAC, 50/60 Hz, 5.0A maximum

• FL-PS10(C): 120VAC, 50/60 Hz, 6.2 A maximum

Wire Size: #12-14 AWG with 600 V insulation

Command Input Circuit:

Trigger Input Voltage: 9 to 32 VDC

Trigger Current: 2.0 mA (16 - 32 V); Per Input: 1.0 mA (9 - 16 V)

Trouble Contact Rating: 4 A at 24 VDC

Output Circuits:

· 24 VDC filtered, regulated

 FL-PS6: TB8-TB9 – 1A Regulated, 3A special applications; TB10-TB12 – 0.3A Regulated, 3A special applications

 FL-PS10: TB8-TB11 – 1.5A Regulated, 3A special applications; TB12-TB14 – 0.3A Regulated, 3A special applications

 6.0 A (FL-PS6) or 10.0 A (FL-PS10) maximum total continuous current for all outputs

Secondary Power (Battery) Charging Circuit:

Supports lead-acid batteries only

Float-charge voltage: 27.6 VDC

Maximum current charge: 1.5 A

Maximum battery capacity: 18 AH (inside cabinet)

Maximum battery charging capacity: 33 AH (external cabinet)

Physical:

Dimensions: 20.0"H x 14.5"W x 3.5"D (cm: 50.8H x 36.83W x 8.9D)

 Weight: with two 7Ah batteries is 24 pounds (10.9 kg), with two 18 AH batteries is 39 pounds (17.7 kg)

Ordering Information

FL-PS6: 6.0 A, 120 VAC remote charger power supply in a lockable, metal enclosure

FL-PS6C: Same as above, ULC-listed model

FL-PS10: 10.0 A, 120 VAC remote charger power supply in a lockable, metal enclosure

FL-PS10C: Same as above, ULC-listed model

ZNAC-PS: Optional Class A output converter module

CMF-300: Addressable Control Module for one Class B or Class A zone of supervised, polarized Notification Appliances. Notification Appliance Circuit option requires external 24 VDC to power notification appliances.

CRF-300: Addressable relay module containing two isolated sets of Form-C contacts, which operate as a DPDT switch

MMF-300: Addressable Monitor Module for one zone of normally open dry-contact initiating devices. Includes plastic cover plate and end-of-line resistor. Module may be configured for either a Class B or Class A IDC.

MDF-300: Dual Monitor Module. Same as MMF-300 except it provides two inputs for Class B wiring only

CDRM-300: Provides two monitored inputs and two Form-C relays. Functions in Class B wiring only.

CMF-300-6: Six-circuit supervised control module

CRF-300-6: Six Form-C relay control module

EOLR-1: 12/24 VDC end-of-line relay for monitoring four-wire smoke detector power

BAT-1270-BP: Battery, 12 volt, 7.0 AH, 5-pack (two required).

BAT-12180-BP: Battery, 12 volt, 18AH, 2-pack

BAT-12330: Battery, 12 volt, 33AH

SEISKIT-MULTI-1: Seismic kit for the FL-PS Series. Includes bracket and hardware for two 7AH or two 18AH batteries.

Fire*Lite® Alarms and System Sensor® are registered trademarks of Honeywell International, Inc. Wheelock® is a registered trademark of Cooper Technologies Company. Gentex® is a registered trademark of Gentex Corporation. AMSECO® is a registered trademark of Potter Electric Signal Company, LLC. ANSI® is a registered trademark of the American National Standards Institute, Inc. ©2020 by Honeywell International Inc. All rights reserved. Unauthorized use of this document is strictly prohibited.



This document is not intended to be used for installation purposes. We try to keep our product information up-to-date and accurate. We cannot cover all specific applications or anticipate all requirements. All specifications are subject to change without notice.

