• STS-K035

Window Intercom System and Hearing Loop





The STS-K035 Window Intercom System provides assistance for clear communication where normal speech is impaired by use of glass, a security screen or other similar barriers.

Components:

- > STS-A31H, Hearing Loop and Duplex Audio Communication Amplifier
- > STS-SU1, Staff Unit Speaker and Microphone
- > STS-B94 (LH/RH), Customer Speaker and Microphone Half Bridge Bar Unit (available with left or right curve)
- > IL-AE99, Under the Counter Hearing Loop Aerial
- > PS-55, Power Supply

Physical Data (boxed)

Dimensions	Height –6.30" Width – 12.20" Depth – 11.81"		
Weight	5.78lbs		
Construction	Metalwork - Mild Steel STS-A31H - ABS Plastic Housing		
Finish Options	Powder Coated Grey Leatherette Black Textured		

Applications

For use where one to one communication takes place such as:

- > Banks
- > Post offices
- → Theaters
- > Information Centers
- › Public Transit Systems
- > Ticket Counters
- > Embassies
- › Government Buildings

Standards

- CE, ROHS and WEEE compliant
- BS EN 60118-4, in correct installations



Phone: (616) 392-3400 Email: sales@contactainc.com www.contactainc.com



Physical and Technical Data (Individual Parts)

Components	Physical Data	Technical Data	Technical Data	
STS A31 Hearing Loop and Duplex Audio Communication Amplifier	Dimensions: Height -1.58" Width - 4.58" Depth - 4.50" Weight: 0.32lbs Construction: ABS Plastic Housing Finish: Matt Black, Fine Texture	Supply Voltage	12-14 VDC	
		Quiescent Current	100mA typical	
		Operating Current	2A typical on speech peaks	
		Power Switch	Push on - push off (tact switch under membrane)	
		Microphones	Electret, supply 5V via 2.2K load resistor	
		Speaker Output Power	RMS: 2.5W / 8 Ω 4.4W / 4 Ω	
		Loop Drive Compliance	Constant current, bounded by 4V RMS & 3A RMS	
		Total Harmonic Distortion	<5% (loop and speakers)	
STS-SU1 Staff Unit Speaker and Microphone	Dimensions: Height of base - 2.61" Height from bottom of base to top of microphone fully extended - 14.50" Width - 3.80" Depth - 6.02" Weight: 1.79lbs Construction: Mild Steel Finish: Powder Coated Grey Leatherette or Black Textured	Speaker		
		RMS	5W	
		Impedance	4 Ω	
		Output	SPL 1W @ 1M 85dB	
		Frequency Response	150Hz - 10300Hz	
		Microphone		
		Directional Response	Cardioid	
		Sensitivity	49.5dB+ 2dB @ 1kHz (0dB=1V/pa)	
		Impedance	1.6K Ω + 3-% @ 1kHz	
		Frequency Response	150Hz - 10500Hz	
	Dimensions of Base: Height - 2.65" Width - 2.37" Depth - 5.11" Dimensions of Microphone: Height from bottom of base to top of microphone fully extended - 9.63" Width of microphone curve - 9.88" Weight: 1.69lbs Construction: Mild Steel Finish: Powder Coated Grey Leatherette or Black Textured	Speaker		
STS-B94 (LH/RH)		RMS	5W	
		Impedance	4 Ω	
		Output	SPL 1W @ 1M 85dB	
Customer Speaker		Frequency Response	150Hz - 11000Hz	
and Microphone Half		Microphone		
Bridge Bar Unit		Directional Response	Cardioid	
		Sensitivity	-67dB +/- 3dB @ 1kHz	
		Impedance	1.6K Ω =/- 30% @ 1kHz	
		Frequency Response	70Hz - 14000Hz	
PS-55 Power Supply	Dimensions: Height - 1.38" Width - 2.08" Depth - 3.92"	Input	100-240V 50-60Hz 1A max	
	Cable length: 70.87" Weight: 0.51lbs Construction: ABS Case Finish: Black	Output	14V 2.14A 30W max	
IL-AE99 Loop Aerial				