# MEG 14-40 Gooseneck Microphone

## **FEATURES**

- Gooseneck with integrated Sennheiser KE 10
   microphone capsule
- RF shielding against intermodulation from wireless
   equipment/devices
- Streamlined design for seamless integration
- Premium quality made in Germany

The MEG 14-40 features a made in Germany quality gooseneck microphone on an attractive price. It features an integrated Sennheiser KE 10 microphone capsule with cardioid directivity for universal miking and a streamlined 40 cm gooseneck with a XLR 3M connector. The flexible element ensures precise alignment of the microphone.



## **SPECIFICATIONS**

Transducer principle	pre-polarised condenser microphone	
Pick-up pattern	cardioid	
Frequency response	50 Hz - 20 kHz	
Nominal impedance	< 100 Ω	
Maximum sound pressure level	130 dB SPL	
Equivalent noise level	26 dB (A) 37 dB (CCIR)	
Phantom powering	P12 - P48 V	
Current consumption microphone	3 mA	
Connectivity	XLR 3M	
Weight	147 g (4.72 oz)	
Length	450 mm (17.71")	
Diameter	8 mm (0.31")	
Operating temperature	0 °C to 40 °C (32 °F to 104 °F)	
Coating	matte black	

## **ARCHITECT'S SPECIFICATION**

The microphone shall be a pre-polarized condenser designed for permanent installation or portable applications. It shall have a microphone capsule with a cardioid polar pattern with uniform 120° angle of acceptance (-3 dB).


It shall have a frequency response of 50 Hz to 20,000 Hz and be capable of handling sound input levels up to 130 dB SPL. Nominal equivalent noise level shall be 26 dBA (37 dB weighted as per CCIR 468-3). Output shall be low impedance balanced (< 100  $\Omega$ ). Operating temperature shall be 0 °C to 40 °C (32 °F to 104 °F). The microphone shall operate from an external 12 V to 48 V DC phantom power source; current consumption shall be 3 mA. The microphone shall offer radio frequency interference (RFI) shielding against intermodulation from wireless equipment or devices.


The microphone shall be a gooseneck design ensuring precise alignment of the microphone and noiseless operation. It shall incorporate a self-contained power module with an XLR 3M-type connector at the base. The microphone shall be a small-diameter gooseneck design with a diameter of 8 mm (0.31") and an overall length of 450 mm (17.71"). Head diameter shall be 22.8 mm (0.9"). The microphone weight shall be 147 g (4.72 oz). Finish shall be matte black.

The microphone shall be Sennheiser MEG 14-40.

# MEG 14-40 Gooseneck Microphone

DIMENSIONS






**PIN ASSIGNMENT** 



1 Ground 2 Microphone + 3 Microphone –

# FREQUENCY RESPONSE



# MEG 14-40 Gooseneck Microphone

## **PRODUCT VARIANTS**

Product	Features	
MEG 14-40 B	<ul> <li>Gooseneck with integrated Senn- heiser KE 10 microphone capsule</li> </ul>	The MEG 1 gooseneck
Art. no. 504791	<ul> <li>RF shielding against intermodu- lation from wireless equipment/ devices</li> </ul>	an integrat cardioid di 40 cm goo
	<ul> <li>Streamlined design for seamless integration</li> </ul>	element er
	Premium quality made in Germany	
MEG 14-40-L B	<ul> <li>Gooseneck with integrated Senn- heiser KE 10 microphone capsule</li> </ul>	The MEG 1 gooseneck indicates t floor. It fea with cardio element of precise ali tor delivers microphon
Art. no. 504792	<ul> <li>92 • RF shielding against intermodu- lation from wireless equipment/ devices</li> </ul>	
	<ul> <li>Streamlined design for seamless integration</li> </ul>	
	• LED ring for speech indication	
	AC/DC lightring powering	
	Premium quality made in Germany	
MEG 14-40-L-II B	Intuitive handling	The MEG 1
Art. no. 506398	<ul> <li>Clearly visible LED ring and micro- phone button</li> </ul>	gooseneck indicates t
	<ul> <li>Proven Sennheiser KE 10 micro- phone capsule</li> </ul>	floor. It fea with cardio

The MEG 14-40 features a made in Germany quality gooseneck microphone on an attractive price. It features an integrated Sennheiser KE 10 microphone capsule with cardioid directivity for universal miking and a streamlined 40 cm gooseneck with a XLR 3M connector. The flexible element ensures precise alignment of the microphone.

The MEG 14-40-L features a made in Germany quality gooseneck microphone on an attractive price. A lightring indicates the spokesperson that is allowed to take the floor. It features a Sennheiser KE 10 microphone capsule with cardioid directivity for universal miking. The flexible element of the streamlined 40 cm gooseneck ensures precise alignment of the microphone. A XLR 5M connector delivers power for the red LED ring and connects the microphone signal.

The MEG 14-40-L-II features a made in Germany quality gooseneck microphone on an attractive price. A lightring indicates the spokesperson that is allowed to take the floor. It features a Sennheiser KE 10 microphone capsule with cardioid directivity for universal miking. The flexible element of the streamlined 40 cm gooseneck ensures precise alignment of the microphone. An XLR 5M connector delivers power for the green LED ring and connects the microphone signal.