


1-Phase Basic PDU specification drawing

230V 10A / 16A / 20A / 32A PDU : C13 x 8

unit : mm



Circuit Protection	Code
Fuse	F
MCB	CR

PDU Feed	Code
Bottom	B
Top	T

Chassis Color	Code
Black	1
White	2
Red	3
Blue	4
Green	5
Orange	6
Yellow	7
Purple	8

Standard color : Black



IEC 60309 Inlet



Open end



IEC 60309 Inlet



IEC320 C20



IEC320 C14

32A model :	Circuit Protection
V8C13-32A/ F _EN/3 B -1	Resettable Fuse x 2
V8C13-32A/ CR _EN/3 T -1	1-pole MCB x 2

20A model :	Circuit Protection
V8C13-20A/ F _OE/3 B -1	Resettable Fuse x 1
V8C13-20A/ CR _OE/3 T -1	1-pole MCB x 1

16A model :	Circuit Protection
V8C13-16A/ F _EN/3 B -1	Resettable Fuse x 1
V8C13-16A/ CR _EN/3 T -1	1-pole MCB x 1

16A model :	Circuit Protection
V8C13-16A/ F _C20/3 B -1	Resettable Fuse x 1
V8C13-16A/ CR _C20/3 T -1	1-pole MCB x 1

10A model :	Circuit Protection
V8C13-10A/ F _C14/3 B -1	Resettable Fuse x 1
V8C13-10A/ CR _C14/3 T -1	1-pole MCB x 1

Input Rating : 32Amp, 230V
Cordset : 3 meter 4.0mm sq. H05V V-F cordset
Protection : 16A resettable fuse or 16A hydraulic MCB x 2
Circuit A : Output 16A max., C13 #1-4
Circuit B : Output 16A max., C13 #5-8
Weight : Net 6.14 Kg / Gross 7.38 Kg

Input Rating : 20Amp, 230V
Cordset : 3 meter 2.5mm sq. H05V V-F cordset
Protection : 20A resettable fuse or 20A hydraulic MCB x 1
Circuit : Output 20A max., C13 #1-8
Weight : Net 4.68 Kg / Gross 5.92 Kg

Input Rating : 16Amp, 230V
Cordset : 3 meter 1.5mm sq. H05V V-F cordset
Protection : 16A resettable fuse or 16A hydraulic MCB x 1
Circuit : Output 16A max., C13 #1-8
Weight : Net 4.61 Kg / Gross 5.85 Kg

Input Rating : 16Amp, 230V
Cordset : 3 meter 1.5mm sq. H05V V-F cordset
Protection : 16A resettable fuse or 16A hydraulic MCB x 1
Circuit : Output 16A max., C13 #1-8
Weight : Net 4.53 Kg / Gross 5.77 Kg

Input Rating : 10Amp, 230V
Cordset : 3 meter 1.5mm sq. H05V V-F cordset
Protection : 10A resettable fuse or 10A hydraulic MCB x 1
Circuit : Output 10A max., C13 #1-8
Weight : Net 4.52 Kg / Gross 5.76 Kg

Operating Temperature : -5 to 60 °C
Storage Temperature : -25 to 65 °C
Operating Altitude : 0 to 2,000 m
Storage Altitude : 0 to 15,000 m
Humidity : 8 to 95% RH, non-condensing

EMC Compliance : CE / EMC
Safety Compliance : CE / LVD & UKCA
Tested to EN 62368-1:2014 / A11:2017 standard
Tested to EN 60730-1:2016 / A1:2019 standard
Environment Compliance : RoHS3 & REACH

AUSTIN HUGHES
Design. Manufacturing. Global Services.


The company reserves the right to modify product specifications without prior notice and assumes no responsibility for any error which may appear in this publication.

Copyright 2023 Austin Hughes Electronics Ltd. All rights reserved.


Product Dimension : 54 (W) x 70 (D) x 600 (H) mm
Packing Dimension (for 2 PDUs) : 110 (W) x 268 (D) x 1093 (H) mm

Lockable IEC Outlet

- Patented design for InfraPower PDU



C13 Outlet



C19 Outlet


Lockable IEC Cable

- Patented design of InfraPower PDU
- Low cost, easy to lock & secure
- Proprietary for lockable IEC outlet
- Applicable to standard IEC outlet
- 6 colors & 3 lengths available
- Custom color & length on request
- VDE & ENEC approval

C13 - C14

H05VV-F 3G 0.75mm²


Cable Color	0.5M	1M	2M
Black	✓	✓	✓
Grey	✓	✓	✓
Red	✓	✓	✓
Blue	✓	✓	✓
Green	✓	✓	✓
Orange	✓	✓	✓



C19 - C20

H05VV-F 3G 1.5mm²

Cable Color	1M	2M
Black	✓	✓
Grey	✓	✓
Red	✓	✓
Blue	✓	✓
Green	✓	✓
Orange	✓	✓




C13 - C14




lockable cable

C19 - C20

- ✓ low cost
- ✓ easy to lock
- ✓ secure



VMS Mounting Button



VMB Mounting Bracket

