



Shown in CC-37 Carrying Case

Features

- Motorized blade rotation
- Bluetooth communication
- Shock resistant
- Simple one-step operation
- 60,000 cleave blade life
- Field serviceable



CT50 Fiber Cleaver

The CT50 features automated blade rotation, unprecedented durability, and simplistic maintenance unseen with any other cleaver. Paired with a Bluetooth enabled Fujikura splicer, cleaver blade positions can be automatically advanced when needed based on cleave count or cleave quality. If automated rotation is not desired, the blade position can be advanced at the touch of a button, no tools required. The easy to read blade position indicator clearly displays the selected position. The Bluetooth® feature, along with simplified mechanical operation, increases overall productivity and reliability. The fiber clamp opens beyond 90 degrees and readies the blade for cleaving in the same motion. This allows easy viewing of the distance scale used to gauge cleave length. The 16-position blade yields 60,000 single-fiber cleaves, or 5,000 12-fiber ribbon cleaves. The built-in scrap collector conveniently stores fiber shards until they can be safely discarded.

The CT50 is an industry first cleaver ruggedized to withstand severe shock, including drops up to 30 inches. If needed, the CT50 is field serviceable with all precision components easily replaced in the field.

Specifications

ITEM		VALUE
Applicable Fiber	Fiber type	Single-mode optical fiber
		Multimode optical fiber
	Fiber count	Single up to 16 fibers
	Cladding dia.	Approx. 125 µm
Applicable Coating	Fiber plate	AD-10-M24 : Max. 900 µm coating diameter AD-50 : Max. 3 mm coating diameter
	Fiber holder	FH- 50, FH-60, FH-70, FH-100 and FH-110 series holders
Cleave Length	Fiber plate	AD-10-M24 : 5 to 20 mm for CD ≤ 250 µm AD-50 [CD = coating diameter] CD= 250µm or less : 5 to 20 mm 250 µm < CD < 1000µm : 10 to 20 mm 1000 µm < CD < 3 mm : 14 to 20 mm
	Fiber holder	Approx. 10 mm
Cleave Angle	Single fiber	Avg. 0.3 to 0.9 degrees
	Fiber ribbon	Avg. 0.3 to 1.2 degrees
Blade Life		Approx. 60,000 fiber cleaves
Physical description	Dimensions W	Approx. 120 mm when closing the lever
	Dimensions D	Approx. 95 mm when closing the lever
	Dimensions H	Approx. 58 mm when closing the lever
	Weight	Approx. 305 g including battery and AD-10-M24
Environmental condition	Temperature	Operate : -10 to 50°C Storage : -40 to 80°C
	Humidity	Operate : 0 to 95% non-condensing Storage : 0 to 95% non-condensing
Battery		2 pieces of LR03/AAA dry battery
Wireless interface ¹		Bluetooth 4.1 LE
Screw hole for tripod		1/4-20UNC
Other features	Blade rotation	Motorized rotation Manual rotation dial
	Replaceable parts	Blade Clamp arm

1. The CT50 No Bluetooth option has the wireless interface permanently disabled.

continued
→

CT50 Fiber Cleaver

Ordering Information

DESCRIPTION	APPLICATION	FIBER HANDLING SYSTEM	CLEAVE LENGTH	AFL NO.
CT50	Single or Ribbon Fiber	AD-10-M24 adapter plate for single fibers or fiber holders for ribbons	See Specifications table on previous page	S017030
CT50 No Bluetooth	Single or Ribbon Fiber	AD-10-M24 adapter plate for single fibers or fiber holders for ribbons	See Specifications table on previous page	S018020

Accessories

DESCRIPTION	AFL NO.
CB-08 Replacement Blade	S017076
FDB-05 Scrap Collector Box	S017121
AD-50 Adapter Plate	S017010
AD-10-M24 Fiber Plate	S017335
ARM-CT50-01 Replacement Arm Set	S017122
BRW-CT08-01 Blade Rotary Wheel	S017110
SC-CT50-01 Side Cover	S017108
CC-37 Transit Case	S017077
SPA-CT-08-10 Spacer	S017011
FDB-05 Fiber Dust Box	S017121

Splice+ is a smartphone application that works in cooperation with Fujikura's splicers, cleavers and ribbon fiber strippers which have Bluetooth capability.

Get the **Splice+** app at the Apple App store or at Google Play.

