

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Trade name or designation of the mixture	Hylotype Red 100
Registration number	-
Synonyms	None.
SDS number	37
Issue date	08-March-2017
Version number	01
Revision date	-
Supersedes date	-

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Non-Setting and Non-Hardening Gasketing Compound.
Uses advised against	Use in accordance with supplier's recommendations.

1.3. Details of the supplier of the safety data sheet

Manufacturer:	Hylomar Ltd.
Address:	Hylo House, Cale Lane, New Springs, Wigan, Greater Manchester, UK, WN2 1JT
Telephone number:	+44(0)1942 617000
E-mail address:	info@hylomar.co.uk
Contact person:	Technical Department
1.4. Emergency telephone number	+1-760-476-3961 (US)
	Access code: 333544

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

The mixture has been assessed and/or tested for its physical, health and environmental hazards and the following classification applies.

Classification according to Regulation (EC) No 1272/2008 as amended

Physical hazards

Flammable liquids	Category 2	H225 - Highly flammable liquid and vapour.
-------------------	------------	--

Health hazards

Serious eye damage/eye irritation	Category 2	H319 - Causes serious eye irritation.
Specific target organ toxicity - single exposure	Category 3 narcotic effects	H336 - May cause drowsiness or dizziness.

Hazard summary	Highly flammable liquid and vapour. Causes serious eye irritation. May cause drowsiness or dizziness.
-----------------------	---

2.2. Label elements

Label according to Regulation (EC) No. 1272/2008 as amended

Contains: Acetone

Hazard pictograms



Signal word: Danger

Hazard statements

H225	Highly flammable liquid and vapour.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.

Precautionary statements

Prevention

P210	Keep away from heat/sparks/open flames/hot surfaces. - No smoking.
P233	Keep container tightly closed.
P280	Wear protective gloves/protective clothing/eye protection/face protection.

Response

P312	Call a POISON CENTRE or doctor/physician if you feel unwell.
------	--

Storage

P403 + P235	Store in a well-ventilated place. Keep cool.
-------------	--

Disposal

P501	Dispose of contents/container in accordance with local/regional/national/international regulations.
------	---

Supplemental label information EUH066 - Repeated exposure may cause skin dryness or cracking.

2.3. Other hazards The product contains organic solvents which may be absorbed into the body by skin contact and cause permanent damage to the nervous system, including the brain. Not a PBT or vPvB substance or mixture.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

General information

Chemical name	%	CAS-No. / EC No.	REACH Registration No.	INDEX No.	Notes
Acetone	30 - 50	67-64-1 200-662-2	-	606-001-00-8	#
Classification:	Flam. Liq. 2;H225, Eye Irrit. 2;H319, STOT SE 3;H336				

List of abbreviations and symbols that may be used above

#: This substance has been assigned Community workplace exposure limit(s).

Composition comments All concentrations are in percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume. The full text for all H-statements is displayed in section 16.

SECTION 4: First aid measures

General information

If you feel unwell, seek medical advice (show the label where possible). Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves. Show this safety data sheet to the doctor in attendance. Thermal burns: Flush with water immediately. While flushing, remove clothes which do not adhere to affected area. Call an ambulance. Continue flushing during transport to hospital.

4.1. Description of first aid measures

Inhalation	If breathing is difficult, remove to fresh air and keep at rest in a position comfortable for breathing. Call a physician if symptoms develop or persist.
Skin contact	Immediately take off all contaminated clothing. Wash skin thoroughly with soap and water. If irritation persists get medical attention.
Eye contact	Immediately flush with plenty of water for at least 15 minutes. Remove contact lenses, if present and easy to do. Get medical attention if irritation develops and persists.
Ingestion	Rinse mouth. Drink a few glasses of water or milk. Get medical attention if any discomfort continues.

4.2. Most important symptoms and effects, both acute and delayed Irritation of eyes and mucous membranes. Skin irritation. Defatting of the skin. Vapours may cause drowsiness and dizziness.

4.3. Indication of any immediate medical attention and special treatment needed Provide general supportive measures and treat symptomatically.

SECTION 5: Firefighting measures

General fire hazards

The product is highly flammable, and explosive vapour/air mixtures may be formed even at normal room temperatures. Vapours are heavier than air and may travel along the ground to some distant source of ignition and flash back.

5.1. Extinguishing media

Suitable extinguishing media	Water spray, foam, dry powder or carbon dioxide.
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.

5.2. Special hazards arising from the substance or mixture By heating and fire, toxic vapours/gases may be formed.

5.3. Advice for firefighters

Special protective equipment for firefighters

Self-contained breathing apparatus and full protective clothing must be worn in case of fire. Selection of respiratory protection for firefighting: follow the general fire precautions indicated in the workplace.

Special fire fighting procedures

Use standard firefighting procedures and consider the hazards of other involved materials. Cool containers exposed to heat with water spray and remove container, if no risk is involved. Prevent runoff from fire control or dilution from entering streams, sewers or drinking water supply.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

For non-emergency personnel

Keep upwind. Ventilate closed spaces before entering them. Avoid inhalation of vapours/spray and contact with skin and eyes. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing.

For emergency responders

Keep unnecessary personnel away. Wear protective clothing as described in Section 8 of this safety data sheet.

6.2. Environmental precautions

Prevent further leakage or spillage if safe to do so. Do not discharge into drains, water courses or onto the ground.

6.3. Methods and material for containment and cleaning up

Eliminate all ignition sources. Ventilate the area. Wipe up with absorbent material (e.g. cloth, fleece). Transfer to a container for disposal. Following product recovery, flush area with water.

6.4. Reference to other sections

For personal protection, see section 8 of the SDS. For waste disposal, see section 13 of the SDS.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Use only outdoors or in a well-ventilated area. Keep away from sources of ignition - No smoking. Avoid inhalation of vapours/spray and contact with skin and eyes. Wear protective clothing as described in Section 8 of this safety data sheet. Wash thoroughly after handling. Wash contaminated clothing before reuse. Observe good industrial hygiene practices. Avoid release to the environment.

7.2. Conditions for safe storage, including any incompatibilities

Keep container tightly closed in a cool, well-ventilated place. Keep away from heat, spark, open flames and other sources of ignition. Store away from incompatible materials.

7.3. Specific end use(s)

Non-Setting and Non-Hardening Gasketing Compound.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational exposure limits

UK. EH40 Workplace Exposure Limits (WELs)

Components	Type	Value	Form
Acetone (CAS 67-64-1)	STEL	3620 mg/m ³	
		1500 ppm	
	TWA	1210 mg/m ³	
Silica, amorphous, fumed (CAS 112945-52-5)		500 ppm	
	TWA	6 mg/m ³	Inhalable dust.
		2.4 mg/m ³	Respirable dust.

EU. Indicative Exposure Limit Values in Directives 91/322/EEC, 2000/39/EC, 2006/15/EC, 2009/161/EU

Components	Type	Value
Acetone (CAS 67-64-1)	TWA	1210 mg/m ³
		500 ppm

Biological limit values

No biological exposure limits noted for the ingredient(s).

Recommended monitoring procedures

Follow standard monitoring procedures.

Derived no effect levels (DNELs)

Not available.

Predicted no effect concentrations (PNECs)

Not available.

8.2. Exposure controls

Appropriate engineering controls

Provide adequate ventilation. Observe Occupational Exposure Limits and minimise the risk of inhalation of vapours. Eye wash facilities and emergency shower must be available when handling this product.

Individual protection measures, such as personal protective equipment

General information	Personal protective equipment should be chosen according to the CEN standards and in discussion with the supplier of the personal protective equipment.
Eye/face protection	If eye contact is likely, safety glasses with side shields or chemical type goggles should be worn.
Skin protection	
- Hand protection	Wear protective gloves. Butyl rubber gloves are recommended. Be aware that the liquid may penetrate the gloves. Frequent change is advisable. Suitable gloves can be recommended by the glove supplier.
- Other	Normal work clothing (long sleeved shirts and long pants) is recommended.
Respiratory protection	In case of inadequate ventilation or risk of inhalation of vapours, use suitable respiratory equipment with gas filter (type A2). If engineering controls do not maintain airborne concentrations below recommended exposure limits (where applicable) or to an acceptable level (in countries where exposure limits have not been established), an approved respirator must be worn.
Thermal hazards	Wear appropriate thermal protective clothing, when necessary.
Hygiene measures	Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.
Environmental exposure controls	Environmental manager must be informed of all major releases.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance

Physical state	Liquid.
Form	Thixotropic gel.
Colour	Red.
Odour	Acetone.
Odour threshold	Not available.
pH	Not available.
Melting point/freezing point	Not available.
Initial boiling point and boiling range	Not available.
Flash point	-17.0 °C (1.4 °F)
Evaporation rate	Not available.
Flammability (solid, gas)	Not applicable.

Upper/lower flammability or explosive limits

Flammability limit - lower (%)	Not available.
Flammability limit - upper (%)	Not available.
Vapour pressure	Not available.
Vapour density	Not available.
Relative density	0.95 (20 °C)
Solubility(ies)	Insoluble in water.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	Not available.
Decomposition temperature	Not available.
Viscosity	Not available.
Explosive properties	Not explosive.
Oxidising properties	Not oxidising.

9.2. Other information

VOC	40 %
------------	------

SECTION 10: Stability and reactivity

10.1. Reactivity	The product is stable and non reactive under normal conditions of use, storage and transport.
10.2. Chemical stability	Material is stable under normal conditions.
10.3. Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.

10.4. Conditions to avoid	Heat, flames and sparks.
10.5. Incompatible materials	Strong oxidising agents.
10.6. Hazardous decomposition products	Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.

SECTION 11: Toxicological information

General information Occupational exposure to the substance or mixture may cause adverse effects.

Information on likely routes of exposure

Inhalation	Vapours may cause drowsiness and dizziness. In high concentrations, vapours may be irritating to the respiratory system.
Skin contact	Prolonged or repeated skin contact may cause drying, cracking, or irritation.
Eye contact	Causes serious eye irritation.
Ingestion	Ingestion may cause irritation and malaise.

Symptoms Irritation of eyes and mucous membranes. Skin irritation. Defatting of the skin. Vapours may cause drowsiness and dizziness.

11.1. Information on toxicological effects

Acute toxicity Not expected to be acutely toxic.

Components	Species	Test results
------------	---------	--------------

Acetone (CAS 67-64-1)

Acute

Dermal

LD50	Rabbit	> 20 ml/kg
------	--------	------------

Inhalation

LC50	Rat	50 mg/l, 8 Hours
------	-----	------------------

Oral

LD50	Rat	5800 mg/kg
------	-----	------------

Skin corrosion/irritation May cause skin irritation.

Serious eye damage/eye irritation Causes serious eye irritation.

Respiratory sensitisation Based on available data, the classification criteria are not met.

Skin sensitisation Based on available data, the classification criteria are not met.

Germ cell mutagenicity Based on available data, the classification criteria are not met.

Carcinogenicity Based on available data, the classification criteria are not met.

Reproductive toxicity Based on available data, the classification criteria are not met.

Specific target organ toxicity - single exposure May cause drowsiness or dizziness.

Specific target organ toxicity - repeated exposure Based on available data, the classification criteria are not met.

Aspiration hazard Not an aspiration hazard.

Mixture versus substance information Not applicable.

Other information No other specific acute or chronic health impact noted.

SECTION 12: Ecological information

12.1. Toxicity The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

Components	Species	Test results
------------	---------	--------------

Acetone (CAS 67-64-1)

Aquatic

Fish	LC50	Fathead minnow (Pimephales promelas) > 100 mg/l, 96 hours
------	------	---

12.2. Persistence and degradability No data available.

12.3. Bioaccumulative potential

Partition coefficient

n-octanol/water (log Kow)

Acetone (CAS 67-64-1)	-0.24
-----------------------	-------

Bioconcentration factor (BCF)	Not available.
12.4. Mobility in soil	The product contains organic solvents which will evaporate easily from all surfaces.
Mobility in general	The product contains organic solvents which will evaporate easily from all surfaces.
12.5. Results of PBT and vPvB assessment	Not a PBT or vPvB substance or mixture.
12.6. Other adverse effects	The product contains a substance which has a photochemical ozone creation potential.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Residual waste	Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).
Contaminated packaging	Empty containers should be taken to an approved waste handling site for recycling or disposal.
EU waste code	08 04 09* The Waste code should be assigned in discussion between the user, the producer and the waste disposal company.
Disposal methods/information	Do not discharge into drains, water courses or onto the ground. Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Dispose of contents/container in accordance with local/regional/national/international regulations.

SECTION 14: Transport information

ADR

14.1. UN number	UN1133
14.2. UN proper shipping name	ADHESIVES.
14.3. Transport hazard class(es)	
Class	3
Subsidiary risk	-
Label(s)	3
Hazard No. (ADR)	33
Tunnel restriction code	D/E
14.4. Packing group	II
14.5. Environmental hazards	No.
14.6. Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.

RID

14.1. UN number	UN1133
14.2. UN proper shipping name	ADHESIVES.
14.3. Transport hazard class(es)	
Class	3
Subsidiary risk	-
Label(s)	3
14.4. Packing group	II
14.5. Environmental hazards	No.
14.6. Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.

ADN

14.1. UN number	UN1133
14.2. UN proper shipping name	ADHESIVES.
14.3. Transport hazard class(es)	
Class	3
Subsidiary risk	-
Label(s)	3
14.4. Packing group	II
14.5. Environmental hazards	No.
14.6. Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.

IATA

14.1. UN number	UN1133
14.2. UN proper shipping name	Adhesives.

14.3. Transport hazard class(es)

Class 3
Subsidiary risk -
Label(s) 3

14.4. Packing group II

14.5. Environmental hazards No.

14.6. Special precautions for user Read safety instructions, SDS and emergency procedures before handling.

IMDG

14.1. UN number UN1133

14.2. UN proper shipping name ADHESIVES.

14.3. Transport hazard class(es)

Class 3
Subsidiary risk -
Label(s) 3

14.4. Packing group II

14.5. Environmental hazards

Marine pollutant No.

EmS F-E, S-D

14.6. Special precautions for user Read safety instructions, SDS and emergency procedures before handling.

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code Not applicable.

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****EU regulations**

Regulation (EC) No. 1005/2009 on substances that deplete the ozone layer, Annex I and II, as amended

Not listed.

Regulation (EC) No. 850/2004 On persistent organic pollutants, Annex I as amended

Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 1 as amended

Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 2 as amended

Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 3 as amended

Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex V as amended

Not listed.

Regulation (EC) No. 166/2006 Annex II Pollutant Release and Transfer Registry, as amended

Not listed.

Regulation (EC) No. 1907/2006, REACH Article 59(10) Candidate List as currently published by ECHA

Not listed.

Authorisations

Regulation (EC) No. 1907/2006, REACH Annex XIV Substances subject to authorisation, as amended

Not listed.

Restrictions on use

Regulation (EC) No. 1907/2006, REACH Annex XVII Substances subject to restriction on marketing and use as amended

Acetone (CAS 67-64-1)

Directive 2004/37/EC: on the protection of workers from the risks related to exposure to carcinogens and mutagens at work, as amended.

Not listed.

Other EU regulations

Directive 2012/18/EU on major accident hazards involving dangerous substances, as amended

Acetone (CAS 67-64-1)

Other regulations

This Safety Data Sheet complies with the requirements of Regulation (EC) No 1907/2006. The product is classified and labelled in accordance with Regulation (EC) 1272/2008 (CLP Regulation) as amended and respective national laws implementing EC directives.

National regulations	Follow national regulation for work with chemical agents.
15.2. Chemical safety assessment	No Chemical Safety Assessment has been carried out.

SECTION 16: Other information

List of abbreviations

DNEL: Derived No-Effect Level.
PBT: Persistent, bioaccumulative and toxic.
PNEC: Predicted No-Effect Concentration.
vPvB: Very Persistent and very Bioaccumulative.
LD50: Lethal Dose, 50%.
LC50: Lethal Concentration, 50%.
STEL: Short term exposure limit.

References

HSDB® - Hazardous Substances Data Bank
Registry of Toxic Effects of Chemical Substances (RTECS)
ESIS (European chemical Substances Information System)

Information on evaluation method leading to the classification of mixture

The mixture is classified based on test data for physical hazards. The classification for health and environmental hazards is derived by a combination of calculation methods and test data, if available. For details, refer to Sections 9, 11 and 12.

Full text of any H-statements not written out in full under Sections 2 to 15

H225 Highly flammable liquid and vapour.
H319 Causes serious eye irritation.
H336 May cause drowsiness or dizziness.

Training information

Follow training instructions when handling this material.

Disclaimer

The information in the sheet was written based on the best knowledge and experience currently available.