

## APC EPDU1116B power distribution unit (PDU) 24 AC outlet(s) 0U Black

**Brand :** APC

**Product code:** EPDU1116B

**Product name :** EPDU1116B

EPDU1116B, Zero U, 16A, 230V, 20x C13, 4x C19, 62x902x44 mm, Black

APC EPDU1116B. PDU types: Basic, Rack capacity: 0U, Type: Single-phase. AC outlets quantity: 24 AC outlet(s), AC outlet types: C13 coupler, C19 coupler, Power plug: IEC 60309. Cable length: 3 m. Nominal input voltage: 200/208/230 V, Maximum current: 16 A, AC input frequency: 50/60 Hz. Width: 62 mm, Depth: 44 mm, Height: 902 mm



Design		Weight & dimensions	
PDU types *	Basic	Width	62 mm
Type	Single-phase	Depth	44 mm
Rack capacity *	0U	Height	902 mm
Mounting	Vertical	Weight	2.2 kg
Housing material	Aluminium	<b>Packaging data</b>	
Product colour	Black	Package weight	2.98 kg
On/off switch	✗	Package width	160 mm
<b>Ports &amp; interfaces</b>		Package depth	110 mm
AC outlets quantity *	24 AC outlet(s)	Package height	1320 mm
Power plug	IEC 60309	<b>Packaging content</b>	
AC outlet types *	C13 coupler, C19 coupler	Manual	✓
<b>Features</b>		<b>Operational conditions</b>	
Cable length	3 m	Operating temperature (T-T)	0 - 45 °C
<b>Power</b>		Storage temperature (T-T)	-25 - 65 °C
Nominal input voltage *	200/208/230 V	Operating relative humidity (H-H)	5 - 95%
AC input frequency	50/60 Hz	Storage relative humidity (H-H)	5 - 95%
Maximum current *	16 A	Operating altitude	0 - 3000 m
Nominal output voltage	230 V	Non-operating altitude	0 - 9000 m
Load capacity	3680 VA		
Maximum input current per phase	16 A		



731304405016

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 15-FEB-2022. Prints or copies of Information are only valid on the printed Publication date