



# APC AP8881 power distribution unit (PDU) 42 AC outlet(s) 0U Black

Brand : APC

Product code: AP8881

Product name : AP8881

Rack PDU 2G, Metered, ZeroU, 11kW, 230V, (36) C13 & (6) C19

APC AP8881 power distribution unit (PDU) 42 AC outlet(s) 0U Black:

APC Metered Rack Power Distribution Units (PDUs) provide active metering to enable energy optimization and circuit protection. User-defined alarm thresholds mitigate risk with real-time local and remote alerts to warn of potential circuit overloads. Metered Rack PDUs provide power utilization data to allow Data Center Managers to make informed decisions on load balancing and right sizing IT environments to lower total cost of ownership. Metered Rack PDUs include real power monitoring, a temperature/humidity sensor port, locking IEC receptacles, and ultra low profile circuit breakers. Users can access and configure Metered Rack PDUs through secure Web, SNMP, or Telnet Interfaces which are complimented by APC Centralized Management platforms using InfraStruxure Central, Operations, Capacity, and Energy Efficiency.



Design		Power	
PDU types *	Metered	AC input frequency	50 - 60 Hz
Rack capacity *	0U	Maximum current *	16 A
Mounting	Vertical	Nominal output voltage	230 V
Product colour	Black	Load capacity	11040 VA
<b>Ports &amp; interfaces</b>		Maximum input current per phase	16 A
AC outlets quantity *	42 AC outlet(s)	Maximum total current draw per phase	16 A
Power plug	IEC309	Maximum power	11040 W
AC outlet types *	C13 coupler, C19 coupler	<b>Weight &amp; dimensions</b>	
Input connection type	IEC 309 16A 3P+N+PE, IEC 309 20A 3P+N+E	Dimensions (WxDxH)	56 x 44 x 1791 mm
Output connections	36x IEC 320 C13 6x IEC 320 C19	Weight	6.38 kg
<b>Features</b>		<b>Operational conditions</b>	
Cable length	1.83 m	Operating temperature (T-T)	5 - 45 °C
Certification	CSA C22.2 No. 60950, IEC 60950, UL 60950-1, VDE RoHS, REACH	Storage temperature (T-T)	-25 - 65 °C
<b>Management features</b>		Operating relative humidity (H-H)	5 - 95%
Monitoring	Current, Power, Voltage	Storage relative humidity (H-H)	5 - 95%
<b>Power</b>			
Nominal input voltage *	400 V		



731304277071

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 28-FEB-2022. Prints or copies of Information are only valid on the printed Publication date