



Fast Ethernet and PoE+ over Coax with up to 6,000ft (1,830m) Reach

EC-Base Extender Solution

The NVT Phybridge EC-Base Extender Solution is designed to supercharge the downlink ports of a standard Ethernet switch, delivering 10/100Mbps symmetrical (full duplex) and PoE over Coax infrastructure with distances up to 6,000ft (1,830m). **That's 18X the reach of standard Ethernet switches,** thus removing the costs and disruptions associated with multiple IDF closet requirements.

With the EC-Base Extender Solution, IP IoT devices can be connected to the existing Coax cabling infrastructure, delivering optimal performance while saving cost, time, and environmental e-waste. Furthermore, the cost savings realized by using the EC Extender Solution can enable system designers to transfer budget and resources towards higher-quality applications and IEEE-compliant IoT devices, including IP-enabled phones, cameras, access control, speakers, and even facilities lighting.

Extend the reach of standard PoE switches with the EC Extender Solution

EC-Base Paired with the EC-Link Enable 1 IP endpoint from a single long run Coax cable with up to 30W of power



***EC-Base Paired with the EC-Link+** Enable 1 IP endpoint from a single long run Coax cable with up to 50W of power



***EC-Base Paired with the EC4** Enable 4 IP endpoints from a single long run Coax cable with up to 50W of power per port

NV-ECLK-BSE



*Pairing options available in conveniently packaged EC-Extender Kits

NVT PHYBRIDGE EC-Base Extender DATASHEET

AT A GLANCE

(NV-ECLK-BSE)

- Base unit for 1-port long reach PoE Extender
- Negotiates with PoE switch
- When paired with EC-Link+ (50W), EC4 (30W) or EC-Link (30W) Adapters, delivers PoE over coax with up to 6,000ft (1,830m) reach
- Can be locally powered
- EN 50121-4 Standard for Railway/ Subway environments

EC-EXTENDER KITS

Each EC Extender Kit is conveniently packaged and includes an EC-Link+ or EC4 Adapter, an EC-Base Extender, and an external power supply.

1-Port EC Extender Kit (NV-ECLK-PLS-XKIT)

- Extend reach of standard PoE switch
- Single port coax extender solution enabling 1 endpoint from a single long run Coax cable
- 10/100Mbps symmetrical (full duplex) and PoE+ (up to 30W) with up to 6,000ft (1,830m) reach
- Up to 50W of power available for the endpoint
- · Adapters can be locally powered
- Includes: EC-Base Extender, EC-Link+ Adapter, and 60W, 55V external power supply

4-Port EC Extender Kit (NV-EC-04-XKIT)

- Extend reach of standard PoE switch
- Single port coax extender solution enabling 4 IP endpoints from a single long run Coax cable
- 10/100Mbps symmetrical (full duplex) and PoE+ (up to 30W) with up to 3,000ft (915m) reach
- Delivers up to 30W of power per downlink port
- Adapters can be locally powered
- Includes: EC-Base Extender, EC4 Adapter, and 110W, 55V external power supply





EC-Base Technical Specifications

Model	EC-Base					
Part Number	NV-ECLK-BSE					
Dimensions	 10.09cm x 5.03cm x 2.57cm (LxWxH); 3.97" x 1.98" x 1.01" (LxWxH) 					
Weight	108g (3.81oz.)					
Interface: Network Infrastructure side (CLEER)	1 BNC port: Coax cable (RG59, RG6, RG11)					
Interface: IEEE Side (IP Device)	(For General/PoE Switch) 1 RJ45 port: supports negotiation with IEEE 802.3 af/at switches					
Power Supply	PoE from standard PoE switch, or external power supply; maximum 50W if locally powered					

Power Consumption	1W			
Operating temperature	-58°F to +158°F (-50°C to +70°C) Tests conducted against international safety standard at maximum ambient temperatures of 60°C at 30W and 55°C at 50W			
Mean Time Before Failure (MTBF)	20+ years			
Humidity	10% to 95% (non-condensing) at 35° C			
Rack Mount Model NV-RMEXT				

EC-Base Compliance and Agency Approval

ЕМС	Emissions: FCC Part 15, ICES-003, EN 55032:2012, EN 50121-4:2015 Class B Immunity: EN 55024:2010, EN 50121-4:2015
Safety	UL 60950-1 2nd Ed 2014-10-14, CAN/CSA C22.2 No. 60950-1-07 2nd Ed 2014-10 IEC 60950-1:2005+A1+A2, EN 60950-1:2006+A1+A2+A11+A12
Environment	RoHS Directive 2011/65

Power & Distance Chart

EC-Base used	l with EC-Lin	k+										
	300ft (92m)	600ft (183m)	900ft (275m)	1,200ft (365m)	1,500ft (457m)	2,000ft (610m)	2,500ft (762m)	3,000ft (915m)	3,500ft (1,067m)	4,000ft (1,220m)	5,000ft (1,524m)	6,000ft (1,830m)
RG11 14AWG	30W	30	30	30	30	29	29	28	27	27	25	24
RG6 18AWG	30W	30	28	27	26	24	22	20	14	16	12	8
RG59 20AWG	30W	27	24	22	19	15	10	6	2	0		
EC-Base used	EC-Base used with EC-Link											
RG11 14AWG	30W	30	30	30	30	29	29	28	27	27		
RG6 18AWG	30W	30	28	27	26	24	22	20	14	16		
RG59 20AWG	30W	27	24	22	19	15	10	6	2	0		
EC-Base used	EC-Base used with EC4											
RG11 14AWG	30W	30	30	30	30	29	29	28				
RG6 18AWG	30W	30	28	27	26	24						
RG59 20AWG	30W	27	24	22	19							

100Mbit 10Mbit

Power & Distances are based on the following cable specs:

Cable Spec	Core Type	AWG	Diameter	Wire Resistance (m)	Wire Resistance (ft)
RG-11	Solid Copper	14 AWG	1.63 mm	1.21 Ω/100m	0.37 Ω/100ft
RG-6	Solid Copper	18 AWG	1.01 mm	3.60 Ω/100m	1.10 Ω/100ft
RG-59U	Solid Copper	22 AWG	0.64 mm	7.87 Ω/100m	2.40 Ω/100ft

CLEER FAMILY ADAPTER OPTIONS

EC Adapter Options

There are three media converter options available to pair with the CLEER family of switches to extend PoE over Coax. The EC-Link and EC Link+ are single endpoint solutions and the EC4 enables 4 IP endpoints from a single long run Coax cable.

EC-Link







EC Adapters Technical Specifications

Model Number	EC-Link	EC-Link+	EC4		
Part Number	NV-ECLNK	NV-ECLK-PLS	NV-EC-04		
Dimensions	8.8cm x 3.2cm x 2.1cm (LxWxH); 10.09cm x 5.03cm x 2.57cm (LxWxH); 3.46" x 1.23" x 0.83" (LxWxH) 3.97" x 1.98" x 1.01" (LxWxH)		11cm x 7cm x 2.5cm (LxWxH); 4.3" x 2.75" x 0.98" (LxWxH)		
Weight	42g (1.48oz.)	108g (3.81oz.)	96g (3.38oz.)		
Interface: Network Infrastructure side (CLEER)			1 BNC port: Coax cable (RG59, RG6, RG11)		
Line Speed	10/100Mbps full duplex	10/100Mbps full duplex	100Mbps full duplex		
Interface: IEEE Side (IP Device)	1 RJ45 port; device must be IEEE 802.3 af/at compliant				
Power Supply	PoE from the CLEER / EC switch or local power from EC-Base, maximum 30W (over 2-pairs) Maximum 50W (If locally powered and 30W if power provided from switch) delivered on 4 pairs.		PoE from the CLEER / EC switch, or external power supply; maximum 50W (over 4-pairs) each port		
DC IN	Optional (sold separately) 48V – 56VDC via an external AC/DC Power Adapter with phoenix connector (IEC Class II isolated only) NOTE 1: Local power supply used must have its output isolated from Earth potential. NOTE 2: If voltage of local power supply is lower than the power voltage provided from the PoE switch, then power on the PoE switch should be turned off.	Optional (sold separately) 48V – 56VDC via an external AC/DC Power Adapter (IEC Class II isolated only) with barrel connector NOTE 1: Local power supply used must have its output isolated from Earth potential. NOTE 2: If voltage of local power supply is lower than the power voltage provided from the PoE switch, then power on the PoE switch should be turned off.	Optional (sold separately) 48V – 56VDC via an external AC/DC Power Adapter (IEC Class II isolated only) with barrel connector NOTE 1: Local power supply used must have its output isolated from Earth potential. NOTE 2: If voltage of local power supply is lower than the power voltage provided from the PoE switch, then power on the PoE switch should be turned off.		
Power Consumption	0.9W	1.1W	1W		
Operating Temperature	-58°F to +158°F (-50°C to +70°C) Tests conducted against international safety standard at maximum ambient temperatures of 50°C	-58°F to +158°F (-50°C to +70°C) Tests conducted against international safety standard at maximum ambient temperatures of 60°C at 30W and 55°C at 50W	-58°F to +158°F (-50°C to +70°C) Tests conducted against international safety standard at maximum ambient temperatures of 50°C		
Mean Time Before Failure (MTBF)	20+ years	20+ years	20+ years		
Humidity	10% to 95% (non-condensing) at 35° C	10% to 95% (non-condensing) at 35° C	10% to 95% (non-condensing) at 35° C		

EC Adapters Compliance and Agency Approval

ЕМС	Emissions: FCC Part 15, ICES-003, EN 55032:2012, EN 50121-4:2015 Class A (EC4) Class B (EC-Link and EC-Link+)
	Immunity: EN 55024:2010, EN 50121-4:2015
Cofoty	UL 60950-1 2nd Ed 2014-10-14, CAN/CSA C22.2 No. 60950-1-07 2nd Ed 2014-10
Safety	IEC 60950-1:2005+A1+A2, EN 60950-1:2006+A1+A2+A11+A12
Environment	RoHS Directive 2011/65

() NVT PHYBRIDGE