

SST™ Central Tube Dielectric Armour Outdoor Cable 6F E9 SMF-28e+® ITU G652.D CT 3.0

CORNING

Part Number:
006EEG-13122A20

Corning cables can be employed outdoors for campus backbone.

The loose tube cable construction, by isolating the fibres from installations and environmental rigors, provides stable and highly reliable transmission parameters.

Features and Benefits

Waterblocking technology

Outside Plant (OSP) applications

All-dielectric cable construction

Requires no grounding or bonding

UV and microbe resistant

Can be directly buried or installed in ducts

Small diameter and bend radius


Easy installation in space-constrained areas

Laminated swelling glass yarns

Improved rodent resistance and longitudinal water protection

Fibres colour coding to Telcordia-Bellcore

Easy identification of the individual fibres



SST™ Central Tube Dielectric Armour Outdoor Cable, 6F E9 SMF-28e+® ITU G652.D CT 3.0

SST™ Central Tube Dielectric Armour Outdoor Cable 6F E9 SMF-28e+® ITU G652.D CT 3.0

CORNING

Specifications

General Specifications

Cable type	Central Tube
Environment	Outdoor
Product type	Dielectric armour
Fibre category	Single-mode (OS2)
Coding according to EN 60794-1-1 (DIN VDE 0888-100-1)	A-DQ(ZN)B2Y
Application	Duct
Cable geometry	Round

Standards

Fibre Standards	TIA/EIA-492CAAB, IEC 60793-2-50 Type B1.3, ITU-T G.652.D, ISO/IEC 11801 Ed.2.2
RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Waterblocking	IEC 60794-1-2 F5

Standards

Fibre Standards	TIA/EIA-492CAAB, IEC 60793-2-50 Type B1.3, ITU-T G.652.D, ISO/IEC 11801 Ed.2.2
-----------------	--

Environmental Conditions

Temperature range, installation	-5 °C to 50 °C
Temperature range, operation	-20 °C to 60 °C
Temperature range, storage	-25 °C to 70 °C

Cable Design

Cable marking	Metre - Handset - Sine - CORNING - Year -SST (TM) A-DQ(ZN)B2Y 6F E9 CT 3.0
Fibre count	6

SST™ Central Tube Dielectric Armour Outdoor Cable 6F E9 SMF-28e+® ITU G652.D CT 3.0

CORNING

Cable Design

Number of ripcords	1
Buffer tube colour coding, layer 1	Yellow
Outer jacket colour	Black
Outer jacket material	Linear Low Density Polyethylene (LLDPE)
Outer jacket nominal thickness	1.2 mm
Tensile strength elements and/or armouring - Layer 1	Laminated swelling glass yarn armour
Buffer tube diameter	3 mm
Fibres per tube	6
Colour Code Standards	Telcordia

Mechanical Specifications

Crush resistance	1500 N/10 cm
Max. tensile strength for installation	1000 N
Min. bend radius installation	130 mm
Min. bend radius operation	100 mm
Nominal outer diameter	6.4 mm

Optical Characteristics

Cable cutoff wavelength	1260 nm
Fibre code	E
Fibre name	E9/125 SMF28e+®
Fibre Type	Single-mode
Performance option code	22
Fibre core diameter	8.2 µm
Maximum Attenuation	0.36 dB/km / 0.36 dB/km / 0.22 dB/km
Serial 1 gigabit ethernet	5000 MHz*km / - / -
Serial 10 gigabit ethernet	10000 MHz*km / - / 40000 MHz*km
Wavelengths	1310 nm / 1383 nm / 1550 nm

SST™ Central Tube Dielectric Armour Outdoor
Cable 6F E9 SMF-28e+® ITU G652.D CT 3.0



Optical Characteristics	
Fibre category	OS2

Dimensions	
Cable Weight	34 kg/km
Max. cable length per reel/drum	6000 m



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
+00 800 2675 4641 • FAX: • www.corning.com/opcomm/emea