


Grade 2 Cylindrical Leverset



Heavy-duty commercial leverset designed for moderate to heavy traffic interior doors.

- Meets ANSI A156.2 Grade 2 Standards
- Designed for ADA Barrier Free Applications
- Schlage “C” and SFIC Prep
- 8 Functions and 3 Finishes
- 2 Lever Designs – Clutched and Rigid Mechanism

SPECIFICATIONS

Certifications	ANSI A156.2 Grade 2, UL Listed 3 Hour Fire, ADA Compliant
Finishes	Satin Chrome (626), Oil Rubbed Bronze (613), Bright Brass (605)
Lever Designs	S-Lever (Straight), N-Lever (Curved) Clutched and Rigid Mechanism
Keyways	SCHL-C, SFIC Prep
Backset	Standard - 2-3/4" Optional - 2-3/8", 3-3/4" & 5"
Strike	ANSI - 1-1/4" x 4-7/8" – Optional - T-Strike
Door Thickness	1-3/8" to 2"

MECHANICAL FUNCTIONS

L2170	Dummy
L210	Passage
L225	Exit (Single Sided)
L240	Privacy
L250	Entry - Push Button
L253	Entry – Push / Turn
L270	Classroom
L280	Storeroom

Warranty - Lifetime Mechanical / 5 Year Finish

General Lock is not responsible for any errors or omissions in specifications and content and does not warrant the same. Specifications are subject to change without notice. Products may not appear as shown.