

Everon® Copper Datacom Class EA Patch Cord, 2xRJ45, Cat.6A, S/FTP LSZH AWG 26 white, 1 m

CORNING

Part Number:
CCAAGB-G9002-A010-C0

The application-neutral Everon® Copper Datacom category 6A patch cords have four individual foil-shielded pairs (PiMF) and an additional braid shield (S/FTP). They are assembled with a shielded RJ45 connectors on each end. The zero halogen patch cords (LSZH) are non-corrosive according to IEC 60754-2 (FRNC), low smoke according to IEC 61034 and flame retardant according to IEC 60332-1. Everon Copper Datacom CCAAGB patch cords provide additional latch protection. They are available in various lengths and colours.

Features and Benefits

Application-neutral due to using all four pairs of RJ45 connectors

Minimum surface transfer impedance of cable (<10 mΩ/m at 10 MHz)

Outstanding transmission characteristics according to 10GBase-T

Additional latch protection

Category 6A

PVP Certificate

Supports Power over Ethernet (PoE / PoE+ / PoE++).
IEEE 802.3bt-2018 performance (4PPoE)
Ready for new applications powered on 4 pairs up to 90W



Everon® Copper Datacom Class EA Patch Cord, 2xRJ45, Cat.6A, S/FTP LSZH™ AWG 26, white, 1 m

Everon® Copper Datacom Class EA Patch Cord, 2xRJ45, Cat.6A, S/FTP LSZH AWG 26 white, 1 m

CORNING

Specifications

General Specifications

Area/range of application	1000Base-T; 2,5GBase-T; 5GBase-T; 10GBase-T/FDDI; ATM
Cable assembly type	Patch cords
Environment	Indoor
Category	6A
Cable type	S/FTP
Halogen-free	Yes
Brand	Everon®
Third Party Certificate	Yes (www.corning.com/emea/en/certificates)

Standards

Flame retardance	Flame retardant according to IEC 60332-1-2 (single cable)
RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Design And Test Criteria	Compliant with PoE / PoE++ IEEE 802.3af, IEEE 802.3at and IEEE 802.3bt
Halogen content test	Low Smoke to IEC 61034
Level of corrosion	Non-corrosive according to IEC 60754-2

Environmental Conditions

Temperature range, installation	0 °C to 50 °C
Temperature range, operation	-20 °C to 60 °C
Transport and indoor storage	Dry environment, no direct sunlight, room temperature ≤ 40 °C

Cable Design

Conductor insulation	Halogen-free foam-skin material
Twisting	2 cores to a pair
Pair screen	Al-laminated foil around each pair

Everon® Copper Datacom Class EA Patch Cord, 2xRJ45, Cat.6A, S/FTP LSZH AWG 26 white, 1 m

CORNING

Cable Design

Overall screen	Copper braid, tinned
Outer jacket material	LSZH/FRNC
Outer jacket colour	White

Mechanical Specifications

Fire load	0.43 MJ/m
Min. bend radius installation	47 mm

Specifications - Connector A

Connector type	RJ45 - 8/8
Durability Cycles	750 N/A
Connector Material	Pin gold plated 50µ inch

Specifications - Connector B

Connector type	RJ45 - 8/8
Durability Cycles	750 N/A
Connector Material	Pin gold plated 50µ inch

Electrical Specifications

Mutual capacity	1600 pF/km
Max. loop resistance	290 Ω/km
Propagation delay	≥ 10 MHz at 4.3 ns/m
DC resistance unbalance	4.3 %
Insulation resistance	5000 MΩ*km
Impedance Zo at 1-100 MHz	100 Ω ± 5% at 100 MHz

Everon® Copper Datacom Class EA Patch Cord,
2xRJ45, Cat.6A, S/FTP LSZH AWG 26 white, 1 m



Dimensions	
Weight	6 kg

Ordering Information	
Product Number	CCAAGB-G9002-A010-C0
EAN Code	4042673367475
Packaging method	Corn Starch Bag
Shipping weight	0.07 kg
Units per delivery	1/1



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
+00 800 2675 4641 • FAX: • www.corning.com/opcomm/emea