

Everon® Copper Datacom U/UTP 450/24, Category 6, LSZH/FRNC, Dca 4P, Green

CORNING

Part Number: DE010024342

The Everon® Copper Datacom U/UTP 450/24 cable is designed up to 450MHz and its transmission characteristics exceed Category 6 specifications according to EN50288-6-1 IEC 61156-5. High system margins for the complete link according to the last version of ISO/IEC 11801 and EN 50173 (Series) will be achieved by using corresponding hardware together with this highend copper cable. The cable has a streamlined construction and low weight. Unshielded cable (U/UTP).

Features and Benefits

U/UTP 450/24 cable designed up to 450 MHz

Fulfils all requirements of category 6 EN50288-6-1 and IEC 61156-5

Suitable for Classe D to E according to ISO/IEC 11801. EN50173 and 10 Gigabit Ethernet according to IEEE 802.3an

Tested and approved for Power over Ethernet applications (PoE/PoE+/4PPoE) according to IEEE 802.3af, IEEE 802.3at and IEEE 802.3bt up to 90W


Certified by a vendor-independent and impartial test lab

Low smoke and halogen-free (LSZH)

Unshielded cable (U/UTP)

Length marking on jacket

Dca, s2, d2, a1



Everon® Copper Datacom U/UTP 450/24, Category 6, LSZH/FRNC, Dca, 4P, Green

Everon® Copper Datacom U/UTP 450/24, Category 6, LSZH/FRNC, Dca 4P, Green

CORNING

Specifications

General Specifications

Environment	Indoor
Category	6
Cable type	U/UTP
Halogen-free	Yes
Construction	Simplex, 4P
Reaction to fire	Dca, s2, d2, a1
Legacy Part Number	VOL6UL4305
Brand	Everon®

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Approvals and Listings	IEC 61156-5; EN 50288-6-1, ISO/IEC 11801 Ed. 2.2; EN 50173-1, ANSI/TIA-568-C-2; IEC 60304
Design And Test Criteria	1000 Base-T IEEE 802.3 an; PoE / PoE++ IEEE 802.3af, IEEE 802.3at
Flame propagation test	IEC 60332-1
Smoke density	IEC 61034-2
Halogen content test	Zero Halogen to IEC 60754-1

Environmental Conditions

Temperature range, installation	0 °C to 50 °C
Temperature range, operation	-20 °C to 60 °C

Cable Design

Conductor	Copper Wire, AWG 24/1
Conductor insulation	Halogen-free foam-skin material
Twisting	2 cores to a pair

Everon® Copper Datacom U/UTP 450/24, Category 6, LSZH/FRNC, Dca 4P, Green

CORNING

Cable Design

Outer jacket material	LSZH/FRNC
Outer jacket colour	Green

Mechanical Characteristics

Fire load	553 MJ/km
Nominal outer diameter	5.4 mm
Min. bend radius installation	8x Cable-Ø
Maximum tensile strength	100 N

Electrical Characteristics

Conductor resistance unbalance	2 %
Delay skew	40 ns/100 m
Max. loop resistance	190 Ω/km
Propagation delay	520 ns/100 m
Voltage rating	Less than 75 V DC max and less than 50 V ACC max
Propagation velocity at >10 MHz (NVP*c)	67 %
Coupling attenuation	40 dB
Insulation Resistance	> 5000 MΩ*km

Dimensions

Weight	324 kg
--------	--------

Ordering Information

Product Number	DE010024342
Cable length	305 m
Packaging method	Reelelex Box
Units per delivery	1/1

Everon® Copper Datacom U/UTP 450/24, Category 6, LSZH/FRNC, Dca 4P, Green

CORNING

Electrical Characteristics								
Frequency [MHz]	4	10	20	63	100	250	300	450
Attenuation according to Standard [db/100m]	3.83	6.0	8.53	15.48	19.92	33.02		46.22
Typical attenuation [db/100m]	3.6	5.7	8.3	14.8	19.0	31.0	34.0	43.0
NEXT according to Standard [db/100m]	66.27	60.3	55.78	48.36	45.3	39.33		35.5
Typical NEXT Values [db/100m]	71.0	65.0	61.0	53.0	50.0	44.0	43.0	40.0
ACR-N according to Standard [db/100m]	55.96	48.0	41.98	32.08	28.0	20.04		14.94
Typical ACR-N Values [db/100m]	67.5	59.3	52.7	38.2	31.0	13.0	9.0	



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
+00 800 2675 4641 • FAX: • www.corning.com/opcomm/emea