

Everon® LAN1 Fibre Housing Front panel loaded with pigtails, LC UPC Duplex, 96 Fibres, 1U, SMF-28® Ultra fibre, stackable splice bridge, black

CORNING

Part Number:
LAN1-96AE-BRDG-B

The LANscape® housing family was designed for various applications in 19-racks and main distribution frames. The fixed or sliding housings can be equipped with industry common adapter types in different fibre categories and are suitable for direct field termination, fusion splicing with pigtails as well as preterminated solutions. The four back openings accommodate cable glands. Additional brackets for cable strain relief for FTTH/FTTO applications or U-Clips for Plug & Play™ and EDGE™ trunks can be mounted at the backside.

The space-optimized interior makes it easy to work with ongoing moves, adds and changes (MACs), thus reducing the risk of network disruptions.

Features and Benefits

Easy to remove top cover

No tools needed

Housing made of aluminium

Lightweight, but robust

Quick-mount feature

Allows single-person mounting of housing

Accomodate different termination methods


Pigtail splicing, field connectorisation, preterminated cables, Plug&Play™ or EDGE™ trunks can be installed in the same housing

Low installation depth

Mountable in shallow cabinets or racks

Multiple labelling options

Port numbering above and below adapter modules or customised labels



Everon® LAN1 Fibre Housing Front panel loaded with pigtails, LC UPC Duplex, 96 Fibres, 1U, SMF-28® Ultra fibre, stackable splice bridge, black

CORNING

Specifications

General Specifications

Fibre category	SMF-28® Ultra fibre
Access type	Front, top, rear
Lockable	No
Mounting Type	Rack 19"

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Environmental Conditions

Temperature range, installation	-10 °C to 60 °C
Temperature range, operation	-10 °C to 60 °C
Temperature range, storage	-10 °C to 60 °C

Design

Fibre count	96
Splice tray type	No Splice Trays
Housing material	Aluminum
Additional cable number reached w/accessories	4
Max. cable number in basic unit w/accessories	4
Cable entry type	Prepunched circular
Number of pigtails	96
Number of splice trays	0
Pigtail length	2 m
Adapter colour front	Blue
Splice protectors type	Heat shrink
Number of adapters	48

**Everon® LAN1 Fibre Housing Front panel loaded
with pigtails, LC UPC Duplex, 96 Fibres, 1U,
SMF-28® Ultra fibre, stackable splice bridge, black**

CORNING

Design

Number of splice protectors	0
Total Splice Capacity	96 universal splices

Design - Adapter

Adapter housing colour	Black
Keyed adapter	No
Shuttered adapter	Yes
Adapter type	LC UPC Duplex Shuttered

Specifications - Connector A

Connector type	LC UPC
Polish	UPC
Insertion loss, max.	0.25 dB

Specifications - Connector B

Polish	UPC
--------	-----

Dimensions

Height	44 mm
Width	483 mm
Depth	233 mm

Shipping Dimensions

Height	44 mm
Width	483 mm
Depth	233 mm

**Everon® LAN1 Fibre Housing Front panel loaded
with pigtails, LC UPC Duplex, 96 Fibres, 1U,
SMF-28® Ultra fibre, stackable splice bridge, black**

CORNING

Ordering Information

Product Number	LAN1-96AE-BRDG-B
Package contents	"LANscape Fiber Housing with adapters, stackable splice organizers for heat-shrink splice protectors including colored pigtails, 1x M20 cable gland and basic accessories"
Height Unit	1 U
Units per delivery	1/1
Shipping Height	55 mm
Shipping Width	532 mm
Shipping Depth	350 mm



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
+00 800 2675 4641 • FAX: • www.corning.com/opcomm/emea