

AXIS P1378 Network Camera

Excellent details in 4K under any circumstances

AXIS P1378 captures excellent detailed images in 4K resolution. Featuring Axis Lightfinder and Axis Forensic WDR it delivers true colors and great details in challenging light or near darkness. It offers P-Iris for images with better contrast, clarity, resolution and depth of field. Designed to act as a deterrent, it includes electronic image stabilization for stable images as well as enhanced security features, barrel distortion correction, shock detection and scene profiles. Axis Zipstream supporting H.264/H.265 provides exceptional savings on bandwidth and storage. Plus, with CS mount and support for motorized i-CS, you can easily change lens to meet your requirements.

- > **4K resolution**
- > **Lightfinder and Forensic WDR**
- > **Signed firmware and secure boot**
- > **Electronic image stabilization**
- > **Zipstream supporting H.264 and H.265**



AXIS P1378 Network Camera

Camera		Defogging Wide dynamic range
Image sensor	1/1.8" progressive scan RGB CMOS	
Lens	IR corrected, CS-mount lens, P-Iris Varifocal 3.9–10 mm, F1.5 Horizontal field of view: 119°–45° Vertical field of view: 62°–25°	Event triggers Analytics, shock detection, edge storage events, supervised external input, audio level, time scheduled MQTT subscribe
Day and night	Automatically removable infrared-cut filter	Event actions MQTT publish Record video: SD card and network share Upload of images or video clips: FTP, SFTP, HTTP, HTTPS, network share and email Pre- and post-alarm video or image buffering for recording or upload Notification: email, HTTP, HTTPS, TCP and SNMP trap PTZ: PTZ preset, start/stop guard tour Overlay text, external output activation, play audio clip, WDR mode, day/night mode
Minimum illumination	4K 25/30 fps with Forensic WDR and Lightfinder: Color: 0.15 lux, at 50 IRE F1.5 B/W: 0.03 lux, at 50 IRE F1.5	Data streaming Event data
Shutter speed	1/8500 s to 1/5 s	Built-in installation aids Focus assistant, pixel counter, remote back focus, autorotation, remote focus and zoom and with optional i-CS lens.
System on chip (SoC)		Analytics
Model	ARTPEC-7	AXIS Object Analytics Object classes: humans, vehicles Features: line crossing, object in area, crossline counting ^{BETA} , time in area ^{BETA} Up to 10 scenarios Metadata visualized with trajectories, color-coded bounding boxes and tables Polygon include/exclude areas Perspective configuration ONVIF Motion Alarm event
Memory	2 GB RAM, 512 MB Flash	Applications Included AXIS Object Analytics AXIS Video Motion Detection, AXIS Motion Guard, AXIS Fence Guard, AXIS Loitering Guard, active tampering alarm, audio detection Supported AXIS Live Privacy Shield Support for additional applications if the device is used with compatible accessories. For more information, contact your Axis partner. Support for AXIS Camera Application Platform enabling installation of third-party applications, see axis.com/acap
Compute capabilities	Machine learning processing unit (MLPU)	Cybersecurity
Video		Edge security Software: Signed firmware, brute force delay protection, digest authentication, password protection, AES-XTS-Plain64 256bit SD card encryption Hardware: Secure boot
Video compression	H.264 (MPEG-4 Part 10/AVC) Baseline, Main and High Profiles H.265 (MPEG-H Part 2/HEVC) Motion JPEG	Network security IEEE 802.1X (EAP-TLS) ^a , HTTPS/HSTS ^a , TLS v1.2/v1.3 ^a , Network Time Security (NTS), X.509 Certificate PKI, IP address filtering
Resolution	3840x2160 (4K) to 160x90	Documentation <i>AXIS OS Hardening Guide</i> <i>Axis Vulnerability Management Policy</i> <i>Axis Security Development Model</i> AXIS OS Software Bill of Material (SBOM) To download documents, go to axis.com/support/cybersecurity/resources To read more about Axis cybersecurity support, go to axis.com/cybersecurity
Frame rate	25/30 fps (50/60 Hz) in all resolutions	General
Video streaming	Multiple, individually configurable streams in H.264, H.265, and Motion JPEG Axis Zipstream technology in H.264 and H.265 Controllable frame rate and bandwidth VBR/ABR/MBR H.264/H.265 Low latency mode Video streaming indicator	Casing Metal (zinc) Color lid: White NCS S 1002-B Color chassis: Black NCS S 9002-N
Multi-view streaming	Up to 8 individually cropped out view areas	Mounting ¼"-20 tripod screw thread Camera stand included
Image settings	Saturation, contrast, brightness, sharpness, Forensic WDR: Up to 120 dB depending on scene, white balance, day/night threshold, exposure mode, exposure zones, local contrast, tone mapping, compression, orientation: auto, 0°, 90°, 180°, 270° including Corridor Format, mirroring of images, dynamic text and image overlay, privacy masks, defogging, electronic image stabilization, barrel distortion correction, scene profiles: forensic, vivid, traffic overview	Sustainability Free of hazardous brominated and chlorinated flame retardants (BFR/CFR free)
Pan/Tilt/Zoom	Digital PTZ Uploadable PTZ driver (Pelco D pre-installed)	Power 12–28 V DC, max 10.5 W, typical 6.1 W Power over Ethernet (PoE) IEEE 802.3af/802.3at Type 1 Class 3, max 10.7 W, typical 6.2 W Power redundancy
Audio		Connectors RJ45 10BASE-T/100BASE-TX/1000BASE-T I/O: 6-pin 2.5 mm terminal block, for 2 supervised alarm inputs and 2 outputs RS485/RS422, 2 pcs, 2 pos, full duplex, terminal block
Audio streaming	Two-way, full duplex	
Audio encoding	AAC LC 8/16/32/48 kHz, G.711 PCM 8 kHz, G.726 ADPCM 8 kHz, Opus 8/16/48 kHz, LPCM 48 kHz Configurable bit rate	
Audio input/output	External microphone input, line input, digital input with ring power, line output, built-in microphone (can be disabled), automatic gain control	
Network		
Security	IP address filtering, HTTPS ^a encryption, IEEE 802.1X (EAP-TLS) ^a network access control, user access log, centralized certificate management	
Network protocols	IPv4, IPv6 USGv6, ICMPv4/ICMPv6, HTTP, HTTPS ^a , HTTP/2, TLS ^a , QoS Layer 3 DiffServ, FTP, CIFS/SMB, SMTP, mDNS (Bonjour), UPnP™, SNMP v1/v2c/v3 (MIB-II), DNS/DNSv6, DDNS, NTP, NTS, RTSP, RTP, SRTP/RTSPS, SFTP, TCP, UDP, IGMPv1/v2/v3, RTCP, ICMP, DHCPv4/v6, ARP, SSH, LLDP, CDP, MQTT v3.1.1, Secure syslog (RFC 3164/5424, UDP/TCP/TLS), Link-Local address (ZeroConf)	
System integration		
Application Programming Interface	Open API for software integration, including VAPIX® and AXIS Camera Application Platform, specifications at axis.com One-Click Cloud Connection ONVIF® Profile G, ONVIF® Profile M, ONVIF® Profile S, and ONVIF® Profile T, specification at onvif.org	
Onscreen controls	Electronic image stabilization Day/night shift	

	DC input, terminal block, 3.5 mm mic/line in, 3.5 mm line out i-CS connector (compatible with P-Iris and DC-iris) Security lock slot AXIS T92G20 connector
Storage	Support for microSD/microSDHC/microSDXC card Support for SD card encryption (AES-XTS-Plain64 256bit) Support for recording to network-attached storage (NAS) For SD card and NAS recommendations see axis.com
Operating conditions	-10 °C to 55 °C (14 °F to 131 °F) Humidity 10-85% RH (non-condensing)
Storage conditions	-40 °C to 65 °C (-40 °F to 149 °F) Humidity 5-95% RH (non-condensing)
Approvals	EMC EN 55032 Class A, EN 61000-3-2, EN 61000-3-3, EN 55024, EN 61000-6-1, EN 61000-6-2, FCC Part 15 Subpart B Class A, ICES-003 Class A, VCCI Class A, RCM AS/NZS CISPR 32 Class A, KCC KN32 Class A, KN35 Safety IEC/EN/UL 62368-1, CAN/CSA C22.2 No. 62368-1, IS 13252 Environment IEC 60068-2-1, IEC 60068-2-2, IEC 60068-2-6, IEC 60068-2-14, IEC 60068-2-27, IEC 60068-2-78 Network NIST SP500-267

Dimensions	214 x 80 x 57 mm (8 7/16 x 3 1/8 x 2 1/4 in)
Weight	750 g (1.7 lb)
Included accessories	Connector kit, Installation Guide, Windows® decoder 1-user license, stand, Resistorx® L-key TR20, Torx® L-key T6
Optional lenses	Lens CS 4-10 mm F0.9 P-Iris Lens i-CS 3.9-10 mm F1.5 8 MP Lens i-CS 9-50 mm F1.5 8 MP
Optional accessories	Axis mounts, Axis lenses, Axis midspans, Axis microphones AXIS TQ1809-LE Housing T92G AXIS T8355 Digital Microphone For more accessories, see axis.com
Video management software	AXIS Companion, AXIS Camera Station, video management software from Axis' Application Development Partners available at axis.com/vms
Languages	English, German, French, Spanish, Italian, Russian, Simplified Chinese, Japanese, Korean, Portuguese, Traditional Chinese, Dutch, Czech, Swedish, Finnish, Turkish, Thai, Vietnamese, Polish
Warranty	5-year warranty, see axis.com/warranty

- a. *This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit (<http://www.openssl.org/>), and cryptographic software written by Eric Young (eyay@cryptsoft.com).*