

LANMARK-6 UTP Plenum Rated Cable

APPLICATION

The LANMARK-6 features a reduced diameter compared to other Category 6UTP cables. This is an ETL Category 6 verified cable, constructed without the center spline for easy installation and termination. LANMARK-6 is capable of transmitting applications such as 1000BASE-T. It is ideal for network applications that extend to 250 MHz. LANMARK-6 is available in both CMP and CMR and conforms to ANSI/TIA-568.2-D Category 6 and ISO/IEC 11801 2nd Edition Class E Category 6 requirements.



BENEFITS

- May be installed in air-handling ducts and plenums without conduit in accordance with the National Electrical Code (NFPA 70) and the National Building Code of Canada
- Provides Category 6 performance
- Cost effective Category 6 solution
- Provides additional usable bandwidth required for future applications
- Superior box design allows cable to be pulled easily from the box with minimum kinking
- Compact box design takes up less shelf space
- Max bundle size for 100 W PoE is 240 cables
- Clearly identified packaging eliminates potential confusion
- Unique ID in print legend allows cable to be traced without additional equipment

FEATURES

- Cost effective, compact design
- Characterized to 500 MHz, 250 MHz greater than the standard
- Jacketed with flame-retardant polymer
- Third-party verified Cat 6 performance

STANDARDS & REGULATIONS

- ANSI/TIA 568.2-D
- ISO/IEC 11801
- IEEE 802.3 PoE Type 1, 2, 3, 4 (100 watts max)
- Cisco UPOE, UPOE+ (90 watts max)
- Power over HDBaseT™ PoH (95 watts max)
- UL 444
- RoHS Compliant (EU Directive 2011/65/EU (RoHS))

FIRE RATING

- Plenum - NFPA 262
- CMP - Plenum Rated

COUNTRY OF ORIGIN

USA

WARRANTY INFORMATION

For Leviton product warranties, go to leviton.com/ns/warranty

PRODUCT SPECIFICATIONS
LANMARK™-6 UTP Plenum Rated Cable

TECHNICAL SPECIFICATIONS

Electrical properties (20 °C ± 5 °C)

DC resistance	Max. 9.38 Ω/100 m
DC resistance unbalance	Max. 5%
Mutual capacitance	Nom. 5.3 nf/100 m at 1 kHz
Capacitance unbalance (pair-to-ground)	Max. 330 pf/100 m at 1 kHz
Nominal velocity of propagation	65%
Delay skew	45 ns/100 m max.

HIGH SPEED DATA AND POWER APPLICATIONS

IEEE 802.3	2.5/5GBASE-T (2.5/5 Gb/s), 1000BASE-T (1 Gb/s), 100BASE-TX (100 Mb/s), 10BASE-T (10 Mb/s)
IEEE 802.3bt	PoE Types 1, 2, 3, and 4

TECHNICAL DATA - PHYSICAL

Conductor	24 AWG bare copper	
Conductor diameter - in. (mm)	0.022	(0.56)
Max insulated conductor diameter - in. (mm)	0.040	(1.02)
Nom. cable weight - lb./kft (kg/km)	27	(40.2)
Nom. cable diameter - in. (mm)	0.230	(5.84)

CHARACTERISTICS

Dimensional Characteristics

Length per reel	1000 ft (305 m)
Number of pairs	4

Usage Characteristics

Field of application	Indoor
Category	Cat 6 Indoor
Type of cable	UTP
Temperature (Installation):	+10 °C to +50 °C (+50 °F to +122 °F)
Temperature (Operating):	-20 °C to +60 °C (-4 °F to +140 °F)
Temperature (Storage):	-20 °C to +60 °C (-4 °F to +140 °F)
Listed temperature	+75 °C (+167 °F)

COLOR CODE

Pair-1	White	Blue
Pair-2	White	Orange
Pair-3	White	Green
Pair-4	White	Brown

PRODUCT SPECIFICATIONS
LANMARK™-6 UTP Plenum Rated Cable



LANMARK-6 UTP Plenum Rated Cable

GUARANTEED PRODUCT PERFORMANCE TRANSMISSION CHARACTERISTICS

Freq. MHz	RL (dB)		NEXT (dB)		PS NEXT (dB)		ACR* (dB/100 m)		PSACR* (dB/100 m)	
	TIA Spec	Product Guarantee	TIA Spec	Product Guarantee	TIA Spec	Product Guarantee	TIA Spec	Product Guarantee	TIA Spec	Product Guarantee
1	20.0	20.0	74.3	74.3	72.3	72.3	72.3	72.3	70.3	70.3
4	23.0	23.0	65.3	65.3	63.3	63.3	61.5	61.5	59.5	59.5
10	25.0	25.0	59.3	59.3	57.3	57.3	53.3	53.3	51.3	51.3
16	25.0	25.0	56.2	56.2	54.2	54.2	48.7	48.7	46.7	46.7
20	25.0	25.0	54.8	54.8	52.8	52.8	46.3	46.3	44.3	44.3
31.25	23.6	23.6	51.9	51.9	49.9	49.9	41.2	41.2	39.2	39.2
62.5	21.5	21.5	47.4	47.4	45.4	45.4	32.0	32.0	30.0	30.0
100	20.1	20.1	44.3	44.3	42.3	42.3	24.5	24.5	22.5	22.5
150	18.9	18.9	41.7	41.7	39.7	39.7	16.9	16.9	14.9	14.9
200	18.0	18.0	39.8	39.8	37.8	37.8	10.8	10.8	8.8	8.8
250	17.3	17.3	38.3	38.3	36.3	36.3	5.5	5.5	3.5	3.5
300**	—	16.8	—	37.1	—	35.1	—	0.7	—	-1.3
350**	—	16.3	—	36.1	—	34.1	—	-3.6	—	-5.6
400**	—	15.9	—	35.3	—	33.3	—	-7.7	—	-9.7
450**	—	15.5	—	34.5	—	32.5	—	-11.5	—	-13.5
500**	—	15.2	—	33.8	—	31.8	—	-15.1	—	-17.1

*ACR and PSACR are provided for calculation only; they are not guaranteed for LANMARK-6

**LANMARK-6 is guaranteed between 1 MHz and 250 MHz; values above 250 MHz are for reference only and not a part of the product guarantee.

GUARANTEED PRODUCT PERFORMANCE TRANSMISSION CHARACTERISTICS, CONTINUED

Freq. MHz	IL (dB/100 m)		ACRF (dB/100 m)		PSACRF (dB/100 m)		LCL/TCL (dB)	EL TCTL (dB)
	TIA Spec	Product Guarantee	TIA Spec	Product Guarantee	TIA Spec	Product Guarantee	Product Guarantee	Product Guarantee
1	2.0	2.0	67.8	67.8	64.8	64.8	40.0	35.0
4	3.8	3.8	55.8	55.8	52.8	52.8	40.0	23.0
10	6.0	6.0	47.8	47.8	44.8	44.8	40.0	15.0
16	7.6	7.6	43.7	43.7	40.7	40.7	38.0	10.9
20	8.5	8.5	41.8	41.8	38.8	38.8	37.0	9.0
31.25	10.7	10.7	37.9	37.9	34.9	34.9	35.1	—
62.5	15.4	15.4	31.9	31.9	28.9	28.9	32.0	—
100	19.8	19.8	27.8	27.8	24.8	24.8	30.0	—
150	24.7	24.5	24.3	24.3	21.3	21.3	28.2	—
200	29.0	28.8	21.8	21.8	18.8	18.7	27.0	—
250	32.8	32.8	19.8	19.8	16.8	16.8	26.0	—
300*	—	36.4	—	18.3	—	15.3	25.2	—
350*	—	39.8	—	16.9	—	13.9	24.6	—
400*	—	43.0	—	15.8	—	12.8	24.0	—
450*	—	46.0	—	14.7	—	11.7	23.5	—
500*	—	48.9	—	13.8	—	10.8	23.0	—

*LANMARK-6 is guaranteed between 1 MHz and 250 MHz; values above 250 MHz are for reference only and not a part of the product guarantee.

PRODUCT SPECIFICATIONS
LANMARK™-6 UTP Plenum Rated Cable



LANMARK-6 UTP Plenum Rated Cable

PART NUMBERS				
Description	Color	Packaging	Length (Ft.)	Part No.
LANMARK-6 UTP Plenum	White	Box	1000	10136230
LANMARK-6 UTP Plenum	Blue	Box	1000	10136226
LANMARK-6 UTP Plenum	Dark gray	Box	1000	11091258
LANMARK-6 UTP Plenum	Yellow	Box	1000	10136749
LANMARK-6 UTP Plenum	Green	Box	1000	10136748
LANMARK-6 UTP Plenum	Pink	Box	1000	11049196
LANMARK-6 UTP Plenum	Red	Box	1000	10137365
LANMARK-6 UTP Plenum	Black	Box	1000	10188830
LANMARK-6 UTP Plenum	Violet	Box	1000	10137364
LANMARK-6 UTP Plenum	Orange	Box	1000	10141073
LANMARK-6 UTP Plenum	Brown	Box	1000	11060822
LANMARK-6 UTP Plenum	White	Reel	1000	10136265
LANMARK-6 UTP Plenum	Blue	Reel	1000	10136233
LANMARK-6 UTP Plenum	Dark gray	Reel	1000	11091284
LANMARK-6 UTP Plenum	Yellow	Reel	1000	10136751
LANMARK-6 UTP Plenum	Green	Reel	1000	10136750
LANMARK-6 UTP Plenum 1500 ft. SMARTPAK™	White	Box	1500	11074742
LANMARK-6 UTP Plenum 1500 ft. SMARTPAK	Blue	Box	1500	11074702
LANMARK-6 UTP Plenum 1500 ft. SMARTPAK	Dark gray	Box	1500	11094952
LANMARK-6 UTP Plenum 1500 ft. SMARTPAK	Yellow	Box	1500	11074893
LANMARK-6 UTP Plenum 1500 ft. SMARTPAK	Green	Box	1500	11074897

PRINT LEGEND:

BERK-TEK LANMARK-6 24AWG CMP 75C C(ETL)US ETL VERIFIED TIA-568.2-D CAT 6 [DATE] [COUNTER] [UID]

For further support information, visit leviton.com/ns/support

Page 4 of 4

USA
 Network Solutions Headquarters
 +1 (800) 722 2082
infoUSA@leviton.com
 Leviton Cable (formerly Berk-Tek)
 +1 (800) 237 5835 | infoUSA@leviton.com

Asia Pacific
 +852 3620 2602
infoAPAC@leviton.com

Canada
 +1 (800) 461 2002
infoCanada@leviton.com

Europe
 +44 (0) 1592 772124
infoEurope@leviton.com

Latin America
 MX: +52 (55) 2128 6286
 LATAM: +52 (55) 2333 5963
infoLATAM@leviton.com

Middle East & Africa
 +971 (4) 247 9800
infoMEA@leviton.com

NETWORK SOLUTIONS PRODUCTS ARE AVAILABLE WORLDWIDE IN OVER 100 COUNTRIES. VISIT US ONLINE AT LEVITON.COM/NS TO LEARN MORE.