

TECHNICAL SPECIFICATIONS

Uninterruptible Power Supply

1440 VA Line-Interactive UPS

LUPS-LI1500T

Designed to protect security cameras, DVRs, desktop computers, network equipment, VoIP communications, telephone systems, external computer accessories, and more against spikes, surges and blackouts.

OVERVIEW:

The Liberty LUPS-LI1500T is a line-interactive VRLA UPS providing 1440 VA of backup power to protect small to medium-load electronics from damage. It's a compact mini tower unit with battery support, spike and surge protection, load-shedding outlets, built-in self-diagnostics, free management/monitoring software, and more.



1440 VA Line-Interactive Mini Tower UPS


FEATURES:

- 2.5-minute runtime (full load)
- 11-minute runtime (half load)
- LCD front panel display
- Tool-less hot-swappable battery replacement
- 3-year warranty for electronic components
- 2-year warranty for battery

COMES WITH:

- 10 total outlets (NEMA 5-15R)
- 5 surge only (non-critical equipment)
- 5 surge and battery with 2 load shedding outlets (critical equipment)
- 2 USB communication/charging ports (1-Type A / 1-Type B)
- Coax surge protection port
- RJ45 ethernet surge protection port (1 Gbit)
- 6' NEMA 5-15P power cord with right-angle plug
- Free management and monitoring software

TECHNICAL SPECIFICATIONS | LUPS-LI1500T



BENEFITS:

- Low-cost, high-performance protection for small to medium-load electronics.
- Compact, mini tower form factor integrates seamlessly into cramped spaces.

1440 VA Line-Interactive Mini Tower UPS - Back

LUPS-LI1500T	
Output Power, Topology	1440 VA / 900 Watts, Line-Interactive
Receptacles	(5) 5-15R (Surge Only) / (5) 5-15R (Battery and Surge)
Input (Non-Battery Operation)	
Voltage Range	90 VAC to 140 VAC
Frequency Range	60 Hz \pm 6 Hz
Output (Non-Battery Operation)	
Voltage	120 VAC
Voltage Regulation	120 VAC \pm 5% until low battery warning
Frequency	60 Hz \pm 0.5 Hz unless synchronized to line
Wave Form	Simulated sine wave
Output (Battery Operation)	
Voltage	120 VAC
Voltage Regulation	120 VAC \pm 5% until low battery warning
Frequency	60 Hz \pm 0.5 Hz unless synchronized to line
Wave Form	Simulated sine wave



TECHNICAL SPECIFICATIONS | LUPS-LI1500T

Battery System	
Hot Swappable Battery	Yes
Internal Battery	BM0066
Battery Type	Sealed, non-spillable, maintenance-free, valve
Half Load / Full Load (min.)	11/2.5
Physical and Certifications	
Dimensions	16.1 x 3.9 x 11" (410 x 99 x 280 mm)
Weight	26.4 lb (12 kg)
Agency Approvals	cTUVus (Conforms to UL1778 5th Edition and CSA 222 no. 107.3:2014/R2017-10), FCC Class B Energy Star 2.0
Environmental Compliance	RoHS2, Energy Star 2.0, DoE 10 CFR Part 430 Subpart B Compliant