



Product: [8761NH](#)

Electronic, 2 C #22 Str TC, PE ins, OS, LSZH Jkt, 300V, Dca

### Product Description

Electronic, 2 Conductor 22AWG (7x30) Tinned Copper, PE Insulation, Overall Beldfoil® Shield, LSZH Outer Jacket, CPR Dca

### Technical Specifications

#### Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; computer communication; panel wiring
------------------------	---

#### Construction Details

##### Conductor

Size	Stranding	Material
22	7x30	TC - Tinned Copper

##### Insulation

Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
PE - Polyethylene	0.017 in (0.43 mm)	1.57 mm (0.0618 in)	Black & Clear

##### Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	22 AWG (7x30) TC

##### Outer Jacket

Material	Nom. Thickness	Nom. Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant)	0.9 mm (0.035 in)	4.95 mm (0.195 in)

Overall Cable Diameter (Nominal):	4.95 mm (0.195 in)
-----------------------------------	--------------------

#### Electrical Characteristics

##### Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedance	Nom. Velocity of Prop.	Max. Current
52.5 Ohm/km (16.0 Ohm/1000ft)	78.7 pF/m (24.0 pF/ft)	154.2 pF/m (47.00 pF/ft)	64 Ohm	66%	2.9 Amps per Conductor

#### Mechanical Characteristics

##### Temperature

Operating	Installation	Storage
-45°C To +80°C	-15°C To +80°C	-45°C To +80°C

##### Bend Radius

Installation Min.	49.5 mm (1.95 in)
-------------------	-------------------

Max. Pull Tension:	158 N (35.5 lbf)
Bulk Cable Weight:	15 lbs/1000ft

## Standards and Compliance

Environmental Suitability:	Indoor - Euroclass Dca, Indoor, Non-Halogenated, Sunlight Resistance
Flammability / Reaction to Fire:	IEC 60332-1-2, IEC 60332-3-24
CPR Compliance:	CPR Euroclass: Dca-s2,d1,a1; CPR UKCA Class: Dca-s2,d1,a1
ISO/IEC Compliance:	IEC 61034-2 - Smoke Density Min Transmittance = 60%
CENELEC Compliance:	EN 50290-2-20
European Halogen Free Standards:	IEC 62821-1 Halogen Free Compliance = Yes, IEC 60754-1 - Halogen Amount = Zero, IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity = 2.5 µS/mm, IEC 60754-2 - Halogen Acid Gas Amount - Min. pH = 4.3
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2)
UK Regulation Compliance:	UKCA Mark

## History

Update and Revision:	Revision Number: 0.334 Revision Date: 03-15-2024
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	EAN
8761NH.00305	Chrome	Reel	305 m	8719605019011
8761NH.00500	Chrome	Reel	500 m	8719605019028
8761NH.001000	Chrome	Reel	1,000 m	8719605019004
8761NH.01305	White	Reel	305 m	8719605174611

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.