



Safety Data Sheet

Copyright, 2022, 3M Company All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

Document group:	18-6943-7	Version number:	15.01
Revision date:	27/07/2022	Supersedes date:	25/05/2022

This Safety Data Sheet has been prepared in accordance with the REACH Regulation (EC) 1907/2006 and its modifications.

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

VHB™ Surface Cleaner 8986

Product Identification Numbers

DT-2729-9063-1

7000071716

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses

Industrial use.

1.3. Details of the supplier of the safety data sheet

Address: 3M United Kingdom PLC, 3M Centre, Cain Road, Bracknell, Berkshire, RG12 8HT.
Telephone: +44 (0)1344 858 000
E Mail: tox.uk@mmm.com
Website: www.3M.com/uk

1.4. Emergency telephone number

+44 (0)1344 858 000

SECTION 2: Hazard identification

2.1. Classification of the substance or mixture

CLP REGULATION (EC) No 1272/2008

The health and environmental classifications of this material have been derived using the calculation method, except in cases where test data are available or the physical form impacts classification. Classification(s) based on test data or physical form are noted below, if applicable.

CLASSIFICATION:

VHB™ Surface Cleaner 8986

Flammable Liquid, Category 2 - Flam. Liq. 2; H225
Serious Eye Damage/Eye Irritation, Category 2 - Eye Irrit. 2; H319
Specific Target Organ Toxicity-Single Exposure, Category 3 - STOT SE 3; H336

For full text of H phrases, see Section 16.

2.2. Label elements CLP REGULATION (EC) No 1272/2008

SIGNAL WORD
DANGER.

Symbols
GHS02 (Flame) | GHS07 (Exclamation mark) |

Pictograms



Ingredients:

Ingredient	CAS Nbr	EC No.	% by Wt
propan-2-ol	67-63-0	200-661-7	60 - 90

HAZARD STATEMENTS:

H225 Highly flammable liquid and vapour.
H319 Causes serious eye irritation.
H336 May cause drowsiness or dizziness.

PRECAUTIONARY STATEMENTS

Prevention:

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P261A Avoid breathing vapours.

Response:

P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

Notes on labelling

Updated per Regulation (EC) No. 648/2004 on detergents.

2.3. Other hazards

None known.

This material does not contain any substances that are assessed to be a PBT or vPvB

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Ingredient	Identifier(s)	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
propan-2-ol	(CAS-No.) 67-63-0 (EC-No.) 200-661-7 (REACH-No.) 01-2119457558-25	60 - 90	Flam. Liq. 2, H225 Eye Irrit. 2, H319 STOT SE 3, H336
Non-Hazardous Ingredients	Mixture	10 - 40	Substance not classified as hazardous

Please see section 16 for the full text of any H statements referred to in this section

For information on ingredient occupational exposure limits or PBT or vPvB status, see sections 8 and 12 of this SDS

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation

Remove person to fresh air. If you feel unwell, get medical attention.

Skin contact

Immediately wash with soap and water. Remove contaminated clothing and wash before reuse. If signs/symptoms develop, get medical attention.

Eye contact

Immediately flush with large amounts of water. Remove contact lenses if easy to do. Continue rinsing. Get medical attention.

If swallowed

Rinse mouth. If you feel unwell, get medical attention.

4.2. Most important symptoms and effects, both acute and delayed

No critical symptoms or effects. See Section 11.1, information on toxicological effects.

4.3. Indication of any immediate medical attention and special treatment required

Not applicable

SECTION 5: Fire-fighting measures

5.1. Extinguishing media

In case of fire: Use a fire fighting agent suitable for flammable liquids such as dry chemical or carbon dioxide to extinguish.

5.2. Special hazards arising from the substance or mixture

Closed containers exposed to heat from fire may build pressure and explode.

Hazardous Decomposition or By-Products

Substance

Carbon monoxide
Carbon dioxide.

Condition

During combustion.
During combustion.

5.3. Advice for fire-fighters

Water may not effectively extinguish fire; however, it should be used to keep fire-exposed containers and surfaces cool and prevent explosive rupture. Wear full protective clothing, including helmet, self-contained, positive pressure or pressure

demand breathing apparatus, bunker coat and pants, bands around arms, waist and legs, face mask, and protective covering for exposed areas of the head.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Evacuate area. Keep away from heat/sparks/open flames/hot surfaces. - No smoking. Use only non-sparking tools. Ventilate the area with fresh air. For large spill, or spills in confined spaces, provide mechanical ventilation to disperse or exhaust vapours, in accordance with good industrial hygiene practice. Warning! A motor could be an ignition source and could cause flammable gases or vapours in the spill area to burn or explode. Refer to other sections of this SDS for information regarding physical and health hazards, respiratory protection, ventilation, and personal protective equipment.

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

Contain spill. Cover spill area with a fire extinguishing foam that is resistant to polar solvents. Working from around the edges of the spill inward, cover with bentonite, vermiculite, or commercially available inorganic absorbent material. Mix in sufficient absorbent until it appears dry. Remember, adding an absorbent material does not remove a physical, health, or environmental hazard. Collect as much of the spilled material as possible using non-sparking tools. Place in a metal container approved for transportation by appropriate authorities. Clean up residue with water. Seal the container. Dispose of collected material as soon as possible.

6.4. Reference to other sections

Refer to Section 8 and Section 13 for more information

SECTION 7: Handling and storage

7.1. Precautions for safe handling

For industrial/occupational use only. Not for consumer sale or use. Keep away from heat/sparks/open flames/hot surfaces. - No smoking. Use only non-sparking tools. Take precautionary measures against static discharge. Avoid breathing dust/fume/gas/mist/vapours/spray. Do not get in eyes, on skin, or on clothing. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Avoid release to the environment. Avoid contact with oxidising agents (eg. chlorine, chromic acid etc.) Wear low static or properly grounded shoes. To minimize the risk of ignition, determine applicable electrical classifications for the process using this product and select specific local exhaust ventilation equipment to avoid flammable vapour accumulation. Ground/bond container and receiving equipment if there is potential for static electricity accumulation during transfer. Vapours may travel long distances along the ground or floor to an ignition source and flash back.

7.2. Conditions for safe storage including any incompatibilities

Store in a well-ventilated place. Keep cool. Keep container tightly closed. Store away from heat. Store away from acids. Store away from oxidising agents. Store away from amines.

7.3. Specific end use(s)

See information in Section 7.1 and 7.2 for handling and storage recommendations. See Section 8 for exposure controls and personal protection recommendations.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Occupational exposure limits

If a component is disclosed in section 3 but does not appear in the table below, an occupational exposure limit is not available for the component.

Ingredient	CAS Nbr	Agency	Limit type	Additional comments
------------	---------	--------	------------	---------------------

propan-2-ol 67-63-0 UK HSC TWA:999 mg/m³(400 ppm);STEL:1250 mg/m³(500 ppm)

UK HSC : UK Health and Safety Commission
TWA: Time-Weighted-Average
STEL: Short Term Exposure Limit
CEIL: Ceiling

Biological limit values

No biological limit values exist for any of the components listed in Section 3 of this safety data sheet.

Recommended monitoring procedures:Information on recommended monitoring procedures can be obtained from UK HSC

8.2. Exposure controls

8.2.1. Engineering controls

Use explosion-proof ventilation equipment.

8.2.2. Personal protective equipment (PPE)

Eye/face protection

Select and use eye/face protection to prevent contact based on the results of an exposure assessment. The following eye/face protection(s) are recommended:

Indirect vented goggles.

Applicable Norms/Standards

Use eye protection conforming to EN 166

Skin/hand protection

Select and use gloves and/or protective clothing approved to relevant local standards to prevent skin contact based on the results of an exposure assessment. Selection should be based on use factors such as exposure levels, concentration of the substance or mixture, frequency and duration, physical challenges such as temperature extremes, and other use conditions. Consult with your glove and/or protective clothing manufacturer for selection of appropriate compatible gloves/protective clothing.

Gloves made from the following material(s) are recommended:

Material	Thickness (mm)	Breakthrough Time
Butyl rubber.	0.5	=>8 hours
Fluoroelastomer	0.4	=>8 hours
Nitrile rubber.	0.35	=>8 hours

The glove data presented are based on the substance driving dermal toxicity and the conditions present at the time of testing. Breakthrough time may be altered when the glove is subjected to use conditions that place additional stress on the glove.

Applicable Norms/Standards

Use gloves tested to EN 374

Respiratory protection

An exposure assessment may be needed to decide if a respirator is required. If a respirator is needed, use respirators as part of a full respiratory protection program. Based on the results of the exposure assessment, select from the following respirator type(s) to reduce inhalation exposure:

Half facepiece or full facepiece air-purifying respirator suitable for organic vapours

For questions about suitability for a specific application, consult with your respirator manufacturer.

Applicable Norms/Standards

Use a respirator conforming to EN 140 or EN 136: filter type A

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Physical state	Liquid.
Specific Physical Form:	Low viscosity liquid
Colour	Colourless
Odor	Alcohol
Odour threshold	<i>No data available.</i>
Melting point/freezing point	<i>Not applicable.</i>
Boiling point/boiling range	82.4 °C
Flammability (solid, gas)	Not applicable.
Flammable Limits(LEL)	2 % volume
Flammable Limits(UEL)	12.7 % volume
Flash point	12 °C
Autoignition temperature	425 <i>Not applicable.</i>
Decomposition temperature	<i>No data available.</i>
pH	6.5 - 7.5
Kinematic Viscosity	<i>No data available.</i>
Water solubility	Complete
Solubility- non-water	<i>No data available.</i>
Partition coefficient: n-octanol/water	<i>No data available.</i>
Vapour pressure	4.3 kPa [<i>Ref Std: AIR=1</i>]
Density	0.87 - 0.88 g/cm ³
Relative density	0.871 - 0.882 [<i>Ref Std: WATER=1</i>] <i>No data available.</i>
Relative Vapor Density	2.07 [<i>Ref Std: AIR=1</i>]

9.2. Other information**9.2.2 Other safety characteristics**

EU Volatile Organic Compounds	<i>No data available.</i>
Evaporation rate	<i>No data available.</i>
Molecular weight	<i>No data available.</i>
Percent volatile	100

SECTION 10: Stability and reactivity**10.1 Reactivity**

This material may be reactive with certain agents under certain conditions - see the remaining headings in this section

10.2 Chemical stability

Stable.

10.3 Possibility of hazardous reactions

Hazardous polymerisation will not occur.

10.4 Conditions to avoid

Sparks and/or flames.
Heat.

10.5 Incompatible materials

Strong oxidising agents.
Alkali and alkaline earth metals.
Amines.

10.6 Hazardous decomposition products

<u>Substance</u>	<u>Condition</u>
None known.	

Refer to section 5.2 for hazardous decomposition products during combustion.

SECTION 11: Toxicological information

The information below may not agree with the EU material classification in Section 2 and/or the ingredient classifications in Section 3 if specific ingredient classifications are mandated by a competent authority. In addition, statements and data presented in Section 11 are based on UN GHS calculation rules and classifications derived from internal hazard assessments.

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Signs and Symptoms of Exposure

Based on test data and/or information on the components, this material may produce the following health effects:

Inhalation

Respiratory tract irritation: Signs/symptoms may include cough, sneezing, nasal discharge, headache, hoarseness, and nose and throat pain. May cause additional health effects (see below).

Skin contact

Prolonged or repeated exposure may cause: Dermal Defatting: Signs/symptoms may include localized redness, itching, drying and cracking of skin.

Eye contact

Severe eye irritation: Signs/symptoms may include significant redness, swelling, pain, tearing, cloudy appearance of the cornea, and impaired vision.

Ingestion

Gastrointestinal irritation: Signs/symptoms may include abdominal pain, stomach upset, nausea, vomiting and diarrhoea. May cause additional health effects (see below).

Additional Health Effects:

Single exposure may cause target organ effects:

Central nervous system (CNS) depression: Signs/symptoms may include headache, dizziness, drowsiness, incoordination, nausea, slowed reaction time, slurred speech, giddiness, and unconsciousness.

Toxicological Data

If a component is disclosed in section 3 but does not appear in a table below, either no data are available for that endpoint or the data are not sufficient for classification.

Acute Toxicity

Name	Route	Species	Value
Overall product	Ingestion		No data available; calculated ATE >5,000 mg/kg
propan-2-ol	Dermal	Rabbit	LD50 12,870 mg/kg
propan-2-ol	Inhalation-Vapour (4)	Rat	LC50 72.6 mg/l

VHB™ Surface Cleaner 8986

	hours)		
propan-2-ol	Ingestion	Rat	LD50 4,710 mg/kg

ATE = acute toxicity estimate

Skin Corrosion/Irritation

Name	Species	Value
propan-2-ol	Multiple animal species	No significant irritation

Serious Eye Damage/Irritation

Name	Species	Value
propan-2-ol	Rabbit	Severe irritant

Skin Sensitisation

Name	Species	Value
propan-2-ol	Guinea pig	Not classified

Respiratory Sensitisation

For the component/components, either no data is currently available or the data is not sufficient for classification.

Germ Cell Mutagenicity

Name	Route	Value
propan-2-ol	In Vitro	Not mutagenic
propan-2-ol	In vivo	Not mutagenic

Carcinogenicity

Name	Route	Species	Value
propan-2-ol	Inhalation	Rat	Some positive data exist, but the data are not sufficient for classification

Reproductive Toxicity

Reproductive and/or Developmental Effects

Name	Route	Value	Species	Test result	Exposure Duration
propan-2-ol	Ingestion	Not classified for development	Rat	NOAEL 400 mg/kg/day	during organogenesis
propan-2-ol	Inhalation	Not classified for development	Rat	LOAEL 9 mg/l	during gestation

Target Organ(s)

Specific Target Organ Toxicity - single exposure

Name	Route	Target Organ(s)	Value	Species	Test result	Exposure Duration
propan-2-ol	Inhalation	central nervous system depression	May cause drowsiness or dizziness	Human	NOAEL Not available	
propan-2-ol	Inhalation	respiratory irritation	Some positive data exist, but the data are not sufficient for classification	Human	NOAEL Not available	
propan-2-ol	Inhalation	auditory system	Not classified	Guinea pig	NOAEL 13.4 mg/l	24 hours
propan-2-ol	Ingestion	central nervous system depression	May cause drowsiness or dizziness	Human	NOAEL Not available	poisoning and/or abuse

Specific Target Organ Toxicity - repeated exposure

Name	Route	Target Organ(s)	Value	Species	Test result	Exposure Duration
propan-2-ol	Inhalation	kidney and/or bladder	Not classified	Rat	NOAEL 12.3 mg/l	24 months
propan-2-ol	Inhalation	nervous system	Not classified	Rat	NOAEL 12 mg/l	13 weeks
propan-2-ol	Ingestion	kidney and/or bladder	Not classified	Rat	NOAEL 400 mg/kg/day	12 weeks

Aspiration Hazard

For the component/components, either no data is currently available or the data is not sufficient for classification.

Please contact the address or phone number listed on the first page of the SDS for additional toxicological information on this material and/or its components.

11.2. Information on other hazards

This material does not contain any substances that are assessed to be an endocrine disruptor for human health.

SECTION 12: Ecological information

The information below may not agree with the EU material classification in Section 2 and/or the ingredient classifications in Section 3 if specific ingredient classifications are mandated by a competent authority. In addition, statements and data presented in Section 12 are based on UN GHS calculation rules and classifications derived from 3M assessments.

12.1. Toxicity

No product test data available.

Material	CAS #	Organism	Type	Exposure	Test endpoint	Test result
propan-2-ol	67-63-0	Bacteria	Experimental	16 hours	LOEC	1,050 mg/l
propan-2-ol	67-63-0	Green algae	Experimental	72 hours	EC50	>1,000 mg/l
propan-2-ol	67-63-0	Invertebrate	Experimental	24 hours	LC50	>10,000 mg/l
propan-2-ol	67-63-0	Medaka	Experimental	96 hours	LC50	>100 mg/l
propan-2-ol	67-63-0	Water flea	Experimental	48 hours	EC50	>1,000 mg/l
propan-2-ol	67-63-0	Green algae	Experimental	72 hours	NOEC	1,000 mg/l
propan-2-ol	67-63-0	Water flea	Experimental	21 days	NOEC	100 mg/l

12.2. Persistence and degradability

Material	CAS Nbr	Test type	Duration	Study Type	Test result	Protocol
propan-2-ol	67-63-0	Experimental Biodegradation	14 days	BOD	86 %BOD/ThO D	OECD 301C - MITI test (I)

12.3 : Bioaccumulative potential

Material	Cas No.	Test type	Duration	Study Type	Test result	Protocol
propan-2-ol	67-63-0	Experimental Bioconcentration		Log Kow	0.05	

12.4. Mobility in soil

No test data available.

12.5. Results of the PBT and vPvB assessment

This material does not contain any substances that are assessed to be a PBT or vPvB

12.6. Endocrine disrupting properties

This material does not contain any substances that are assessed to be an endocrine disruptor for environmental effects

12.7. Other adverse effects

No information available.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Dispose of contents/ container in accordance with the local/regional/national/international regulations.

Incinerate in a permitted waste incineration facility. As a disposal alternative, utilize an acceptable permitted waste disposal facility. Empty drums/barrels/containers used for transporting and handling hazardous chemicals (chemical substances/mixtures/preparations classified as Hazardous as per applicable regulations) shall be considered, stored, treated & disposed of as hazardous wastes unless otherwise defined by applicable waste regulations. Consult with the respective regulating authorities to determine the available treatment and disposal facilities.

The coding of a waste stream is based on the application of the product by the consumer. Since this is out of the control of 3M, no waste code(s) for products after use will be provided. Please refer to the European Waste Code (EWC - 2000/532/EC and amendments) to assign the correct waste code to your waste stream. Ensure national and/or regional regulations are complied with and always use a licensed waste contractor.

EU waste code (product as sold)

- 070604* Other organic solvents, washing liquids and mother liquors
- 20 01 29* Detergents containing dangerous substances

SECTION 14: Transportation information

	Ground Transport (ADR)	Air Transport (IATA)	Marine Transport (IMDG)
14.1 UN number or ID number	UN1219	UN1219	UN1219
14.2 UN proper shipping name	ISOPROPANOL	ISOPROPANOL	ISOPROPANOL
14.3 Transport hazard class(es)	3	3	3
14.4 Packing group	II	II	II

VHB™ Surface Cleaner 8986

14.5 Environmental hazards	Not Environmentally Hazardous	Not applicable	Not a Marine Pollutant
14.6 Special precautions for user	Please refer to the other sections of the SDS for further information.	Please refer to the other sections of the SDS for further information.	Please refer to the other sections of the SDS for further information.
14.7 Marine Transport in bulk according to IMO instruments	No data available.	No data available.	No data available.
Control Temperature	No data available.	No data available.	No data available.
Emergency Temperature	No data available.	No data available.	No data available.
ADR Classification Code	F1	Not applicable.	Not applicable.
IMDG Segregation Code	Not applicable.	Not applicable.	NONE

Please contact the address or phone number listed on the first page of the SDS for additional information on the transport/shipment of the material by rail (RID) or inland waterways (ADN).

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****Global inventory status**

Contact 3M for more information.

DIRECTIVE 2012/18/EU

Seveso hazard categories, Annex 1, Part 1

None

Seveso named dangerous substances, Annex 1, Part 2

Dangerous Substances	Identifier(s)	Qualifying quantity (tonnes) for the application of	
		Lower-tier requirements	Upper-tier requirements
propan-2-ol	67-63-0	10	50

Regulation (EU) No 649/2012

No chemicals listed

15.2. Chemical Safety Assessment

A chemical safety assessment has not been carried out for this substance/mixture in accordance with Regulation (EC) No 1907/2006, as amended.

SECTION 16: Other information

List of relevant H statements

H225	Highly flammable liquid and vapour.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.

Revision information:

Section 12: Persistence and Degradability information information was modified.

Section 12:Biocumulative potential information information was modified.

DISCLAIMER: The information on this Safety Data Sheet is based on our experience and is correct to the best of our knowledge at the date of publication, but we do not accept any liability for any loss, damage or injury resulting from its use (except as required by law). The information may not be valid for any use not referred to in this Data Sheet or use of the product in combination with other materials. For these reasons, it is important that customers carry out their own test to satisfy themselves as to the suitability of the product for their own intended applications. In addition, this SDS is being provided to convey health and safety information. If you are the importer of record of this product into the European Union, you are responsible for all regulatory requirements, including, but not limited to, product registrations/notifications, substance volume tracking, and potential substance registration.

3M United Kingdom MSDSs are available at www.3M.com/uk