

21.5" Widescreen LED Security Monitor

with HDMI, VGA & BNC Inputs, RCA & PC Audio, IR Remote

LSM22R




FEATURES:

- ◆ NDAA & TAA Compliant
- ◆ 16:9 Aspect Ratio
- ◆ 1920 x 1080 Max Resolution
- ◆ Active Display, Diagonal 21.5" (54.61cm)
- ◆ Dual HDMI Inputs
- ◆ VGA & Looping BNC Input
- ◆ Low Power Consumption
- ◆ Includes HDMI & VGA Cables
- ◆ Includes Remote Control
- ◆ Super Fast 5ms Response Time
- ◆ 3D Comb Filter & 3D De-Interlace
- ◆ 3D Digital Noise Reduction
- ◆ RCA & PC Audio Inputs
- ◆ Full OSD Control of All Monitor Functions
- ◆ Vesa Mounting (100 x 100)
- ◆ LED Backlight
- ◆ CE & FCC Certifications

PACKAGE CONTENTS:

- 1. – 1.8M HDMI Cable
- 1. – 1.8M VGA Cable
- 1. – 1.5M 3.5mm Stereo Audio Cable
- 1. – Power Supply w/ 1.8M Power Cord
- 1. – User Manual
- 1. – Remote Control
- 1. – Monitor Stand

REAR PANEL CONNECTIONS:



SPECIFICATION	LSM22R
Video System	NTSC/PAL (Auto Sensing)
Max Resolution	1920 x 1080
Supported Resolutions	720x400; 640x480; 800x600; 1024x768; 1280x1024; 1366x768; 1440x900; 1600x900; 1680x1050; 1920x1080
3D Comb Filter	Yes
3D De-Interlace	Yes
OSD (On Screen Display)	Yes
Backlight	LED (RGB)
Active Display Area	Diagonal 21.5" (54.61cm)
Impedance	75 OHM Self Terminating
Video Input Signals	HDMI, VGA, Composite BNC
Video Connections	HDMI x2, VGA x1, BNC x1
Audio Connections	RCA x2, PC Audio x1
IR Remote	Yes - Included
Aspect Ratio	16:9
Pixel Pitch	0.275 x 0.275
Color Depth	16.7 Million Colors
Brightness	280 cd/m2
Contrast Ratio	1000:1
Viewing Angle (H/V)	Vertical -80°~80° / Horizontal -85°~85°
Response Time	5 ms
Auto Adjustment	Yes
Certificates	CE, FCC
Languages	English, French, Spanish, German, Japanese, Dutch, Russian, Italian
Input Voltage	External 12Volt DC / 3 Amp
Power Consumption	30W Maximum
Dimensions (with stand) (W x H x D)	513 x 391 x 164 mm
Weight (with stand)	3.53Kgs(7.78lbs)
Vesa Mounting	Yes - 100 x 100
Operating Temperature	32° ~ 104°F

21.5" Widescreen LED Security Monitor

with HDMI, VGA & BNC Inputs, RCA & PC Audio, IR Remote

LSM22R

Monitor Dimensions:

