

Product data sheet

Specifications



APC Step-Down Transformer RM 2U 208V IN 120V OUT; w/5-20 Receptacles

AP9626

Overview

Presentation	The Step-Down Transformer converts high voltage (208 or 200 VAC) output into low voltage (120 or 100 VAC) output for powering low voltage AC equipment.
Lead time	Usually in Stock

Main

Main Input Voltage	208 V
Product or Component Type	Accessory
Main Output Voltage	120 V
Input Connection Type	NEMA L6-30P
Number of rack unit	2U
Number of cables	1
Provided Equipment	User Manual Rack Mounting brackets

Physical

Color	Black
Height	3.50 in (8.9 cm)
Width	17.52 in (44.5 cm)
Depth	24.02 in (61 cm)
Net Weight	95.20 lb(US) (43.18 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Rack-mounted

Input

permissible voltage	208 V
Max line current	24 A
Input current limits	30 A
Load Capacity	5000 VA

Output

Maximum Total Current Draw per Phase	24 A
Number of power socket outlets	12

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Efficiency	90 %
------------	------

Number of power socket outlets	12 NEMA 5-20R
--------------------------------	---------------

Conformance

Product Certifications	CSA
------------------------	-----

Standards	OSHPD UL 1778
-----------	------------------

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
---------------------------------------	-------------------------

Relative Humidity	0...95 %
-------------------	----------

Operating altitude	0...10000 ft
--------------------	--------------

Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
-------------------------------------	--------------------------

Storage Relative Humidity	0...95 %
---------------------------	----------

Storage altitude	0...50000 ft (0...15240 m)
------------------	----------------------------

Ordering and shipping details

GTIN	731304249139
------	--------------

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Nbr. of units in pkg.	1
-----------------------	---

Package 1 Height	10.00 in (25.4 cm)
------------------	--------------------

Package 1 Width	37.52 in (95.3 cm)
-----------------	--------------------

Package 1 Length	24.49 in (62.2 cm)
------------------	--------------------

Package weight(Lbs)	110.2 lb(US) (50 kg)
---------------------	----------------------

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle) 4550

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard Yes

Packaging without single use plastic No

[EU RoHS Directive](#) Compliant with Exemptions

REACH Regulation [REACH Declaration](#)

Halogen content performance Product contains halogen above thresholds

Energy efficiency

Optimized Energy Efficiency Energy efficient product

Use Again

Repack and remanufacture

Circularity Profile [End of Life Information](#)

Take-back No

WEEE Label  The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Image of product / Alternate images

Alternative

