

**Part Number: 10GX IDC Patch Panel 24 Port 1U**



10GX IDC Patch Panel

**Product Description**

10GX IDC Patch Panel, 24-port, 1U, Black (Empty)

**Technical Specifications**

**Product Overview**

Environmental Space:	Indoor
Suitable Applications:	Compatible with Cross-Connect Application or Consolidation Point Application for use with Belden IBDN Systems 10GX, 4800, 2400 and 1200.

**Physical Characteristics (Overall)**

**Insulation**

<b>Nominal Diameter</b>	
0.17 mm	
Port Count:	24 connectors
Packaging:	Individually packaged in a cardboard box
Weight:	0.5 g

**Connectors**

**Materials**

Description	Material
Panel	Steel

**Electrical Characteristics**

**Inductance**

<b>Nominal Inductance</b>	
0.17 $\mu$ H/m	

**High Frequency (Nominal/Typical)**

<b>Nom. Insertion Loss</b>	
0.17 dB/100m	

**Temperature Range**

Installation Temp Range:	-10°C To +60°C
Storage Temp Range:	-40°C To +70°C
Operating Temp Range:	-10°C To +60°C

**Mechanical Characteristics**

Footprint/Type:	IDC
-----------------	-----

**Dimensions (WxHxD)**

Width	Height	Depth
19	1.75	1.64

## Standards

Data Category:	Category 6A
----------------	-------------

## Applicable Environmental and Other Programs

EU Directive Compliance:	EU Directive 2002/95/EC (RoHS)
EU RoHS Compliance Date (yyyy-mm-dd):	2008-12-16

## Suitability

Suitability - Indoor:	Yes
-----------------------	-----

## Flammability, LSOH, Toxicity Testing

Safety Listing:	UL 1863 and CSA-C22.2
-----------------	-----------------------

## Part Number

Related Parts:	10GX IDC Connecting Block
----------------	---------------------------

## Variants

Item #	Color
AX104138	Black

## Product Notes

Included Parts:	4 Screws (10x32); 4 Screws (12x24); 1 Printable LabelFlex Half-Sheet; 1 Label Insert Kit, 1 Installation Guide
Notes:	For proper installation refer to Installation Guide PX104781 included with the product or visit our web site at <a href="http://www.belden.com/pdfs/Techpprs/InstallationGuide.pdf">http://www.belden.com/pdfs/Techpprs/InstallationGuide.pdf</a>

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.