

Anaerobic Connector, LC Single-mode (OS2)

CORNING

Part Number:
95-201-98-SP

Corning anaerobic-cured connectors offer optical performance in a fast, easy field-termination solution designed for fiber-to-the-workstation applications for single-mode and multimode connections. This connector combines the quick-cured convenience of anaerobic adhesive with the performance of epoxy-and-polish connectors. Ideal for enterprise networks and any installations requiring field-installed connectors, the anaerobic-cured technology enables fiber optic networks to be installed cost effectively with minimal tools. Installation of the connector can be accomplished in minutes with the anaerobic adhesive two-part epoxy process. The adhesive is first injected into the connector ferrule, and then the fiber is dipped into the primer and inserted into the connector. Curing takes only one minute without the use of lamps or ovens. With the hand-polish process, an average insertion loss of 0.2 dB is achieved.

Features and Benefits

Quick-cure epoxy


No lamps or ovens needed

Minimal tools and no index-matching gel


Low installation cost

Hand polished for minimum insertion loss

Reliability and optical performance




Anaerobic Connector, LC, single-mode (OS2)



Anaerobic Connector, LC, single-mode (OS2)

Anaerobic Connector, LC Single-mode (OS2)



Specifications

General Specifications	
Fibre category	Single-mode (OS2)
Product type	Field-Installable Connectors
Corning logo	Yes
Keyed (security)	No
Technology	Field Polish (anaerobic)

Standards	
RoHS	Free of hazardous substances according to RoHS 2011/65/EU

Environmental Conditions	
Temperature cycling standard	" ≤ 0.3 dB IL, -40° to $+75^{\circ}$ C, 21 cycles"
Temperature range, operation	-40° C to 75° C

Anaerobic Connector, LC Single-mode (OS2)

CORNING

Design - Connector

Connector type	LC
Housing colour	Blue
Boot colour	Blue
Ferrule material	Ceramic

Optical Specifications - Connector

Insertion loss, max.	0.75 dB
Reflectance	≤ -40 dB
Insertion loss, typical	≤ 0.1 dB

Ordering Information

Product Number	95-201-98-SP
EAN Code	4056418201221
Package contents	"Connector, Trigger, Crimp Band (1.6/2.0 mm), Crimp Band (3.0 mm), Boot (900 μ m), Boot (2.0 mm), Boot (3.0 mm)"
Packaging method	Individual Pack
Units per delivery	1/1



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
+00 800 2675 4641 • FAX: • www.corning.com/opcomm/emea