

UniCam® Connector, LC 50 µm multimode (OM3/OM4)

CORNING

Part Number:
95-050-99-X

Corning® UniCam® LC connectors offer optical performance in a fast, easy field-termination solution ideal for fibre-to-the-workstation applications where setup and teardown time is critical. The high-precision mechanical splice technology enables fibre optic networks to be installed quickly and cost effectively. Installation of an LC, SC or ST® compatible connector can be accomplished in about 50 seconds to one minute with the UniCam High-Performance Tool Kit.

The lightweight, handheld installation tool and high-performance precision cleaver virtually eliminate human variability during installation, ensuring terminations are right the first time, every time. This kit was designed with consideration for network installers, from the cleaver, with its intuitive, hand-held precision design and dual-clamp precision hold, to the installation tool, with its immediate go/no-go feedback signal indicating proper mating of the field fibre to the fibre stub. Installation is as easy as strip, clean, cleave, cam and crimp, with exceptional optical performance assured. Every UniCam connector is assured to meet the published specification at the time of installation or Corning will replace it.

Features and Benefits

Performance guarantee

100 percent yield guarantee

Broad operating temperature (-40° to +75°C)

Utility and flexibility

Factory-polished end face



Consistent optical performance

Fast termination and no consumables

Low installation cost

Minimum insertion loss

Optimum optical performance



UniCam® Connector, LC 50 µm multimode (OM3/OM4)



Specifications

General Specifications	
Fibre category	50 µm MM (OM3/OM4)
Product type	Field-Installable Connectors
Corning logo	Yes
Keyed (security)	No
Technology	No-epoxy/no-polish

Standards	
RoHS	Free of hazardous substances according to RoHS 2011/65/EU

Environmental Conditions	
Temperature range, operation	-40 °C to 75 °C

Design - Connector	
Connector type	LC
Housing colour	Black
Boot colour	Turquoise
Ferrule material	Ceramic
Pinned	No

Mechanical Specifications - Connector	
Nominal fibre outer diameter	125 µm
Tensile strength jacketed cable	50 N
Durability	≤ 0.2 dB change, 500 rematings, FOTP-21
Tensile strength 900 µm cable	4.9 N (1.1 lb) change ≤ 0.2 dB, FOTP-6

UniCam® Connector, LC 50 µm multimode (OM3/OM4)



Optical Specifications - Connector

Polish	UPC
Insertion loss, max.	0.5 dB
Insertion loss, typical	0.1 dB

Ordering Information

Product Number	95-050-99-X
EAN Code	4042673619420
Package contents	"Connector, Trigger, Crimp Band, Boot (900 µm), Boot (3.0 mm), Boot (2.0 mm)"
Packaging method	Individual Pack
Units per delivery	1/1



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
+00 800 2675 4641 • FAX: • www.corning.com/opcomm/emea