



Part Number: 1351A

CAT6 Horizontal, 4pr, F/UTP, PVC Jkt, CMR

Product Description

CAT6 (350MHz), 4-Pair, F/UTP-foil shielded, Riser-CMR, Premise Horizontal cable, 23 AWG solid bare copper conductors, polyolefin insulation, polyester separator, overall Beldfoil® shield, PVC jacket

Technical Specifications

Product Overview

Environmental Space:	Riser
Suitable Applications:	Networking Horizontal Cable, 1000Base-T (Gigabit Ethernet), 100Base-T (Fast Ethernet), 10Base-T (Ethernet), 100BaseVG, ANYLAN, 155ATM, 622ATM, ANSI.X3.263 FDDI TP-PMD, NTSC/PAL Component or Composite Video, AES/EBU, Digital Video, RS-422, Noisy Environments, 250 MHz Category 6

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
23	Solid	BC - Bare Copper	4

Conductor Count:	8
Total Number of Pairs:	4
Conductor Size:	23 AWG

Insulation

Material
3 x PO - Polyolefin, 1 x FEP - Fluorinated Ethylene Propylene

Bonded-Pair:	N/A
--------------	-----

Color Chart

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum/Polyester	Beldfoil®	100 %	TC - Tinned Copper	24	Solid

Outer Jacket Material

Material	Nominal Diameter	Ripcord	Separator Material
PVC - Polyvinyl Chloride	0.290 in	No	Polyester Tape

Construction and Dimensions

Cabling

Filler
Patented Central X-spline

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Max. DCR Unbalance
93.8 Ohm/km	3 %

Capacitance

Max. Capacitance Unbalance	Nom. Mutual Capacitance
160 pF/100m	14 pF/ft

Delay

Frequency [MHz]	Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
100 MHz	537.6 ns/100m	45 ns/100m	68 %

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance	Min. TCL [dB]	Min. ELTCTL [dB]
1 MHz	2.0 dB/100m	74.3 dB	72.3 dB	70.3 dB	67.8 dB	64.8 dB	20.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	40.0 dB	35.0 dB
4 MHz	3.8 dB/100m	65.3 dB	63.3 dB	59.5 dB	55.7 dB	52.7 dB	23.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	40.0 dB	23.0 dB
8 MHz	5.3 dB/100m	60.8 dB	58.8 dB	53.4 dB	49.7 dB	46.7 dB	24.5 dB	100 ± 15 Ohm	100 ± 15 Ohm	40.0 dB	16.9 dB
10 MHz	6.0 dB/100m	59.3 dB	57.3 dB	51.4 dB	47.8 dB	44.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	40.0 dB	15.0 dB
16 MHz	7.6 dB/100m	56.3 dB	54.3 dB	46.7 dB	43.7 dB	40.7 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	38.0 dB	10.9 dB
20 MHz	8.5 dB/100m	54.8 dB	52.8 dB	44.3 dB	41.7 dB	38.7 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	37.0 dB	9.0 dB
25 MHz	9.5 dB/100m	53.3 dB	51.3 dB	41.8 dB	39.8 dB	36.8 dB	24.3 dB	100 ± 15 Ohm	100 ± 15 Ohm	36.0 dB	7.0 dB
31.25 MHz	10.7 dB/100m	51.9 dB	49.9 dB	39.2 dB	37.9 dB	34.9 dB	23.6 dB	100 ± 15 Ohm	100 ± 15 Ohm	35.1 dB	5.1 dB
62.5 MHz	15.4 dB/100m	47.4 dB	45.4 dB	30.0 dB	31.8 dB	28.8 dB	21.5 dB	100 ± 15 Ohm	100 ± 15 Ohm	32.0 dB	
100 MHz	19.8 dB/100m	44.3 dB	42.3 dB	22.5 dB	27.8 dB	24.8 dB	20.1 dB	100 ± 15 Ohm	100 ± 15 Ohm	30.0 dB	
155 MHz	25.2 dB/100m	41.5 dB	39.5 dB	14.3 dB	23.9 dB	20.9 dB	18.8 dB	100 ± 22 Ohm	100 ± 15 Ohm	28.1 dB	
200 MHz	29.0 dB/100m	39.8 dB	37.8 dB	8.8 dB	21.7 dB	18.7 dB	18.0 dB	100 ± 22 Ohm	100 ± 15 Ohm	27.0 dB	
250 MHz	32.8 dB/100m	38.3 dB	36.3 dB	3.5 dB	19.8 dB	16.8 dB	17.3 dB	100 ± 32 Ohm	100 ± 15 Ohm	26.0 dB	

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

Installation Temp Range:	0°C To +50°C
UL Temp Rating:	75°C
Storage Temp Range:	-20°C To +75°C
Operating Temp Range:	-20°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	41 lbs/1000ft
Max Recommended Pulling Tension:	25 lbs
Min Bend Radius/Minor Axis:	1.0 in
Min Bend Radius/Installation:	2.25 in

Standards

NEC/(UL) Specification:	CMR
CEC/C(UL) Specification:	CMR
ISO/IEC Compliance:	11801 ed 2.2 (2011) Class E
CPR Euroclass:	Eca
Data Category:	Category 6
ANSI Compliance:	S-116-732-2013 Category 6, ANSI/NEMA WC-66 Category 6
Telecommunications Standards:	ANSI/TIA-568-C.2 Category 6
IEEE Specification:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
Third Party Performance Verification:	Category 6

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
--------------------------------	-----

EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	Yes
EU CE Mark:	Yes
EU REACH SVHC Compliance (yyyy-mm-dd):	2017-07-10
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	No
Suitability - Oil Resistance:	No
Suitability - Outdoor:	No
Suitability - Sunlight Resistance:	No

Flammability, LSOH, Toxicity Testing

C(UL) Flammability:	FT4
UL Flammability:	UL 1666 Riser
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	1352A

Part Number

Variants

Item #	Color	Footnote
1351A 0061000	Blue	C
1351A 0081000	Gray	C
1351A 0091000	White	C
1351A 0041000	Yellow	C

Footnote:	C - CRATE REEL PUT-UP.
Patent:	https://www.belden.com/resources/patents

Product Notes

Notes:	Shield is Bonded to Jacket Inner Wall for Electrical Stability. Print Includes Descending Footage Markings from Max. Put-Up Length to 0.
--------	--

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.