



**Part Number: 2424**

**CAT6+ Horizontal, 4pr, UTP, LSZH Jkt**

### Product Description

CAT6+ (350MHz), 4-Pair, U/UTP-unshielded, Zero Halogen, Premise Horizontal cable, 23 AWG solid bare copper conductors, polyolefin insulation, patented tape separator, ripcord, LSZH jacket.

### Technical Specifications

#### Product Overview

Environmental Space:	LSZH
Suitable Applications:	Premise Horizontal Cable, POE, POE+, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU, Digital Video, RS-422

#### Physical Characteristics (Overall)

##### Conductor

AWG	Stranding	Material	No. of Pairs
23	Solid	BC - Bare Copper	4

Conductor Count:	8
Total Number of Pairs:	4
Conductor Size:	23 AWG

##### Insulation

Material	
PO - Polyolefin	
Bonded-Pair:	N/A

##### Color Chart

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

##### Outer Jacket Material

Material	Material Trade Name	Nominal Diameter	Ripcord	Separator Material
LSZH - Low Smoke Zero Halogen	Haloarrest®	0.221 in	Yes	Patented Dielectric Tape

#### Electrical Characteristics

##### Conductor DCR

Max. Conductor DCR	Max. DCR Unbalance
78 Ohm/km	3 %

##### Capacitance

Max. Capacitance Unbalance	Nom. Mutual Capacitance
330 pF/100m	17 pF/ft

##### Delay

Frequency [MHz]	Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
100 MHz	537.6 ns/100m	35 ns/100m	70 %

#### High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance	Min. TCL [dB]	Min. ELTCTL [dB]
1 MHz	2.0 dB/100m	75.3 dB	75.3 dB	73.3 dB	73.3 dB	70.8 dB	67.8 dB	20.0 dB	100 ± 15 Ohm	102 ± 15 Ohm	40.0 dB	35.0 dB
4 MHz	3.7 dB/100m	66.3 dB	66.3 dB	62.5 dB	62.5 dB	58.8 dB	55.8 dB	23.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	40.0 dB	23.0 dB
8 MHz	5.3 dB/100m	61.8 dB	61.8 dB	56.5 dB	56.5 dB	52.7 dB	49.7 dB	24.5 dB	100 ± 15 Ohm	100 ± 15 Ohm	40.0 dB	16.9 dB
10 MHz	5.9 dB/100m	60.3 dB	60.3 dB	54.4 dB	54.4 dB	50.8 dB	47.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	40.0 dB	15.0 dB
16 MHz	7.4 dB/100m	57.2 dB	57.2 dB	49.8 dB	49.8 dB	46.7 dB	43.7 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	38.0 dB	10.9 dB
20 MHz	8.3 dB/100m	55.8 dB	55.8 dB	47.4 dB	47.4 dB	44.8 dB	41.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	37.0 dB	9.0 dB
25 MHz	9.4 dB/100m	54.3 dB	54.3 dB	45.0 dB	45.0 dB	42.8 dB	39.8 dB	24.3 dB	100 ± 15 Ohm	100 ± 15 Ohm	36.0 dB	7.0 dB
31.25 MHz	10.5 dB/100m	52.9 dB	52.9 dB	42.4 dB	42.4 dB	40.9 dB	37.9 dB	23.6 dB	100 ± 15 Ohm	100 ± 15 Ohm	35.1 dB	5.1 dB
62.5 MHz	15.1 dB/100m	48.4 dB	48.4 dB	33.3 dB	33.3 dB	34.9 dB	31.9 dB	21.5 dB	100 ± 15 Ohm	100 ± 15 Ohm	32.0 dB	
100 MHz	19.3 dB/100m	45.3 dB	45.3 dB	26.0 dB	26.0 dB	30.8 dB	27.8 dB	20.8 dB	100 ± 15 Ohm	100 ± 15 Ohm	30.0 dB	
155 MHz	24.5 dB/100m	42.4 dB	42.4 dB	17.9 dB	17.9 dB	27.0 dB	24.0 dB	19.5 dB	100 ± 22 Ohm	100 ± 15 Ohm	28.1 dB	
200 MHz	28.2 dB/100m	40.8 dB	40.8 dB	12.6 dB	12.6 dB	24.8 dB	21.8 dB	18.7 dB	100 ± 22 Ohm	100 ± 15 Ohm	27.0 dB	
250 MHz	31.8 dB/100m	39.3 dB	39.3 dB	7.5 dB	7.5 dB	22.8 dB	19.8 dB	18.0 dB	100 ± 32 Ohm	100 ± 15 Ohm	26.0 dB	
300 MHz	35.2 dB/100m	38.1 dB	36.1 dB	2.9 dB	0.9 dB	21.3 dB	18.3 dB	17.5 dB	100 ± 32 Ohm	100 ± 15 Ohm	25.2 dB	
350 MHz	38.4 dB/100m	37.1 dB	35.1 dB			19.9 dB	16.9 dB	17.0 dB	100 ± 32 Ohm	100 ± 15 Ohm	24.6 dB	
400 MHz	41.5 dB/100m	36.3 dB	34.3 dB			18.8 dB	15.8 dB	16.6 dB	100 ± 32 Ohm	100 ± 15 Ohm	24.0 dB	
450 MHz	44.3 dB/100m	35.5 dB	33.5 dB			17.7 dB	14.7 dB	16.2 dB	100 ± 32 Ohm	100 ± 15 Ohm	23.5 dB	
500 MHz	47.1 dB/100m	34.8 dB	32.8 dB			16.8 dB	13.8 dB	15.9 dB	100 ± 32 Ohm	100 ± 15 Ohm	23.0 dB	
550 MHz	49.7 dB/100m	34.2 dB	32.2 dB			16.0 dB	13.0 dB	15.6 dB	100 ± 32 Ohm	100 ± 15 Ohm		

Segregation class according EN50174-2: a

#### Voltage

##### UL Voltage Rating

300 V RMS

#### Temperature Range

Installation Temp Range:	+5°C To +50°C
Non-UL Temp Rating:	+75°C
Storage Temp Range:	-20°C To +75°C
Operating Temp Range:	-20°C To +75°C

#### Mechanical Characteristics

Bulk Cable Weight:	23 lbs/1000ft
Max Recommended Pulling Tension:	25 lbs
Min Bend Radius/Minor Axis:	1.0 in
Min Bend Radius/Installation:	2.25 in

#### Standards

NEC/(UL) Specification:	N/A
ISO/IEC Compliance:	11801 ed 2.2 (2011) Class E
CPR Euroclass:	Eca
Data Category:	Category 6
ANSI Compliance:	S-116-732-2013 Category 6, ANSI/NEMA WC-66 Category 6
Telecommunications Standards:	ANSI/TIA-568-C.2 Category 6
IEEE Specification:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
Third Party Performance Verification:	Category 6

#### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes

EU Directive Compliance:	Yes
EU CE Mark:	No
EU REACH SVHC Compliance (yyyy-mm-dd):	2017-07-10
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	Yes
Suitability - Oil Resistance:	No
Suitability - Outdoor:	No
Suitability - Sunlight Resistance:	No

## Flammability, LSOH, Toxicity Testing

UL voltage rating:	300 V RMS
--------------------	-----------

## Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	2413

## Part Number

Non-Plenum Number:	2412
--------------------	------

## Variants

Item #	Color
2424.06305	Blue
2424.08305	Blue
2424 0061000	Blue
2424.07305	Purple
2424 0071000	Purple
2424.071000	Purple
2424.02500	Red
2424 0091000	White

Patent:	<a href="https://www.belden.com/resources/patents">https://www.belden.com/resources/patents</a>
---------	---

## Product Notes

Notes:	Values above 350 MHz are for Engineering Information Only. Print Includes Descending Footage/Meter Markings from Max. Put-Up Length to 0.
--------	---

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.