

FuseLite® 2 Splice-on Connector LC, 2 mm, multimode (OM4), pack of 6

CORNING

Part Number:
FL2-LC-2MM-OM4-6

The FuseLite® 2 Splice-On Connector enables fast, reliable fusion splicing connectivity for all networks and offers flexibility for repairs and restoration of connectivity. Available in SC, LC and ST® compatible, the FuseLite2 Connector provides a reliable connectivity option for applications where fusion splicing may be preferred, such as reflectance-sensitive applications. The FuseLite2 Connector eliminates the need for splice trays and is compatible with leading fusion splicers in the market. Contact Corning Customer Service at 1-800-743-2675 for more information.

Features and Benefits

Broad operating temperature (-40° to +75°C)

Utility and flexibility

Factory-polished end face


Consistent optical performance

Fusion splice connectivity

Ideal for reflectance-sensitive applications

Splice protection within connector body

No splice trays required



FuseLite® 2 Splice-on Connector LC, 2 mm, multimode (OM4), pack of 6



Specifications

General Specifications	
Fibre category	50 µm MM (OM4)
Product type	Field-Installable Connectors
Compatibility	LC
Corning logo	No
Keyed (security)	No
Technology	Fuse-On

Standards	
RoHS	Free of hazardous substances according to RoHS 2011/65/EU

Environmental Conditions	
Temperature range, operation	-40 °C to 75 °C

Design - Connector	
Connector type	LC

Optical Specifications - Connector	
Insertion loss, max.	0.3 dB
Reflectance	< -30 dB
Insertion loss, typical	0.2 dB

Ordering Information	
Product Number	FL2-LC-2MM-OM4-6
Package contents	"FuseLite® 2 Splice-on Connector, LC, 2 mm, multimode (OM4)"

FuseLite® 2 Splice-on Connector LC, 2 mm, multimode (OM4), pack of 6



Ordering Information	
Packaging method	Bulk Pack
Units per delivery	6/1



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
+00 800 2675 4641 • FAX: • www.corning.com/opcomm/emea