

Everon® Copper Datacom Class E Patch Cord, 2xRJ45, Cat.6, U/UTP LSZH AWG 26 white, 5 m

CORNING

Part Number: CCAVGE-D9002-A050-C0

The application-neutral Everon® Copper Datacom category 6 patch cords are unshielded (U/UTP). They are assembled with unshielded RJ45 connectors on each end. The zero halogen patch cords (LSZH) are non-corrosive according to IEC 60754-2 (FRNC), low smoke according to IEC 61034 and flame retardant according to IEC 60332-1. Everon® Copper Datacom CCAVGE patch cords provide additional latch protection. They are available in various lengths and colours.

Features and Benefits

Application-neutral due to using all four pairs of RJ45 connectors


IP68 rated ruggedized design

Additional latch protection

Category 6

Certified by a vendor-independent and impartial test lab (GHMT AG)

Supports Power over Ethernet (PoE / PoE+ / PoE++).
IEEE 802.3bt-2018 performance (4PPoE)
Ready for new applications powered on 4 pairs up to 90W



Everon® Copper Datacom Class E Patch Cord, 2xRJ45, Cat.6, U/UTP LSZH™ AWG 26, white, 5 m

Everon® Copper Datacom Class E Patch Cord, 2xRJ45, Cat.6, U/UTP LSZH AWG 26 white, 5 m

CORNING

Specifications

General Specifications

Area/range of application	10Base-T; 100Base-TX; 1000Base-T/ATMLAN1.2Gbit/s
Cable assembly type	Patch cords
Environment	Indoor
Category	6
Cable type	U/UTP
Halogen-free	Yes
Legacy Part Number	VOL-6UDL
Brand	Everon®
Third Party Certificate	Yes (www.corning.com/emea/en/certificates)

Standards

Flame retardance	Flame retardant according to IEC 60332-1-2 (single cable)
RoHS	Free of hazardous substances according to RoHS 2011/65/EU
Design And Test Criteria	Compliant with PoE / PoE++ IEEE 802.3af, IEEE 802.3at and IEEE 802.3bt
Halogen content test	Low Smoke to IEC 61034
Level of corrosion	Non-corrosive according to IEC 60754-2

Environmental Conditions

Temperature range, installation	0 °C to 50 °C
Temperature range, operation	-20 °C to 60 °C
Transport and indoor storage	Dry environment, no direct sunlight, room temperature ≤ 40 °C

Cable Design

Conductor insulation	Halogen-free foam-skin material
Twisting	2 cores to a pair

Everon® Copper Datacom Class E Patch Cord, 2xRJ45, Cat.6, U/UTP LSZH AWG 26 white, 5 m

CORNING

Cable Design

Outer jacket material	LSZH/FRNC
Outer jacket colour	White

Mechanical Specifications

Fire load	0.3 MJ/m
Min. bend radius installation	34 mm

Specifications - Connector A

Connector type	RJ45 - 8/8
Durability Cycles	750 N/A
Connector Material	Pin gold plated 50µ inch

Specifications - Connector B

Connector type	RJ45 - 8/8
Durability Cycles	750 N/A
Connector Material	Pin gold plated 50µ inch

Electrical Specifications

Mutual capacity	1600 pF/km
Max. loop resistance	150 Ω/km
Propagation delay	5.38 ns/m at 100 MHz
DC resistance unbalance	5 %
Insulation resistance	500 MΩ*km
Impedance Zo at 1-100 MHz	100 Ω ± 5% at 100 MHz

Everon® Copper Datacom Class E Patch Cord,
2xRJ45, Cat.6, U/UTP LSZH AWG 26 white, 5 m



Dimensions	
Length	5 m
Weight	12 kg

Ordering Information	
Product Number	CCAVGE-D9002-A050-C0
EAN Code	4064394141950
Packaging method	Corn Starch Bag
Shipping weight	0.13 kg
Units per delivery	1/1



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
+00 800 2675 4641 • FAX: • www.corning.com/opcomm/emea