

Part Number: CAT 5E HD-110 PP 48 2U

CAT 5E HD-110 Patch Panel, 48 Port, 2U



Product Description

CAT5E HD-110 Patch Panel, 48-port, 2U

Technical Specifications

Product Overview

Environmental Space:	Indoor
Suitable Applications:	IBDN System 1200, TIA Category 5e, ISO Class D, 1000BASE-T, 100BASE-T

Physical Characteristics (Overall)

Height:	3.440 in
Width:	19.000 in
Depth:	1.35 in
Port Count:	48 Port
Front Connection:	Flush
Packaging:	Individually packaged in a cardboard box.
Weight:	1.700 lbs

Connectors

Materials

DescriptionMaterialPanelSteel

Construction and Dimensions

Max Capacity:	48 connectors (preloaded)
Electrical Characteristics	

Dielectric Strength:	1,000 V RMS @ 60 Hz for 1 minute
Current Rating:	1.500 A
Insulation Resistance:	500 M-Ohm Minimum
Termination Resistance:	2.5 mOhm

Temperature Range

Installation Temp Range:	-10°C To +60°C
Storage Temp Range:	-40°C To +70°C
Operating Temp Range:	-10°C To +60°C

Mechanical Characteristics

Footprint/Type:	HDPP
Tool Compatibility:	Gigaflex Connecting Tool (AX100749)
Plug /Jack Compatibility:	RJ45
Termination Type:	Universal T568A/B

Standards

Data Category:	Category 5e
Telecommunications Standards:	Category 5 - ISO/IEC 11801:2002 Ed.2
Other Standards:	FCC Part 68, Subpart F, IEC 60603-7

Applicable Environmental and Other Programs

EU Directive 2011/65/EU (ROHS II):	Yes
MII Order #39 (China RoHS):	EUP 50

Flammability, LS0H, Toxicity Testing

Safety Listing:	ACA, Bi-national Standard Listed
Part Number	
Related Parts:	CAT5E Modular Cords
Variants	
Item #ColorAX103259Black	
Product Notes	

Included Parts:	4 Screws (10x32); 4 Screws (12x24); 1 Printable LabelFlex Half-Sheet; 1 Installation Guide.
Notes:	For proper installation refer to Installation Guide PX100733 included with the product

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.