

**Part Number:** CAT 6 KCONN PP 48 2U



CAT 6 KeyConnect Patch Panel, 48 Port, 2U

## Product Description

CAT6+ KeyConnect Patch Panel, 48-port, 2U

## Technical Specifications

### Product Overview

Environmental Space:	Indoor
Suitable Applications:	IBDN System 4800, 3600, 2400, TIA Category 6, ISO Class E, 1000BASE-T

### Physical Characteristics (Overall)

Height:	3.5 in
Width:	19.000 in
Depth:	1.3 in
Port Count:	48 Port
Front Connection:	Flush
Packaging:	Individually packaged in a cardboard box.
Weight:	2.500 lbs

### Connectors

#### Materials

Description	Material
Panel	Steel

### Construction and Dimensions

Max Capacity:	48 connectors (preloaded)
---------------	---------------------------

### Electrical Characteristics

Dielectric Strength:	1,000 V RMS @ 60 Hz for 1 minute
Current Rating:	1.500 A
Insulation Resistance:	500 M-Ohm Minimum
Termination Resistance:	2.5 mOhm

### Temperature Range

Installation Temp Range:	-10°C To +60°C
Storage Temp Range:	-40°C To +70°C
Operating Temp Range:	-10°C To +60°C

### Mechanical Characteristics

Footprint/Type:	KeyConnect
Plug /Jack Compatibility:	RJ45
Termination Type:	Universal T568A/B

### Standards

Data Category:	Category 6
Telecommunications Standards:	Category 6 - TIA 568.C.2, ISO/IEC 11801:2002 Ed.2, EIA/ECA 310
Other Standards:	UL 1863
Third Party Performance Verification:	ETL - Verified Category 6

## Applicable Environmental and Other Programs

EU Directive 2011/65/EU (ROHS II):	Yes
MII Order #39 (China RoHS):	EUP 50

## Flammability, LS0H, Toxicity Testing

Safety Listing:	Bi-national Standard Listed
-----------------	-----------------------------

## Part Number

Related Parts:	CAT6+ Modular Cords
----------------	---------------------

## Variants

Item #	Color
AX103255	Black

## Product Notes

Included Parts:	4 Screws (10x32); 4 Screws (12x24); 1 Label Holder; 1 Printable LabelFlex Half-Sheet; 2 Velcro Straps; 2 Rear Cable Management Bracket; 1 Installation Guide; 1 kit Termination Bar
Notes:	For proper installation refer to Installation Guide PX104691 included with the product

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.