



Part Number: CAT6+ MDVO JACKS

CAT6+ Modular Jack, RJ45, MDVO Style

Product Description

CAT6+ KeyConnect Jacks are available in several colors.

Technical Specifications

Product Overview

Environmental Space:	Indoor
Suitable Applications:	IBDN System 2400 and 4800, TIA Category 6+, ISO Class E, 1000 BASE-T

Physical Characteristics (Overall)

Height:	0.765 in
Width:	0.77 in
Depth:	1.29 in
Wiring Scheme:	T568A/B
Packaging:	Individually packaged in a plastic bag. Standard pack of 50 units.
Weight:	0.014 lbs

Connectors

Materials

Description	Material	Type
Front Connection	Copper Alloy with 50 μ inch Gold over Nickel	Lead Frame
Rear Connection	Copper Alloy with Nickel Plating	IDC
Connector Body	Plastic - UL940V-0	

Electrical Characteristics

Dielectric Strength:	1,000V RMS @ 60 Hz for 1 minute
Current Rating:	1.500 A
Insulation Resistance:	500 M-Ohm Minimum
Max Contact Resistance:	20 mOhm
Termination Resistance:	2.5 mOhm

Temperature Range

Installation Temp Range:	-10°C to +60°C
Storage Temp Range:	-40°C to +70°C
Operating Temp Range:	-10°C to +60°C

Mechanical Characteristics

Footprint/Type:	MDVO
Tool Compatibility:	Belden 110 Connecting Tool, MediaFlex Termination Station
Plug /Jack Compatibility:	RJ45, RJ11
Termination Front Connection:	Mated Connection
Termination Front Connection Durability:	1,000 cycles
Termination Rear Connection:	Gas Tight IDC Connection

Termination Rear Connection Durability:	20 terminations
Connector/Hardware Retention:	20 lbs
Plug/Connector Retention:	11.250 lbs

Standards

Data Category:	Category 6+
Telecommunications Standards:	ISO/IEC 11801:2002 Ed.2
Other Standards:	FCC Part 68, Subpart F, IEC 60603-7
Third Party Performance Verification:	ETL - Verified Category 6

Applicable Environmental and Other Programs

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2006-07-01
MII Order #39 (China RoHS):	EUP 50

Flammability, LSOH, Toxicity Testing

Safety Listing:	ACA, c(UL)us Listed
-----------------	---------------------

Part Number

Related Parts:	Compatible with Interface and MDVO Style Faceplates, Adapters, Boxes and Patch Panels
----------------	---

Variants

Item #	Color	Packaging	Wiring Scheme
AX101064	Almond	Single Pack	T568A/B
AX101066	Black	Single Pack	T568A/B
AX101063	Gray	Single Pack	T568A/B
AX102563	Ivory	Single Pack	T568A/B
AX101071	TIA Blue	Single Pack	T568A/B
AX101073	TIA Brown	Single Pack	T568A/B
AX101070	TIA Green	Single Pack	T568A/B
AX101067	TIA Orange	Single Pack	T568A/B
AX101072	TIA Purple	Single Pack	T568A/B
AX101068	TIA Red	Single Pack	T568A/B
AX101069	TIA Yellow	Single Pack	T568A/B
AX101065	White	Single Pack	T568A/B

Product Notes

Included Parts:	1 T-Bar +1 Dust Cap
Notes:	Please see Installation Guide PX103329

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.