

Product data sheet

Specifications



APC Smart-UPS Ultra, 5kVA,
Rackmount 4U, 208V, 12x
5-20R+2x L6-20R+1x L6-30R
NEMA, Network Card+SmartSlot,
W/ rail kit, W/ transformer 208V to
120V

SRTL5KRM2UT-5KRMTF

Overview

Lead time Usually in Stock

Main

Main Input Voltage	208 V
Product or Component Type	Uninterruptible power supply (UPS)
Other Input Voltage	240 V
Main Output Voltage	120 V
Other Output Voltage	240 V
Kw Rating	4900 W
Rated power in VA	4900 VA
Input Connection Type	NEMA L6-30P
output connection type	12 NEMA 5-20R 2 NEMA L6-20R 2 NEMA L6-30R
Number of rack unit	4U
Cable length	10 ft (3.05 m)
Number of cables	1
Provided equipment	Rack Mounting brackets Stabilization feet Rack Mounting support rails USB cable Temperature Probe Strain relief Battery
Range of Product	Smart-UPS Ultra

Batteries & Runtime

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph
Battery Type	Li-Ion (Lithium Ion)
Battery Voltage	180 V
Extendable Run Time	1
Included Battery Modules	0

Battery Slots Empty	0
Typical recharge time	1.5 h
RBC Quantity	1
Battery life	8...10 year(s)
Battery Charge Power (Watts)	600 W rated

General

Number of power module filled slots	0
Number of power module free slots	0
product web sub-family	High density
Redundant	No
Topology	On-Line

Physical

color	Black
Height	6.9 in (176 mm)
Width	17.008 in (432 mm)
Depth	28.3 in (719 mm)
Net Weight	159.37 lb(US) (72.29 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Rack-mounted
Two post mountable	0
USB compatible	Yes
Mounting position	Horizontal

Input

Efficiency at full load	100...275 V adjustable (half load)
Input Frequency	40 - 70 Hz auto-sensing

Output

Bypass type	Internal Bypass (Automatic and Manual)
Crest factor	3 : 1
Harmonic distortion	Less than 2%
Maximum configurable power in VA	4900 VA
Max Configurable Power (Watts)	4900 W
Waveform Type	Sine wave
Full load runtime	4900 W
Half load runtime	2450 W
Output frequency	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product Certifications	ENERGY STAR V2.0 (USA)
------------------------	------------------------

Environmental

Acoustic level	55 dBA
Heat dissipation	1047 Btu/h
Operating altitude	0...10000 ft
Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0...15240 m)
IP degree of protection	IP20
Relative Humidity	0...95 % non-condensing
Storage Relative Humidity	0...95 % non-condensing

Communications & Management

Emergency Power Off (EPO)	Yes
Pre-Installed SmartSlot™ Cards	Network management card 3 with environmental monitoring
Alarm	Audible and visible alarms : prioritized by severity

Surge Protection and Filtering

Surge energy rating	1260 J
---------------------	--------

Ordering and shipping details

GTIN	731304437086
------	--------------

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	20.0 in (50.8 cm)
Package 1 Width	37.8 in (96 cm)
Package 1 Length	24.5 in (62.2 cm)
Package weight(Lbs)	174.4 lb(US) (79.1 kg)

Contractual warranty

Warranty	5 years repair or replace
----------	---------------------------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

Environmental footprint

Carbon footprint (kg CO2 eq, Total Life cycle)	11268
--	-------

Environmental Disclosure	Product Environmental Profile
--------------------------	---

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
--	-----

Packaging without single use plastic	No
--------------------------------------	----

EU RoHS Directive	Compliant with Exemptions
-----------------------------------	---------------------------

REACH Regulation	REACH Declaration
------------------	-----------------------------------

Energy efficiency

 ENERGY STAR®	ENERGY STAR UPS V2.0 (USA)
--	----------------------------

Product contributes to saved and avoided emissions	Yes
--	-----

Use Again

Repack and remanufacture

Circularity Profile	End of Life Information
---------------------	---

Removable battery	User replaceable
-------------------	------------------

Take-back	Yes
-----------	-----

Product data sheet SRTL5KRM2UT-5KRMTF

Image of product / Alternate images

Alternative

