



Part Number: FX UHD Cassette OM4 18P MPO12F

FX UHD Cassette OM4 18 Ports MPO-12 F

Product Description

FX UHD Cassette OM4 18 Ports MPO-12 Female. Available in several fiber and polarity types as well as adapter colors.

Technical Specifications

Product Overview

Environmental Space:	Indoor
Suitable Applications:	FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room, Data Centers

Construction

Fiber Cable Construction

Fiber Type	
OM4	
Fiber Type:	OM4

Buffer Specification

Fiber Type	
OM4	
Weight:	0.657 lbs
Height:	1.5 m
Width:	4.5
Length:	6.6 ft

Mechanical Characteristics

Front Connection:	Static
-------------------	--------

Temperature Range

Operating Temp Range:	-10 to 60°C
Storage Temp Range:	-10 to 75°C

Product Material

Materials

Element	Description	Material	Color
Zirconia-Ceramic	Adapter Sleeve Material	Zirconia-Ceramic	
Plastic - UL94V-0	Front Connector Body	Plastic - UL94V-0	Erika Violet
Plastic - UL94V-0	Cassette Assembly	Plastic - UL94V-0	Black

Standards

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2006-01-07
MII Order #39 (China RoHS):	EUP 50

Additional Notes

Packaging:	Individually packaged in a plastic shell, Shipped in cardboard box (14/box)
Related Parts:	FX UHD & FXU Patch Panels, FX MPO Trunks

History

Variants

Item #	Color	Connector Type	Polarity Identification
FC4H18LDMFAA	Erika Violet	LC Duplex	Type-A
FC4H18LDMF1E	Erika Violet	LC Duplex	Type-A Alternate
FC4H18LDMF1A	Erika Violet	LC Duplex	Type-A Alternate
FC4H18LDMF	Erika Violet	LC Duplex	Type-A
FC4H18LDMF-NPI	Erika Violet	LC Duplex	

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.