



Part Number: 10GX UTP CMR PIGTAILS

10GX UTP CMR Pigtails

Product Description

10GX UTP CMR Pigtails

Technical Specifications

Product Overview

Environmental Space:	Riser
Suitable Applications:	IBDN System 10GX, TIA Category 6A, ISO Class EA, 10GBASE-T

Physical Characteristics (Overall)

Total Number of Pairs:	4
Conductor Size:	24 AWG
Overall Nominal Diameter:	0.295 in
Packaging:	Individually packaged in a clear plastic bag.

Connectors

Materials

Description	Material	Color
Boot	Elastomer	Translucent
Conductor	BC - Bare Copper	
Front Connection	Blades Phosphor Bronze with 50u inch Gold over Nickel Plating	
Inner Jacket	PVC - Polyvinyl Chloride	
Insulation	PO - Polyolefin	
Outer Jacket	PVC - Polyvinyl Chloride	

Electrical Characteristics

Dielectric Strength:	1,000 V RMS @ 60 Hz for 1 minute
Current Rating:	1.500 A
Insulation Resistance:	500 M-Ohm Minimum
Max Contact Resistance:	20 mOhm

Temperature Range

Installation Temp Range:	-10°C To +60°C
Storage Temp Range:	-40°C To +70°C
Operating Temp Range:	-10°C To +60°C

Mechanical Characteristics

Min Bend Radius (Overall Cable):	1.040 in
Plug /Jack Compatibility:	RJ45

Termination Interface

Connection	Durabilities
Mated Connection	750 Cycles

Standards

UL Rating:	Riser
Data Category:	Category 6A
Telecommunications Standards:	Category 6A - TIA 568-C.2, Class EA - ISO/IEC 11801:2002 Ed.2 Amendment 2
Other Standards:	FCC Part 68, Subpart F, IEC 60603-7

Applicable Environmental and Other Programs

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2006-01-01
MII Order #39 (China RoHS):	EUP 50

Flammability, LS0H, Toxicity Testing

Safety Listing:	c(UL)us Listed
-----------------	----------------

Part Number

Related Parts:	10GX Modular Jacks and Couplers, 10GX Patch Panels, 10GX IDC Blocks
----------------	---

Variants

Item #	Color	Length
CA31306100	Blue	100 ft
CA31306075	Blue	75 ft
CA31306060	Blue	60 ft
CA31306050	Blue	50 ft
CA31306035	Blue	35 ft
CA31306030	Blue	30 ft
CA31306025	Blue	25 ft
CA31306020	Blue	20 ft
CA31306015	Blue	15 ft
CA31206100	Blue	100 ft
CA31206075	Blue	75 ft
CA31206050	Blue	50 ft
CA31206035	Blue	35 ft
CA31206025	Blue	25 ft
CA31206020	Blue	20 ft
CA31206004	Blue	4 ft
CA31308100	Gray	100 ft
CA31308075	Gray	75 ft
CA31308065	Gray	65 ft
CA31308050	Gray	50 ft
CA31308040	Gray	40 ft
CA31308035	Gray	35 ft
CA31308030	Gray	30 ft
CA31308025	Gray	25 ft
CA31308020	Gray	20 ft
CA31308015	Gray	15 ft
CA31208075	Gray	75 ft
CA31208050	Gray	50 ft
CA31208065	Gray	65 ft
CA31208035	Gray	35 ft
CA31208025	Gray	25 ft
CA31208020	Gray	20 ft
CA31208015	Gray	15 ft
CA31208100	Gray	100 ft
CA31208007	Gray	7 ft
CA31205025	Green	25 ft
CA31205035	Green	35 ft
CA31309100	White	100 ft
CA31309007	White	7 ft
CA31308007	White	7 ft
CA31309075	White	75 ft

CA31309050	White	50 ft
CA31309035	White	35 ft
CA31309025	White	25 ft
CA31309020	White	20 ft
CA31309015	White	15 ft
CA31209100	White	100 ft
CA31209010	White	10 ft
CA31209075	White	75 ft
CA31209050	White	50 ft
CA31209035	White	35 ft
CA31209025	White	25 ft
CA31209020	White	20 ft
CA31209015	White	15 ft

Product Notes

Labeling:	Belden Part Number, Performance Acronym, Wiring Scheme and Cord Length.
-----------	---

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.