



Part Number: FX UHD Frame OS2 18P

FX UHD Frame OS2 18 Ports

Product Description

FX UHD Frame OS2 18 Ports

Technical Specifications

Product Overview

Part Number:	FFSH18MP
Environmental Space:	Indoor
Suitable Applications:	FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room, Data Centers

Construction

Fiber Cable Construction

Fiber Type	
OS2	
Fiber Type:	OS2

Buffer Specification

Fiber Type	
OS2	
Weight:	4.46 kg
Height:	1.5 m
Depth:	2.2

Temperature Range

Operating Temp Range:	-10 to 60°C
Storage Temp Range:	-10 to 75°C

Product Material

Materials

Description	Material	Color
Frame	Plastic - UL94V-0	Black
Front Connector Body	Plastic - UL94V-0	Blue

Standards

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2006-01-07
MII Order #39 (China RoHS):	EUP 50

Additional Notes

Packaging:	Individually packaged in a plastic shell, Shipped in cardboard box (60/box)
Included Parts:	Dust Caps
Related Parts:	FiberExpress Ultra Patch panels, Pre-terminated MPO low loss cable assemblies

Variants

Item #	Color	Connector Type	Port Count	Fiber Type
FFSH18MP	Blue	MPO Up/Down	18 Port	OS2

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.