



Part Number: 10GX12

CAT6A 10GX, 4pr, UTP, PVC Jkt, CMR

Product Description

CAT6A (625MHz), 4-Pair, U/UTP-unshielded, Riser-CMR 90C OR CMR-LP (0.5A) OR CL3R-LP (0.5A), Premise Horizontal cable, 23 AWG solid bare copper conductors, polyolefin insulation, patented Double-H spline, ripcord, PVC jacket

Technical Specifications

Product Overview

Environmental Space:	Riser
Suitable Applications:	Premise Horizontal Cable, 10 Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU Digital Audio, AES51, RS-422, Noisy Environments, PoE

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
23	Solid	BC - Bare Copper	4

Conductor Count:	8
Total Number of Pairs:	4
Conductor Size:	23 AWG

Insulation

Material	
PO - Polyolefin	
Bonded-Pair:	N/A

Color Chart

Number	Color
1	White & Blue
2	White & Orange
3	White & Green
4	White & Brown

Outer Jacket Material

Material	Nominal Diameter	Ripcord	Separator Material
PVC - Polyvinyl Chloride	0.295 in	Yes	Patented RoundFlex - Double H Cross-Web

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Max. DCR Unbalance	Max DCR Unbalanced Between Pairs [%]
74 Ohm/km	3 %	5 %

Capacitance

Max. Capacitance Unbalance	Nom. Mutual Capacitance
50 pF/100m	17 pF/ft

Delay

Frequency [MHz]	Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]	Typical Delay Skew
100 MHz	537.6 ns/100m	45 ns/100m	64 %	35 ns/100m

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. PSNEXT [dB]	Min. PSACR [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance	Min. PSANEXT	Min. PSAACRF	Min. TCL [dB]	Min. ELTCTL [dB]
1 MHz	2.1 dB/100m	73.3 dB	71.2 dB	68.8 dB	20.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	67.0 dB	67.0 dB	40.0 dB	35.0 dB
4 MHz	3.8 dB/100m	64.3 dB	60.5 dB	56.8 dB	23.0 dB	100 ± 15 Ohm	100 ± 10 Ohm	67.0 dB	67.0 dB	40.0 dB	23.0 dB
8 MHz	5.3 dB/100m	59.8 dB	54.4 dB	50.7 dB	24.5 dB	100 ± 15 Ohm	100 ± 10 Ohm	67.0 dB	61.1 dB	40.0 dB	16.9 dB
10 MHz	5.9 dB/100m	58.3 dB	52.4 dB	48.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 10 Ohm	67.0 dB	59.2 dB	40.0 dB	15.0 dB
16 MHz	7.5 dB/100m	55.2 dB	47.8 dB	44.7 dB	25.0 dB	100 ± 15 Ohm	100 ± 10 Ohm	67.0 dB	55.1 dB	40.0 dB	10.9 dB
20 MHz	8.4 dB/100m	53.8 dB	45.4 dB	42.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 10 Ohm	67.0 dB	53.2 dB	38.0 dB	9.0 dB
25 MHz	9.4 dB/100m	52.3 dB	43.0 dB	40.8 dB	24.3 dB	100 ± 15 Ohm	100 ± 10 Ohm	67.0 dB	51.2 dB	36.0 dB	7.0 dB
31.25 MHz	10.5 dB/100m	50.9 dB	40.4 dB	38.9 dB	23.6 dB	100 ± 15 Ohm	100 ± 10 Ohm	67.0 dB	49.3 dB	35.1 dB	
62.5 MHz	15.0 dB/100m	46.4 dB	31.4 dB	32.9 dB	21.5 dB	100 ± 15 Ohm	100 ± 10 Ohm	66.6 dB	43.3 dB	32.0 dB	
100 MHz	19.1 dB/100m	43.3 dB	24.2 dB	28.8 dB	20.1 dB	100 ± 15 Ohm	100 ± 10 Ohm	63.5 dB	39.2 dB	30.0 dB	
200 MHz	27.6 dB/100m	38.8 dB	11.2 dB	22.8 dB	18.0 dB	100 ± 22 Ohm	100 ± 10 Ohm	59.0 dB	33.2 dB	27.0 dB	
250 MHz	31.1 dB/100m	37.3 dB	6.3 dB	20.8 dB	17.3 dB	100 ± 32 Ohm	100 ± 10 Ohm	57.5 dB	31.2 dB	26.0 dB	
300 MHz	34.3 dB/100m	36.1 dB	1.9 dB	19.3 dB	16.8 dB	100 ± 32 Ohm	100 ± 10 Ohm	56.3 dB	29.7 dB	25.2 dB	
350 MHz	37.2 dB/100m	35.1 dB		17.9 dB	16.3 dB	100 ± 32 Ohm	100 ± 10 Ohm	55.3 dB	28.3 dB	24.6 dB	
400 MHz	40.1 dB/100m	34.3 dB		16.8 dB	15.9 dB	100 ± 32 Ohm	100 ± 10 Ohm	54.5 dB	27.2 dB	24.0 dB	
450 MHz	42.7 dB/100m	33.5 dB		15.7 dB	15.5 dB	100 ± 32 Ohm	100 ± 10 Ohm	53.7 dB	26.1 dB	23.5 dB	
500 MHz	45.3 dB/100m	32.8 dB		14.8 dB	15.2 dB	100 ± 32 Ohm	100 ± 10 Ohm	53.0 dB	25.2 dB	23.0 dB	
550 MHz	47.7 dB/100m	32.2 dB		14.0 dB	14.9 dB	100 ± 32 Ohm	100 ± 10 Ohm	52.4 dB	24.4 dB		
600 MHz	50.1 dB/100m	31.6 dB		13.2 dB	14.7 dB	100 ± 32 Ohm	100 ± 10 Ohm	51.8 dB	23.6 dB		
625 MHz	51.2 dB/100m	31.4 dB		12.9 dB	14.5 dB	100 ± 32 Ohm	100 ± 10 Ohm	51.6 dB	23.3 dB		
750 MHz	56.7 dB/100m	30.2 dB		11.3 dB	14.0 dB			50.4 dB	21.7 dB		
860 MHz	61.2 dB/100m	29.3 dB		10.1 dB	13.6 dB			49.5 dB	20.5 dB		

Segregation class according EN50174-2: a

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

Installation Temp Range:	+5°C To +50°C
UL Temp Rating:	90°C
Storage Temp Range:	-20°C To +75°C
Operating Temp Range:	-20°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	36 lbs/1000ft
Max Recommended Pulling Tension:	25 lbs
Min Bend Radius/Minor Axis:	1.25 in
Min Bend Radius/Installation:	3.0 in

Standards

NEC Articles:	800
NEC/(UL) Specification:	CMR
CEC/C(UL) Specification:	CMR
ISO/IEC Compliance:	11801 ed 2.2 (2011) Class EA
CPR Euroclass:	Eca
Data Category:	Category 6A
ANSI Compliance:	S-116-732-2013 Category 6A, ANSI/NEMA WC-66 Category 6A
Telecommunications Standards:	ANSI/TIA-568-C.2 Category 6A
IEEE Specification:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
Other Specification:	Verified Channel/Category 6A
Other Standards:	C(UL)US CMR 90C OR (UL) CMR-LP (0.5A) OR CL3R-LP (0.5A)

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	Yes
EU CE Mark:	Yes
EU REACH SVHC Compliance (yyyy-mm-dd):	2017-07-10
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	No
Suitability - Oil Resistance:	No
Suitability - Outdoor:	No
Suitability - Sunlight Resistance:	No

Flammability, LSOH, Toxicity Testing

C(UL) Flammability:	FT4
UL Flammability:	UL 1666 Riser
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	10GX13

Part Number

Variants

Item #	Color
10GX12 0101000	Black
10GX12 0101500	Black
10GX12 0061000	Blue
10GX12 0062500	Blue
10GX12 0081000	Gray
10GX12 0051000	Green
10GX12 0031000	Orange
10GX12 0071000	Purple
10GX12 0021000	Red
10GX12 0091000	White
10GX12 0091500	White
10GX12 0041000	Yellow
10GX12 0041500	Yellow

Patent:	https://www.belden.com/resources/patents
---------	---

Product Notes

Notes:	Values above 625 MHz are for Engineering Information Only. 0.295" Cable Dimension per TIA 6@1 Equivalent Diameter. Print Includes Descending Footage/Meter Markings from Max. Put-Up Length to 0.
--------	---

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.