



Part Number: MDVO SC MODULE

MDVO SC Fiber Module

Product Description

MDVO SC Fiber Module. Available in several colors and fiber types.

Technical Specifications

Product Overview

Environmental Space:	Indoor
Suitable Applications:	FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room

Physical Characteristics (Overall)

Height:	0.63 m
Width:	0.63
Depth:	1.31
Front Connection:	Flush
Packaging:	10 units packaged in a plastic bag.
Weight:	0.013 lbs

Connectors

Materials

Description	Material	Type
Front Connection	Plastic - UL94V-0	SC-Simplex
Rear Connection	Plastic - UL94V-0	SC-Simplex

Temperature Range

Installation Temp Range:	-10°C To +60°C
Storage Temp Range:	-40°C To +70°C
Operating Temp Range:	-10°C To +60°C

Mechanical Characteristics

Footprint/Type:	MDVO
Connector/Hardware Retention:	20 lbs

Applicable Environmental and Other Programs

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2006-07-01
MII Order #39 (China RoHS):	EUP 50

Flammability, LS0H, Toxicity Testing

Safety Listing:	c(UL)us Listed
-----------------	----------------

Part Number

Related Parts:	Compatible MDVO-style Faceplate and Patch Panel, SC Fiber Patch Cord
----------------	--

Variants

Item #	Color
AX105698-AL	Almond
A0407004	Almond
AX105697-AL	Almond
AX104624-02	Almond
AX105698-BK	Black
A0407006	Black
AX105697-BK	Black
AX104624-04	Black
AX104624-01	Gray
A0407003	Gray
AX105698-GY	Gray
AX105697-GY	Gray
AX104624-12	Ivory
AX102596	Ivory
AX104624-03	White
A0407005	White
AX105698-WH	White
AX105697-WH	White

Product Notes

Included Parts:	Dust Caps
Notes:	For additional information about this product, visit our web site at http://www.belden.com

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.