



Part Number: 10GXS13

CAT6A 10GX Small Diameter, 4pr, UTP, LS-PVC Jkt, CMP

Product Description

CAT6A Enhanced (625MHz), 4-Unbonded-Pair, Plenum-CMP 105C OR CMP-LP (0.7A) OR CL3P-LP (0.7A), Premise Horizontal cable, 23 AWG Solid Bare Copper conductors, FEP insulation, patented EquiSpline™ & EquiBlock™ Technologies, ripcord, Flamarrest® jacket

Technical Specifications

Product Overview

Environmental Space:	Plenum
Suitable Applications:	Premise Horizontal Cable, 10 Gigabit Ethernet, Wireless, WIFI, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU Digital Audio, AES51, RS-422, Noisy Environments, PoE, PoE Plus

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
23	Solid	BC - Bare Copper	4

Conductor Count:	8
Total Number of Pairs:	4
Conductor Size:	23 AWG

Insulation

Material	
FEP - Fluorinated Ethylene Propylene	
Bonded-Pair:	N/A

Color Chart

Number	Color
1	White & Blue
2	White & Orange
3	White & Green
4	White & Brown

Outer Jacket Material

Material	Material Trade Name	Nominal Diameter	Ripcord	Separator Material
LS PVC - Low Smoke Polyvinyl Chloride	Flamarrest®	0.265 in	Yes	Patented EquiSpline Central Member

Construction and Dimensions

Cabling

Filler Material
Patented EquiSpline Central Member

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Max. DCR Unbalance	Max DCR Unbalanced Between Pairs [%]
82 Ohm/km	3 %	5 %

Capacitance

Max. Capacitance Unbalance	Nom. Mutual Capacitance
45 pF/100m	17 pF/ft

Delay

Frequency [MHz]	Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]	Typical Delay Skew
100 MHz	537.6 ns/100m	45 ns/100m	69 %	30 ns/100m

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. PSNEXT [dB]	Min. PSACR [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance	Min. PSANEXT	Min. PSAACRF	Min. TCL [dB]	Min. ELTCTL [dB]
1 MHz	2.1 dB/100m	75.3 dB	73.2 dB	74.8 dB	20.0 dB	100 ± 15 Ohm	105 ± 10 Ohm	75.0 dB	77.0 dB	40.0 dB	35.0 dB
4 MHz	3.8 dB/100m	66.3 dB	62.5 dB	62.8 dB	23.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	75.0 dB	76.2 dB	40.0 dB	23.0 dB
8 MHz	5.3 dB/100m	61.8 dB	56.5 dB	56.7 dB	24.5 dB	100 ± 15 Ohm	100 ± 15 Ohm	75.0 dB	70.1 dB	40.0 dB	16.9 dB
10 MHz	5.9 dB/100m	60.3 dB	54.4 dB	54.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	75.0 dB	68.2 dB	40.0 dB	15.0 dB
16 MHz	7.4 dB/100m	57.2 dB	49.8 dB	50.7 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	75.0 dB	64.1 dB	38.0 dB	10.9 dB
20 MHz	8.3 dB/100m	55.8 dB	47.5 dB	48.8 dB	25.0 dB	100 ± 15 Ohm	100 ± 15 Ohm	75.0 dB	62.2 dB	37.0 dB	9.0 dB
25 MHz	9.3 dB/100m	54.3 dB	45.0 dB	46.8 dB	24.3 dB	100 ± 15 Ohm	100 ± 15 Ohm	75.0 dB	60.2 dB	36.0 dB	7.0 dB
31.25 MHz	10.4 dB/100m	52.9 dB	42.5 dB	44.9 dB	23.6 dB	100 ± 15 Ohm	100 ± 10 Ohm	75.0 dB	58.3 dB	35.1 dB	5.1 dB
62.5 MHz	14.8 dB/100m	48.4 dB	33.6 dB	38.9 dB	21.5 dB	100 ± 15 Ohm	100 ± 10 Ohm	73.6 dB	52.3 dB	32.0 dB	
100 MHz	18.9 dB/100m	45.3 dB	26.4 dB	34.8 dB	20.1 dB	100 ± 15 Ohm	100 ± 10 Ohm	70.5 dB	48.2 dB	30.0 dB	
200 MHz	27.0 dB/100m	40.8 dB	13.8 dB	28.8 dB	18.0 dB	100 ± 22 Ohm	100 ± 10 Ohm	66.0 dB	42.2 dB	27.0 dB	
250 MHz	30.4 dB/100m	39.3 dB	9.0 dB	26.8 dB	17.3 dB	100 ± 32 Ohm	100 ± 10 Ohm	64.5 dB	40.2 dB	26.0 dB	
300 MHz	33.5 dB/100m	38.1 dB	4.6 dB	25.3 dB	16.8 dB	100 ± 32 Ohm	100 ± 10 Ohm	63.3 dB	38.7 dB	25.2 dB	
350 MHz	36.3 dB/100m	37.1 dB	0.8 dB	23.9 dB	16.3 dB	100 ± 32 Ohm	100 ± 10 Ohm	62.3 dB	37.3 dB	24.6 dB	
400 MHz	39.0 dB/100m	36.3 dB		22.8 dB	15.9 dB	100 ± 32 Ohm	100 ± 10 Ohm	61.5 dB	36.2 dB	24.0 dB	
450 MHz	41.5 dB/100m	35.5 dB		21.7 dB	15.5 dB	100 ± 32 Ohm	100 ± 10 Ohm	60.7 dB	35.1 dB	23.5 dB	
500 MHz	43.9 dB/100m	34.8 dB		20.8 dB	15.2 dB	100 ± 32 Ohm	100 ± 10 Ohm	60.0 dB	34.2 dB	23.0 dB	
550 MHz	46.2 dB/100m	33.2 dB		20.0 dB	14.9 dB	100 ± 32 Ohm	100 ± 10 Ohm	59.4 dB	33.4 dB		
600 MHz	48.4 dB/100m	32.6 dB		19.2 dB	14.7 dB	100 ± 32 Ohm	100 ± 10 Ohm	58.8 dB	32.6 dB		
625 MHz	49.5 dB/100m	32.4 dB		18.9 dB	14.5 dB	100 ± 32 Ohm	100 ± 10 Ohm	58.6 dB	32.3 dB		
750 MHz	54.7 dB/100m	32.2 dB		17.3 dB	14.0 dB			57.4 dB	30.7 dB		
860 MHz	58.9 dB/100m	31.3 dB		16.1 dB	13.6 dB			56.5 dB	29.5 dB		

Segregation class according EN50174-2: a

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

Installation Temp Range:	0°C To +50°C
UL Temp Rating:	105°C
Storage Temp Range:	-20°C To +75°C
Operating Temp Range:	-20°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	37 lbs/1000ft
Max Recommended Pulling Tension:	25 lbs
Min Bend Radius/Minor Axis:	1.25 in
Min Bend Radius/Installation:	2.75 in

Standards

NEC Articles:	800
NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
ISO/IEC Compliance:	11801 ed 2.2 (2011) Class EA
CPR Euroclass:	Eca
Data Category:	Category 6A
ANSI Compliance:	S-116-732-2013 Category 6A, ANSI/NEMA WC-66 Category 6A

Telecommunications Standards:	ANSI/TIA-568-C.2 Category 6A
IEEE Specification:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
Other Specification:	Verified Channel/Category 6A
Other Standards:	C(UL)US CMP 105C OR (UL) CMP-LP (0.7A) OR CL3P-LP (0.7A)

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	Yes
EU CE Mark:	Yes
EU REACH SVHC Compliance (yyyy-mm-dd):	2017-07-10
EU RoHS Compliance Date (yyyy-mm-dd):	2015-03-31
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	No
Suitability - Oil Resistance:	No
Suitability - Outdoor:	No
Suitability - Sunlight Resistance:	No

Flammability, LSOH, Toxicity Testing

C(UL) Flammability:	FT6
UL Flammability:	NFPA 262 Plenum (UL 910)
CSA Flammability:	FT6
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

Part Number

Non-Plenum Number:	10GXS12
--------------------	---------

Variants

Item #	Color
10GXS13 D151000	Blue
10GXS13 0081000	Gray
10GXS13 0021000	Red
10GXS13 0091000	White
10GXS13009A1000	White

Patent:	https://www.belden.com/resources/patents
---------	---

Product Notes

Notes:	Values above 625 MHz are for Engineering Information Only. Print Includes Descending Footage/Meter Markings from Max. Put-Up Length to 0.
--------	---

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.