



**Part Number: MEDIAFLEX SG ADAPTER BOX**

**MediaFlex 1-Gang Adapter Box**

**Product Description**

MediaFlex Surface Adapter Box, Single Gang

**Technical Specifications**

**Product Overview**

Environmental Space:	Indoor
Suitable Applications:	Compatible with a variety of modules that are suitable for use with Belden IBDN Systems 10GX, 4800, 3600, 2400, 1200, Fiber and Coax.

**Physical Characteristics (Overall)**

Height:	4.62 m
Width:	3.14
Depth:	1.75
Front Connection:	Flush
Packaging:	Individually shrink wrapped with plastic

**Connectors**

**Materials**

Description	Material
Adapter Box	Plastic - UL94V-0

**Temperature Range**

Installation Temp Range:	-10 to 60°C
Storage Temp Range:	-40 to 70°C
Operating Temp Range:	-10 to 60°C

**Mechanical Characteristics**

Footprint/Type:	Mediaflex
-----------------	-----------

**Applicable Environmental and Other Programs**

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2006-01-07
MII Order #39 (China RoHS):	EUP 50

**Flammability, LS0H, Toxicity Testing**

Safety Listing:	ACA, Bi-national Standard Listed
-----------------	----------------------------------

**Part Number**

Related Parts:	Compatible with MediaFlex Faceplates
----------------	--------------------------------------

**Variants**

Item #	Color
AX102481	Almond
AX102483	Black

AX102482	Electric White
AX102480	Gray
AX102485	Ivory
AX102484	White

## Product Notes

Included Parts:	adhesive foam tape, installation guide
Notes:	For proper installation refer to Installation Guide PX102064 included with the product or visit our web site at <a href="http://www.belden.com">http://www.belden.com</a>

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.