



Part Number: 2413F

CAT6+ Horizontal, 4pr, F/UTP, LS-PVC Jkt, CMP

Product Description

CAT6+ (350MHz), 4-Pair, F/UTP-foil shielded, Plenum-CMP, Premise Horizontal cable, 23 AWG solid bare copper conductors, FEP/PO insulation, patented X-spline, overall Beldfoil® shield, Flamarrest® jacket

Technical Specifications

Product Overview

Environmental Space:	Plenum
Suitable Applications:	Networking Horizontal Cable, HDBaseT, 1000Base-T (Gigabit Ethernet), 100Base-T (Fast Ethernet), 10Base-T (Ethernet), 100BaseVG, ANYLAN, 155ATM, 622ATM, ANSI.X3.263 FDDI TP-PMD, NTSC/PAL Component or Composite Video, AES/EBU, Digital Video, RS-422, Noisy Environments, 250 MHz Category 6

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
23	Solid	BC - Bare Copper	4

Conductor Count:	8
Total Number of Pairs:	4
Conductor Size:	23 AWG

Insulation

Material
FEP - Fluorinated Ethylene Propylene

Bonded-Pair:	N/A
--------------	-----

Color Chart

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum/Polyester	Beldfoil®	100 %	TC - Tinned Copper	24	Solid

Outer Jacket Material

Material	Material Trade Name	Nominal Diameter	Ripcord	Separator Material
LS PVC - Low Smoke Polyvinyl Chloride	Flamarrest®	0.310 in	No	Polyester Tape

Construction and Dimensions

Cabling

Filler
Patented Central X-Spline

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Max. DCR Unbalance
93.8 Ohm/km	5 %

Capacitance

Max. Capacitance Unbalance	Nom.Mutual Capacitance
330 pF/100m	14 pF/ft

Delay

Frequency [MHz]	Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
100 MHz	537.6 ns/100m	45 ns/100m	72 %

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Max./Min. Input Impedance (unFitted)	Max./Min. Fitted Impedance	Min. TCL [dB]	Min. ELTCTL [dB]
0.772 MHz	1.8 dB/100m	77.0 dB	77.0 dB	75.2 dB	76.2 dB	73.0 dB	70.0 dB	19.4 dB	100 +/- 15	100 ± 15 Ohm	40.0 dB	37.2 dB
1 MHz	2.0 dB/100m	75.3 dB	75.3 dB	73.3 dB	74.3 dB	70.8 dB	67.8 dB	20.0 dB	100 +/- 15	100 ± 15 Ohm	40.0 dB	35.0 dB
4 MHz	3.7 dB/100m	66.3 dB	66.3 dB	62.6 dB	63.6 dB	58.8 dB	55.8 dB	23.0 dB	100 +/- 15	100 ± 15 Ohm	40.0 dB	23.0 dB
8 MHz	5.2 dB/100m	61.8 dB	61.8 dB	56.6 dB	57.6 dB	52.7 dB	49.7 dB	24.5 dB	100 +/- 15	100 ± 15 Ohm	40.0 dB	16.9 dB
10 MHz	5.8 dB/100m	60.3 dB	60.3 dB	54.5 dB	55.5 dB	50.8 dB	47.8 dB	25.0 dB	100 +/- 15	100 ± 15 Ohm	40.0 dB	15.0 dB
16 MHz	7.4 dB/100m	57.2 dB	57.2 dB	49.9 dB	50.9 dB	46.7 dB	43.7 dB	25.0 dB	100 +/- 15	100 ± 15 Ohm	38.0 dB	10.9 dB
20 MHz	8.3 dB/100m	55.8 dB	55.8 dB	47.5 dB	48.5 dB	44.8 dB	41.8 dB	25.0 dB	100 +/- 15	100 ± 15 Ohm	37.0 dB	9.0 dB
25 MHz	9.3 dB/100m	54.3 dB	54.3 dB	45.1 dB	46.1 dB	42.8 dB	39.8 dB	24.3 dB	100 +/- 15	100 ± 15 Ohm	36.0 dB	7.0 dB
31.25 MHz	10.4 dB/100m	52.9 dB	52.9 dB	42.5 dB	43.5 dB	40.9 dB	37.9 dB	23.6 dB	100 +/- 15	100 ± 15 Ohm	35.1 dB	5.1 dB
62.5 MHz	15.0 dB/100m	48.4 dB	48.4 dB	33.4 dB	34.4 dB	34.9 dB	31.9 dB	21.5 dB	100 +/- 15	100 ± 15 Ohm	32.0 dB	
100 MHz	19.3 dB/100m	45.3 dB	45.3 dB	26.0 dB	27.0 dB	30.8 dB	27.8 dB	20.1 dB	100 +/- 15	100 ± 15 Ohm	30.0 dB	
155 MHz	24.6 dB/100m	42.4 dB	42.4 dB	17.9 dB	18.9 dB	27.0 dB	24.0 dB	19.5 dB	100 +/- 22	100 ± 15 Ohm	28.1 dB	
200 MHz	28.3 dB/100m	40.8 dB	40.8 dB	12.5 dB	13.5 dB	24.8 dB	21.8 dB	18.7 dB	100 +/- 22	100 ± 15 Ohm	27.0 dB	
250 MHz	32.1 dB/100m	39.3 dB	39.3 dB	7.2 dB	8.2 dB	22.8 dB	19.8 dB	18.0 dB	100 +/- 32	100 ± 15 Ohm	26.0 dB	
300 MHz	35.6 dB/100m	38.1 dB	36.1 dB	2.5 dB	1.5 dB	21.3 dB	18.3 dB	17.5 dB	100 +/- 32	100 ± 15 Ohm	25.2 dB	
350 MHz	38.9 dB/100m	37.1 dB	35.1 dB			19.9 dB	16.9 dB	17.0 dB	100 +/- 32	100 ± 15 Ohm	24.6 dB	
400 MHz	42.0 dB/100m	36.3 dB	34.3 dB			18.8 dB	15.8 dB	16.6 dB	100 +/- 32	100 ± 15 Ohm	24.0 dB	
450 MHz	45.0 dB/100m	35.5 dB	33.5 dB			17.7 dB	14.7 dB	16.2 dB	100 +/- 32	100 ± 15 Ohm	23.5 dB	
500 MHz	47.9 dB/100m	34.8 dB	32.8 dB			16.8 dB	13.8 dB	15.9 dB	100 +/- 32		23.0 dB	
550 MHz	50.6 dB/100m	34.2 dB	32.2 dB			16.0 dB	13.0 dB	15.6 dB	100 +/- 32		22.6 dB	

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

Installation Temp Range:	0°C To +50°C
UL Temp Rating:	75°C
Storage Temp Range:	-20°C To +75°C
Operating Temp Range:	-20°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	44 lbs/1000ft
Max Recommended Pulling Tension:	25 lbs
Min Bend Radius/Minor Axis:	1.0 in
Min Bend Radius/Installation:	2.25 in

Standards

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
ISO/IEC Compliance:	11801 ed 2.2 (2011) Class E
CPR Euroclass:	Eca
Data Category:	Category 6
ANSI Compliance:	S-116-732-2013 Category 6, ANSI/NEMA WC-66 Category 6
Telecommunications Standards:	ANSI/TIA-568-C.2 Category 6

IEEE Specification:	IEEE 802.3bt Type 1, Type 2, Type 3, Type 4
Third Party Performance Verification:	Category 6

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	Yes
EU CE Mark:	Yes
EU REACH SVHC Compliance (yyyy-mm-dd):	2017-07-10
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	No
Suitability - Oil Resistance:	No
Suitability - Outdoor:	No
Suitability - Sunlight Resistance:	No

Flammability, LS0H, Toxicity Testing

C(UL) Flammability:	FT6
UL Flammability:	NFPA 262 Plenum (UL 910)
CSA Flammability:	FT6
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

Part Number

Non-Plenum Number:	2412F
--------------------	-------

Variants

Item #	Color
2413F 0101000	Black
2413F D151000	Blue
2413F D15A500	Blue
2413F 0081000	Gray
2413F 0051000	Green
2413F 0031000	Orange
2413F 0021000	Red
2413F 0091000	White
2413F 009A500	White
2413F 0041000	Yellow

Patent:	https://www.belden.com/resources/patents
---------	---

Product Notes

Notes:	Values above 300 MHz are for Engineering Information Only. Shield is Bonded to Jacket Inner Wall for Electrical Stability. Print Includes Descending Footage Markings from Max. Put-Up Length to 0.
--------	---

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.