



**Part Number:** ATMM300

CAT3 Backbone, 300pr, Armor Shield, PVC Jkt, CMR

**Product Description**

CAT3, ATMM/ARMM, 300-Pair, F/UTP-foil shield, Riser-CMR, Premise Backbone Cable, 24 AWG solid bare copper conductors, foam polyolefin insulation with PVC skin, ripcord, corrugated aluminum shield bonded to overall PVC jacket

**Technical Specifications**

**Product Overview**

Environmental Space:	Riser
Suitable Applications:	Premise Backbone Cable

**Physical Characteristics (Overall)**

**Conductor**

AWG	Stranding	Material	No. of Pairs
24	Solid	BC - Bare Copper	300

Conductor Count:	600
Total Number of Pairs:	300
Conductor Size:	24 AWG

**Insulation**

Material
FPO - Foam Polyolefin

Bonded-Pair:	N/A
--------------	-----

**Color Chart**

Number	Color
1	White & Blue
2	White & Orange
3	White & Green
4	White & Brown
5	White & Slate
6	Red & Blue
7	Red & Orange
8	Red & Green
9	Red & Brown
10	Red & Slate
11	Black & Blue
12	Black & Orange
13	Black & Green
14	Black & Brown
15	Black & Slate
16	Yellow & Blue
17	Yellow & Orange
18	Yellow & Green
19	Yellow & Brown
20	Yellow & Slate

21	Violet & Blue
22	Violet & Orange
23	Violet & Green
24	Violet & Brown
25	Violet & Slate
Group One Binder	White/Blue
Group Two Binder	White/Orange
Group Three Binder	White/Green
Group Four Binder	White/Brown
Group Five Binder	White/Slate
Group Six Binder	Red/Blue
Group Seven Binder	Red/Orange
Group Eight Binder	Red/Green
Group Nine Binder	Red/Brown
Group Ten Binder	Red/Slate
Group Eleven Binder	Black/Blue
Group Twelve Binder	Black/Orange

#### Color Chart 2

Number
1
2
3
4
5
6
7
8
9
10
11
12

#### Outer Shield Material

Material
Corrugated Aluminum

#### Outer Jacket Material

Material	Nominal Diameter	Ripcord
PVC - Polyvinyl Chloride	1.320 in	Yes

## Construction and Dimensions

---

#### Armor

Type of Armor	Material	Thickness of Armoring Tape
Corrugated	Aluminum	.008 in

## Electrical Characteristics

---

#### Conductor DCR

Max. Conductor DCR	Max. DCR Unbalance
93.8 Ohm/km	5 %

#### Capacitance

Max. Capacitance Unbalance	Nom. Mutual Capacitance
330 pF/100m	17 pF/ft

#### Delay

Frequency [MHz]	Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
16 MHz	543 ns/100m	45 ns/100m	68 %

#### High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. RL (Return Loss) [dB]	Max./Min. Fitted Impedance
-----------------	-----------------------------------	----------------	------------------	---------------	-----------------	----------------------------	----------------------------

0.772 MHz	2.2 dB/100m	47.0 dB	43.0 dB	50.1 dB	46.1 dB		100 +/- 15
1.0 MHz	2.6 dB/100m	45.0 dB	41.0 dB	47.8 dB	43.8 dB	12.0 dB	100 +/- 15
4.0 MHz	5.6 dB/100m	36.0 dB	32.0 dB	36.0 dB	32.0 dB	12.0 dB	100 +/- 15
8.0 MHz	8.5 dB/100m	31.0 dB	27.0 dB	28.3 dB	24.3 dB	12.0 dB	100 +/- 15
10.0 MHz	9.7 dB/100m	30.0 dB	26.0 dB	26.2 dB	22.2 dB	12.0 dB	100 +/- 15
16.0 MHz	13.1 dB/100m	27.0 dB	23.0 dB	20.1 dB	16.1 dB	10.0 dB	100 +/- 15

#### Voltage

<b>UL Voltage Rating</b>
300 V RMS

#### Temperature Range

Installation Temp Range:	-20°C To +60°C
UL Temp Rating:	60°C
Storage Temp Range:	-30°C To +60°C
Operating Temp Range:	-30°C To +60°C

#### Mechanical Characteristics

Bulk Cable Weight:	1104 lbs/1000ft
Max Recommended Pulling Tension:	1800 lbs
Min Bend Radius/Minor Axis:	13.25 in
Min Bend Radius/Installation:	26.5 in

#### Standards

NEC/(UL) Specification:	CMR
CEC/C(UL) Specification:	CMR
Data Category:	Category 3
ANSI Compliance:	S-90-661-2012 Category 3, ANSI/NEMA WC-63.1 Category 3
Telecommunications Standards:	ANSI/TIA-568-C.2 Category 3

#### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	Yes
EU CE Mark:	Yes
EU REACH SVHC Compliance (yyyy-mm-dd):	2017-07-10
EU RoHS Compliance Date (yyyy-mm-dd):	2005-08-19
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

#### Suitability

Suitability - Aerial:	No
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	No
Suitability - Oil Resistance:	No
Suitability - Outdoor:	No
Suitability - Sunlight Resistance:	No

#### Flammability, LS0H, Toxicity Testing

C(UL) Flammability:	FT4
UL Flammability:	UL 1666 Riser
UL voltage rating:	300 V RMS

#### Plenum/Non-Plenum

Plenum (Y/N): No

## Part Number

### Variants

Item #	Color
ATMM300 008CUT	Gray
ATMM300 008CUT	Gray

Patent: <https://www.belden.com/resources/patents>

## Product Notes

Notes: Print Includes Descending Footage/Meter Markings. Corrugated Aluminum Armor Bonded to the Jacket.

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.