

Part Number: FX Brilliance OM1 LC

FX Brilliance OM1 LC Connector



Product Description

FX Brilliance Universal LC Field Installable Connector, Multimode, OM1, Beige Housing, 1/Pack, with support for 250 um (using Breakout kit), 900 um, 2 mm and 3 mm fiber (using jacketed boots). Includes 900 um boot, other accessories (Breakout Kit & jacketed boots) sold separately.

Technical Specifications

Product Overview

Part Number:	AX105200
Environmental Space:	Indoor
Suitable Applications:	Field-termination of fiber optic cables within Patch Panels, Distribution Frames, Workstation Outlets for FTTD (Fiber to the Desk), drops for FTTH (Fiber to the home) and MDU (Multiple Dwelling Units).

Construction

Fiber Cable Construction

Fiber Type	
OM1	
Fiber Type:	OM1

Buffer Specification

Fiber Type	
OM1	
Weight:	.003 kg

Optical Characteristics

Mechanical Specifications

Test	TIA 568.3-D (MM)
Intermateability Requirement	Compliant with TIA/EIA-604-10A (FOCIS 10)
Operating Temp Range	-40°C to +75°C
Storage Temp Range	-40°C to +60°C
Durability	500 cycles, less than 0.2 dB change, FOTP-21

Mechanical Characteristics

Maximum Insertion Loss:	0.50 dB
Typical Insertion Loss:	0.20 dB
Minimum Reflectance @ 1550nm:	-30 dB
Termination Style:	Mechanical
Interconnection Compatibility:	Compliant with TIA/EIA-604-10A (FOCIS 10)
Durabilities@Termination1:	500 cycles, less than 0.2 dB change, FOTP-21

Temperature Range

Operating Temp Range:	-40°C to +75°C
Storage Temp Range:	-40°C to +60°C

Product Material

Materials

Description	Material	Color
Boot	Rubber	Black
Protective Ferrule Cap	Plastic	Opaque
Connector Body	Plastic	Beige
Ferrule	Ceramic	

Standards

Telecommunications Standards:	TIA 568-C.3
EU Directive 2011/65/EU (ROHS II):	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2006-07-01
MII Order #39 (China RoHS):	EUP 50
Safety Listing:	ACA

Additional Notes

Packaging:	Individually packaged in a sealed plastic bag. Twenty-five (25) connectors come in a dust and moisture resistant blister package.
Included Parts:	900 µm boot, protective ferrule cap
Related Parts:	FX Brilliance Precision Installation Kit, Boots for 2mm and 3mm Jacketed Fiber, 250um to 900um break out kits.
Notes:	Refer to Installation Guide PX105234 for installation procedures. Fiber can be reterminated up to 5 times with the same connector.

History

Variants

Item #	Color	Packaging
AX105200-S1	Beige	1-Pack
AX105200-B25	Beige	25-Pack

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.