

Cisco Catalyst 2960-C and 3560-C Series Compact Switches

Cisco® Catalyst® compact switches (Figure 1) easily extend an intelligent, fully managed Cisco Catalyst wired switching infrastructure, including end-to-end IP and Borderless Network services, with a single Ethernet cable or fiber from the wiring closet. These attractive, small form-factor Gigabit and Fast Ethernet switches are ideal for connecting multiple devices on the retail sales floor and in classrooms, hotels, and factories and for extending wireless LAN networks: wherever space is at a premium and multiple cable runs could be challenging.

Cisco Catalyst 2960-C and 3560-C Series Compact Switches highlights:

- Extend a highly secure, intelligent, managed Cisco Catalyst infrastructure with a single Ethernet cable or fiber from the wiring closet
- Support for advanced security and services, including voice, video, and Cisco Borderless Network services, to remote endpoints
- Power over Ethernet (PoE) pass-through enables the compact switch to draw power from the wiring closet and pass it to end devices (selected models)
- Attractive, small form factor and fanless operation fit in confined spaces where multiple cable runs could be challenging
- Easy to deploy, manage and extend the network loop free
- Enhanced limited lifetime hardware warranty

Figure 1. Cisco Catalyst Compact Switches



Cisco Catalyst 2960-C Series Compact Switches

Cisco Catalyst 3560-C Series Compact Switches

Switch Configurations

Table 1 compares switch models.

Table 1. Available Cisco Catalyst Compact Switch models

Model	Ethernet Ports	PoE Output Ports	Available PoE Power	Uplinks	MACsec
2960C-8TC-L	8 x 10/100 Fast Ethernet	N/A		2 x 1G copper or 2 x 1G SFP	N/A
2960C-8TC-S	8 x 10/100 Fast Ethernet	N/A		2 x 1G copper or 2 x 1G SFP	N/A
2960CPD-8TT-L	8 x 10/100 Fast Ethernet	N/A		2 x 1G (PoE+ input)	N/A
2960C-8PC-L	8 x 10/100 Fast Ethernet	8 PoE	124W	2 x 1G copper or 2 x 1G SFP	N/A
2960CPD-8PT-L	8 x 10/100 Fast Ethernet	8 PoE	Up to 30.8W ¹	2 x 1G (PoE+ input)	N/A
2960C-12PC-L	12 x 10/100 Fast Ethernet	12 PoE	124W	2 x 1G copper or 2 x 1G SFP	N/A
2960CG-8TC-L	8 x 10/100/1000 Gigabit Ethernet	N/A		2 x 1G copper or 2 x 1G SFP	N/A
3560C-8PC-S	8 x 10/100 Fast Ethernet	8 PoE+	124W	2 x 1G copper or 2 x 1G SFP	N/A
3560C-12PC-S	12 x 10/100 Fast Ethernet	12 PoE+	124W	2 x 1G copper or 2 x 1G SFP	N/A
3560CG-8TC-S	8 x 10/100/1000 Gigabit Ethernet	N/A		2 x 1G copper or 2 x 1G SFP	Yes
3560CG-8PC-S	8 x 10/100/1000 Gigabit Ethernet	8 PoE+	124W	2 x 1G copper or 2 x 1G SFP	Yes
3560CPD-8PT-S	8 x 10/100/1000 Gigabit Ethernet	8 PoE	Up to 23.8W ²	2 x 1G (PoE+ input)	Yes

Cisco Catalyst 2960-C and 3560-C Series Software

Cisco Catalyst 2960-C Series compact switches ship with the LAN Base version of Cisco IOS[®] Software, as available on other Cisco Catalyst 2960 Series Switches. Similarly, Cisco Catalyst 3560-C compact switches ship with the IP Base version of Cisco IOS Software, as with other 3560 Series switches. Neither series of compact switches can be upgraded.

Cisco Catalyst 2960-C switches deliver advanced Layer 2 switching with intelligent Layer 2 through 4 services for the network edge, such as voice, video, and wireless LAN services. The IP Base feature set on Cisco Catalyst 3560-C switches adds baseline enterprise services, including support for routed access, Cisco TrustSec[®], media access control security (MACsec), and other Cisco Borderless Network services.

The LAN Base feature set offers enhanced intelligent services that include comprehensive Layer 2 features. The IP Base feature set provides baseline enterprise services in addition to all LAN Base features. IP Base also includes the support for routed access, MACsec, and Open Shortest Path First (OSPF).

¹ Using UPOE uplinks.

² Using UPOE uplinks.

Applications

Cisco Borderless Networks and Access Switching

Borderless Networks, a Cisco next-generation architecture, deliver the new workspace experience, connecting anyone, anywhere, using any device, to any resource - securely, reliably, transparently. The Cisco Borderless Networks architecture addresses primary IT and business challenges to help create a truly borderless experience by bringing interactions closer to the employee and customer. Innovations in switching help organizations deliver ease of operation, green efficiency, security, and performance to accelerate the way IT delivers and scales those services on the network.

Cisco Compact Switches for Retail

Major retailers are increasingly moving customer-facing IP-based applications and services to the middle of the sales floor. A typical transaction area on the floor will often include multiple point-of-sale terminals, card readers, IP phones, and printers. Free-standing kiosks, which allow customers to access online catalogs with click-to-chat capabilities and other applications, are being deployed. Cisco Catalyst compact switches extend fully managed IP services, including end-to-end PCI-compliant solutions, to the floor with a single Ethernet cable or fiber. Because of their quiet operation, attractive appearance, and flexible mounting options, they are ideally suited for mounting in confined spaces on the floor.

Cisco Compact Switches for Education

Video and distance learning applications have become a common part of the curriculum for K-12 and higher education. Support for IP phones and secure wired and wireless connectivity in the classroom are also common requirements. Yet schools and universities must often work within limited budgets and aging facilities, making wiring runs from a central point in the building to multiple devices in the classroom cost prohibitive. Cisco Catalyst compact switches extend fully managed IP services to the classroom with a single Ethernet cable or fiber. Quiet operation and flexible mounting options make them ideally suited for classrooms or confined areas nearby.

Cisco Compact Switches Extend Enterprise Networks

Enterprises often look to extend the reach of their networks - to bring wired connectivity to more employees and to support new wireless deployments. Running additional Ethernet cables for individual devices might be impractical, but the same security, services, and management must be supported. Cisco Catalyst 2960-C and 3560-C Series compact switches extend the wired Cisco access infrastructure, 8 or 12 ports at a time, with a single Ethernet cable or fiber, all while delivering the same services as the Cisco Catalyst switches in the wiring closet. PoE, quiet operation, and flexible mounting options allow placement in confined spaces.

Cisco Networked Sustainability: Good for Business, Better for Environment

- **PoE pass-through** gives the ability to power PoE end devices through drawing PoE from the wiring closet. The Cisco Catalyst 3560CPD-8PT-S and 2960CPD-8PT-L have eight downlink ports with two PoE input ports that allow it to be powered by another switch. These switches do not need a power supply and receives power over the uplink from an upstream PoE or Cisco Universal Power over Ethernet (Cisco UPOE™) device, providing deployment flexibility and availability. These switches are ideal for wiring and space-constrained applications.

- **Cisco EnergyWise** is an innovative architecture, added to the Cisco Catalyst 3560-C and 2960-C Series compact switches, that enables the measurement of power consumption in the network infrastructure and network-attached devices. EnergyWise encompasses a highly intelligent network-based approach to communicate messages that measure and control energy between network devices and endpoints. The network discovers Cisco EnergyWise-manageable devices, monitors their power consumption, and takes action based on business rules to reduce power consumption.
- **Efficient switch operation:** Cisco Catalyst 3560-C and 2960-C Series compact switches use hardware components created by Cisco providing optimum power saving, low-power operations for industry best-in-class power management, and power consumption capabilities. The Cisco Catalyst 3560-C ports are capable of reduced power modes so that ports not in use can move into a lower power utilization state.
- **IEEE 802.3at or PoE+:** Available on the Cisco Catalyst 3560-C is the latest in PoE technology, allowing capable devices to be powered with power output up to 30W per port. Table 2 outlines switch models and power capacity for the Cisco Catalyst 3560-C and 2960-C Series compact switches.

Table 2. Switch PoE and PoE+ Power Capacity

Switch Model	Powering Options	Available PoE Power (W)
WS-C2960CPD-8PT-L	1 PoE Uplink	0W
	2 PoE Uplinks	7W
	1 PoE+ Uplinks	7W
	1 PoE+ and 1 PoE Uplinks	15.4W
	2 PoE+ Uplinks	22.4W
	1 Cisco UPOE Uplink	30.8W
	Auxiliary Input	22.4W (30.8W ⁽¹⁾)
WS-C3560CPD-8PT-S	1 PoE+	0W
	2 PoE+	15.4W
	1 Cisco UPOE Uplink	23.8W
	Auxiliary Input	15.4W (23.8W ⁽¹⁾)
WS-C2960C-8PC-L	Internal Power Supply	124W
WS-C2960C-12PC-L	Internal Power Supply	124W
WS-C3560C-12PC-S	Internal Power Supply	124W
WS-C3560C-8PC-S	Internal Power Supply	124W
WS-C3560CG-8PC-S	Internal Power Supply	124W

(¹) When the Auxiliary AC input is used as a backup to a Cisco UPOE powered switch

Cisco Operational Excellence: Reducing Operating Costs

Cisco Catalyst 3560-C and 2960-C Series compact switches make deployment easy: reduce switch installation, configuration, troubleshooting time, and operational costs.

- **Cisco Catalyst Smart Operations** is a set of features to enhance operational excellence:
 - **Cisco Smart Install** is a transparent plug-and-play technology to configure the Cisco IOS Software image and switch configuration without user intervention. Smart Install utilizes dynamic IP address allocation and the assistance of other switches to facilitate installation, providing transparent network plug and play.

- **Cisco Smart Configuration** provides a single point of management for a group of switches and in addition adds the ability to archive and back up configuration files to a file server or switch. A group of switches can be upgraded or configured from a single point in the network.
- **Cisco Auto SmartPorts** provides automatic configuration as devices connect to the switch port, allowing autodetection and plug and play of the device onto the network. It configures the port with predefined configurations encapsulating years of Cisco networking expertise, including security, IP telephony, availability, QoS, and manageability features with minimal effort and expertise.
- **USB file storage and console** for file backup, distribution, and simplified operations allow the user to back up and boot from a USB device and allow for Mini USB console access along with traditional RS-232 console connectivity.
- **Cisco Smart Troubleshooting** is an extensive array of debug diagnostic commands and system health checks within the switch, including Generic Online Diagnostics (GOLD).
- **Easy-to-Use Deployment and Control Features**
 - **Automatic QoS (AutoQoS)** simplifies QoS configuration in voice over IP (VoIP) networks by issuing interface and global switch commands to detect Cisco IP phones, classify traffic, and help enable egress queue configuration.
 - **Dynamic Host Configuration Protocol (DHCP)** autoconfiguration of multiple switches through a boot server eases switch deployment.
 - **Auto-Negotiation** on all ports automatically selects half- or full-duplex transmission mode to optimize bandwidth.
 - **Dynamic Trunking Protocol (DTP)** facilitates dynamic trunk configuration across all switch ports.
 - **Port Aggregation Protocol (PAgP)** automates the creation of Cisco Fast EtherChannel groups or Gigabit EtherChannel groups to link to another switch, router, or server.
 - **Link Aggregation Control Protocol (LACP)** allows the creation of Ethernet channeling with devices that conform to IEEE 802.3ad. This feature is similar to Cisco EtherChannel technology and PAgP.
 - **Automatic Media-Dependent Interface Crossover (MDIX)** automatically adjusts transmit and receive pairs if an incorrect cable type (crossover or straight-through) is installed.
 - **Unidirectional Link Detection Protocol (UDLD)** and Aggressive UDLD allow unidirectional links caused by incorrect fiber-optic wiring or port faults to be detected and disabled on fiber-optic interfaces.
 - **Switching Database Manager (SDM)** templates for access, routing, and VLAN deployment allow the administrator to easily maximize memory allocation to the desired features based on deployment-specific requirements.
 - **Local Proxy Address Resolution Protocol (ARP)** works in conjunction with Private VLAN Edge to minimize broadcasts and maximize available bandwidth.
 - **Internet Group Management Protocol (IGMP)** Snooping for IPv4 and IPv6 MLD v1 and v2 Snooping provide fast client joins and leaves of multicast streams and limit bandwidth-intensive video traffic to only the requestors.
 - **Multicast VLAN Registration (MVR)** continuously sends multicast streams in a multicast VLAN while isolating the streams from subscriber VLANs for bandwidth and security reasons.
 - **Per-port Broadcast, Multicast, and Unicast Storm Control** prevents faulty end stations from degrading overall systems performance.

- **Voice VLAN** simplifies telephony installations by keeping voice traffic on a separate VLAN for easier administration and troubleshooting.
- **Cisco VLAN Trunking Protocol (VTP)** supports dynamic VLANs and dynamic trunk configuration across all switches.
- **Remote Switch Port Analyzer (RSPAN)** allows administrators to remotely monitor ports in a Layer 2 switch network from any other switch in the same network.
- For enhanced traffic management, monitoring, and analysis, the **Embedded Remote Monitoring (RMON)** software agent supports four RMON groups (history, statistics, alarms, and events).
- **Layer 2 Traceroute** eases troubleshooting by identifying the physical path that a packet takes from source to destination.
- **Trivial File Transfer Protocol (TFTP)** reduces the cost of administering software upgrades by downloading from a centralized location.
- **Network Timing Protocol (NTP)** provides an accurate and consistent timestamp to all intranet switches.

Network Management

The Cisco Catalyst 3560-C and 2960-C Series Switches offer a superior CLI for detailed configuration and administration. These switches are also supported in the full range of Cisco network management solutions.

Cisco Prime Infrastructure

Cisco Prime™ network management solutions provide comprehensive network lifecycle management. Cisco Prime Infrastructure provides an extensive library of easy-to-use features to automate the initial and day-to-day management of your Cisco network. Cisco Prime integrates hardware and software platform expertise and operational experience into a powerful set of workflow-driven configuration, monitoring, troubleshooting, reporting, and administrative tools, including:

- Support for new technologies and services from initial deployment to day-to-day administration and management, such as EnergyWise, identity, Cisco Auto Smartports, Cisco Smart Install, and much more
- Configuration management tools built from Cisco experience and Cisco Validated Design recommendations
- Monitoring and troubleshooting capabilities that incorporate Cisco hardware best practices and diagnostics features
- Automation in managing hardware inventories, security vulnerabilities (PSIRTS), and platform end-of-life and support cycles

For detailed information about Cisco Prime, visit <http://www.cisco.com/go/prime>.

Cisco Network Assistant

A PC-based network management application designed for small and medium-sized business (SMB) networks with up to 250 users, Cisco Network Assistant offers centralized network management and configuration capabilities. This application also features an intuitive GUI where users can easily apply common services across Cisco switches, routers, and access points.

For detailed information about Cisco Network Assistant, visit <http://www.cisco.com/go/cna>.

Enhanced Work Space Experience for End Users

Borderless Security

The Cisco Catalyst compact switches provide superior Layer 2 threat defense capabilities for mitigating man-in-the-middle attacks (such as MAC, IP, and ARP spoofing). TrustSec, a primary element of Borderless Security Architecture, helps enterprise customers secure their networks, data and resources with policy-based access control, identity and role-aware networking, pervasive integrity, and confidentiality.

The borderless security is enabled by the following feature sets in the Cisco Catalyst 3560-C and 2960-C Series compact switches:

- Threat defense
- Cisco TrustSec
- Other advanced security features

Threat Defense

Cisco Integrated Security Features are an industry-leading solution available on Cisco Catalyst switches that proactively protects your critical network infrastructure. Delivering powerful, easy-to-use tools to effectively prevent the most common and potentially damaging Layer 2 security threats, Cisco Integrated Security Features provide robust security throughout the network. Cisco Integrated Security Features include Port Security, DHCP Snooping, Dynamic ARP Inspection, and IP Source guard.

- **Port Security** secures the access to an access or trunk port based on MAC address. It limits the number of learned MAC addresses to deny MAC address flooding.
- **DHCP Snooping** prevents malicious users from spoofing a DHCP server and sending out bogus addresses. This feature is used by other primary security features to prevent a number of other attacks such as ARP poisoning.
- **Dynamic ARP Inspection (DAI)** helps ensure user integrity by preventing malicious users from exploiting the insecure nature of the ARP protocol.
- **IP source guard** prevents a malicious user from spoofing or taking over another user's IP address by creating a binding table between the client's IP and MAC address, port, and VLAN.

Cisco TrustSec

TrustSec secures access to the network, enforces security policies, and delivers standard-based security solutions such as 802.1X enabling secure collaboration and policy compliance. TrustSec capabilities reflect Cisco thought leadership, innovations, and commitment to customer success. These new capabilities include:

- **IEEE 802.1AE MACsec** with prestandard 802.1X-REV Key management: industry's first fixed switches with prestandard 802.1X-Rev key management. Available on Cisco Catalyst 3560-C Series Switches, MACsec provides Layer 2, line rate Ethernet data confidentiality and integrity on host facing ports, protecting against man-in-the-middle attacks (snooping, tampering, and replay).
- **Flexible authentication** that supports multiple authentication mechanisms including 802.1X, MAC Authentication Bypass, and web authentication using a single, consistent configuration.
- **Open mode** that creates a user friendly environment for 802.1X operations.
- **Integration of device profiling technology and guest access** handling with Cisco switching to significantly improve security while reducing deployment and operational challenges.

- **RADIUS Change of Authorization and Downloadable ACLs** for comprehensive policy management capabilities.
- **802.1X Supplicant with Network Edge Access Transport (NEAT)** enables extended secure access where compact switches in the conference rooms have the same level of security as switches inside the locked wiring closet.

Other Advanced Security Features

Other Advanced Security features include but are not limited to:

- **Private VLAN Edge** provides security and isolation between switch ports, which helps ensure that users cannot snoop on other users' traffic.
- **Multidomain Authentication** allows an IP phone and a PC to authenticate on the same switch port while placing them on appropriate voice and data VLAN.
- **Port-Based ACLs** for Layer 2 interfaces allow security policies to be applied on individual switch ports.
- **Secure Shell (SSH) Protocol, Kerberos, and Simple Network Management Protocol Version 3 (SNMPv3)** provide network security by encrypting administrator traffic during Telnet and SNMP sessions. SSH Protocol, Kerberos, and the cryptographic version of SNMPv3 require a special cryptographic software image because of U.S. export restrictions.
- Bidirectional data support on the **Switched Port Analyzer (SPAN)** port allows Cisco Intrusion Detection System (IDS) to take action when an intruder is detected.
- **TACACS+ and RADIUS Authentication** facilitates centralized control of the switch and restricts unauthorized users from altering the configuration.
- **MAC Address Notification** allows administrators to be notified of users added to or removed from the network.
- **Multilevel Security on Console Access** prevents unauthorized users from altering the switch configuration.
- **Bridge Protocol Data Unit (BPDU) Guard** shuts down Spanning Tree PortFast-enabled interfaces when BPDUs are received to avoid accidental topology loops.
- **Spanning Tree Root Guard (STRG)** prevents edge devices not in the network administrator's control from becoming Spanning Tree Protocol root nodes.
- **IGMP Filtering** provides multicast authentication by filtering out nonsubscribers and limits the number of concurrent multicast streams available per port.
- **Dynamic VLAN Assignment** is supported through implementation of VLAN Membership Policy Server client capability to provide flexibility in assigning ports to VLANs. Dynamic VLAN facilitates the fast assignment of IP addresses.

Table 3 shows switch hardware information.

Table 3. Cisco Catalyst 3560-C and 2960-C Series Compact Switch Hardware

Description	Specification	Cisco Catalyst 3560-C	Cisco Catalyst 2960-C	
Performance	Forwarding Bandwidth	10 Gbps	10 Gbps	
	Flash memory	64 MB	64 MB	
	Memory DRAM	128 MB	128 MB	
	Max VLANs	1005	255*	
	VLAN IDs	4000	4000	
	Maximum transmission unit (MTU)	Up to 9000 bytes	Up to 9000 bytes	
	Jumbo frames	9018 bytes	9018 bytes	
	Forwarding rate 64 Byte Packet Cisco Catalyst 3560-C			
	WS-C3560CG-8PC-S	14.9 mpps		
	WS-C3560CPD-8PT-S	14.9 mpps		
	WS-C3560CG-8TC-S	14.9 mpps		
	WS-C3560C-8PC-S	4.2 mpps		
	WS-C3560C-12PC-S	4.8 mpps		
	Forwarding rate 64 Byte Packet Cisco Catalyst 2960-C			
	WS-C2960CG-8TC-L	14.9 mpps		
	WS-C2960CPD-8PT-L	4.2 mpps		
	WS-C2960CPD-8TT-L	4.2 mpps		
	WS-C2960C-8PC-L	4.2 mpps		
	WS-C2960C-8TC-L	4.2 mpps		
	WS-C2960C-8TC-S	4.2 mpps		
	WS-C2960C-8PT-L	4.2 mpps		
	WS-C2960C-12PT-L	4.8 mpps		
Resource Cisco Catalyst 3560-C, 2960-C				
See the release notes for the SDM Templates for 3560-C and 2960-C.				
<ul style="list-style-type: none"> • 2960-C: http://www.cisco.com/en/US/docs/switches/lan/catalyst2960c_3560c/software/release/12.2_55_ex/release/notes/ol23942.html. • 3560-C: http://www.cisco.com/en/US/docs/switches/lan/catalyst2960c_3560c/software/release/12.2_55_ex/release/notes/ol24071.html. 				
Connectors and cabling	Cisco Catalyst 3560-C and 2960-C with SFP-based ports:			
	<ul style="list-style-type: none"> • 10BASE-T ports: RJ-45 connectors, 2-pair Category 3, 4, or 5 unshielded twisted-pair (UTP) cabling • 100BASE-TX ports: RJ-45 connectors, 2-pair Category 5 UTP cabling • 1000BASE-T ports: RJ-45 connectors, 4-pair Category 5 UTP cabling • 1000BASE-T SFP-based ports: RJ-45 connectors, 4-pair Category 5 UTP cabling • 1000BASE-SX -LX/LH, -ZX, -BX, -T, -FX*, and CWDM SFP-based ports: LC fiber connectors (single/multimode fiber) • 100BASE-LX, -BX, -FX: SFP-based ports: LC fiber connectors (single/multimode fiber) 			
*GLC-T and GLC-GE-100FX are not supported				
For the complete list of SFPs supported, see http://www.cisco.com/en/US/docs/interfaces_modules/transceiver_modules/compatibility/matrix/OL_6981.html .				

Description	Specification			
Power connectors	<ul style="list-style-type: none"> Customers can provide power to a switch by using the internal power supply. The connector is located at the back of the switch. The internal power supply is an autoranging unit (3560CPD-8PT-S, 2960CPD-8TT-L, 2960CPD-8PT-L do not require a power supply). The internal power supply supports input voltages between 100 and 240VAC. Use the supplied AC power cord to connect the AC power connector to an AC power outlet. <p>Note: The Cisco Catalyst 3560CPD-8PT-S, 2960CPD-8PT-L and 2960CPD-8TT-L have an option for an external power adapter if desired.</p>			
Indicators	<ul style="list-style-type: none"> Per-port status: Link integrity, disabled, activity, speed, full-duplex System status: System, RPS, link status, link duplex, link speed 			
Dimensions (H x W x D)	Cisco Catalyst 2960-C	Inches	Centimeters	
	WS-C2960CPD-8TT-L	1.75x10.6x6.8	4.44x26.9x17.2	
	WS-C2960CPD-8PT-L	1.75x10.6x6.8	4.44x26.9x17.2	
	WS-C2960CG-8TC-L	1.75x10.6x8.4	4.44x26.9x21.3	
	WS-C2960C-8TC-L	1.75x10.6x8.4	4.44x26.9x21.3	
	WS-C2960C-8TC-S	1.75x10.6x8.4	4.44x26.9x21.3	
	WS-C2960C-8PC-L	1.75x10.6x9.4	4.44x26.9x23.8	
	WS-C2960C-12PC-L	1.75x10.6x9.4	4.44x26.9x23.8	
	Cisco Catalyst 3560-C	Inches	Centimeters	
	WS-C3560CG-8TC-S	1.75x10.6x8.4	4.44x26.9x21.3	
	WS-C3560CG-8PC-S	1.75x10.6x9.4	4.44x26.9x23.8	
	WS-C3560CPD-8PT-S	1.75x10.6x7.6	4.44x26.9x19.4	
	WS-C3560C-8PC-S	1.75x10.6x9.4	4.44x26.9x21.3	
	WS-C3560C-12PC-S	1.75x10.6x9.4	4.44x26.9x21.3	
	Weight	Cisco Catalyst 2960-C	Pounds	Kilograms
		WS-C2960CPD-8TT-L	2.4	1.08
		WS-C2960CPD-8PT-L	2.4	1.08
WS-C2960C-8TC-L		2.8	1.27	
WS-C2960C-8TC-S		2.8	1.27	
WS-C2960CG-8TC-L		3.0	1.35	
WS-C2960C-8PC-L		4.1	1.86	
WS-C2960C-12PC-L		4.1	1.86	
Cisco Catalyst 3560-C		Pounds	Kilograms	
WS-C3560CG-8TC-S		3.0	1.35	
WS-C3560CPD-8PT-S		3.3	1.50	
WS-C3560C-8PC-S		4.1	1.86	
WS-C3560C-12PC-S		4.1	1.86	
WS-C3560CG-8PC-S	4.3	1.92		

Description	Specification				
Environmental ranges		Cisco Catalyst 3560-C		Cisco Catalyst 2960-C	
	Operating [*] temperature up to 5000 ft (1524 m)	-5°C to +45°C**	+23°F to +113°F	-5°C to +45°C**	+23°F to +113°F
	Operating [*] temperature up to 10,000 ft (3048 m)	-5°C to +45°C	+23°F to +113°F	-5°C to +45°C	+23°F to +113°F
	Storage temperature up to 15,000 ft (4572 m)	-25°C to +70°C	-13°F to +158°F	-25°C to +70°C	-13°F to +158°F
	Operating altitude	Up to 3048 m	Up to 10,000 ft	Up to 3048 m	Up to 10,000 ft
	Storage altitude	Up to 4000 m	Up to 15,000 ft	Up to 4000 m	Up to 15,000 ft
	Operating relative humidity	5% to 95% noncondensing		5% to 95% noncondensing	
	Storage relative humidity	5% to 95% noncondensing		5% to 95% noncondensing	
[*] Minimum ambient temperature for cold start is 0°C (+32°F). ^{**} FE SKUs only GE SKU have a max operation temp of 40C.					
Acoustic noise	ISO 7779 and ISO 9296: Bystander positions operating to an ambient temperature of 25°C.				
	Model	Sound pressure LpA (Typical)	Model	Sound pressure LpA (Typical)	
	Cisco Catalyst 3560-C	0dB (fanless)	Cisco Catalyst 2960-C	0dB (fanless)	
Mean time between failure (MTBF)	Cisco Catalyst 3560-C	MTBF	Cisco Catalyst 2960-C	MTBF	
	3560CG-8PC-S	355,830	2960CPD-8PT-L	346,590	
	3560CG-8TC-S	488,549	2960CPD-8TT-L	471,888	
	3560CPD-8PT-S	333,354	2960CG-8TC-L	542,482	
	3560C-8PC-S	373,635	2960C-8TC-L	516,980	
	3560C-12PC-S	357,027	2960C-8TC-S	516,980	
				2960C-8PC-L	373,635
			2960C-12PC-L	357,027	

^{*} The 2960-C LAN Lite only supports 64 VLANs.

Table 4 shows switch power specifications.

Table 4. Power Specifications for Cisco Catalyst 3560-C and 2960-C Series Compact Switch

Description	Specification			
Measured 100% throughput power consumption	Cisco Catalyst 3560-C	Switch Power Consumption Watts	Cisco Catalyst 2960-C	Switch Power Consumption Watts
	3560CPD-8PT-S	Single Uplink = 21W ¹ Dual Uplink = 22W ¹	2960CPD-8PT-L	Single Uplink = 12W ¹ Dual Uplink = 15W ¹
	3560CG-8PC-S	24W	2960CPD-8TT-L	Single Uplink = 12W ¹ Dual Uplink = 15W ¹
	3560CG-8TC-S	20W	2960CG-8TC-L	18W
	3560C-8PC-S	17W	2960C-8TC-L	11W
	3560C-12PC-S	19W	2960C-8TC-S	11W
			2960C-8PC-L	17W
		2960C-12PC-L	19W	

Description	Specification								
Measured 5% throughput power consumption	Cisco Catalyst 3560-C		Switch Power Consumption Watts		Cisco Catalyst 2960-C		Switch Power Consumption Watts		
	3560CPD-8PT-S		Single Uplink = 20W ¹ Dual Uplink = 21W ¹		2960CPD-8PT-L		Single Uplink = 12W ¹ Dual Uplink = 15W ¹		
	3560CG-8PC-S		24W		2960CPD-8TT-L		Single Uplink = 12W ¹ Dual Uplink = 15W ¹		
	3560CG-8TC-S		18W		2960CG-8TC-L		18W		
	3560C-8PC-S		17W		2960C-8TC-L		11W		
	3560C-12PC-S		19W		2960C-8TC-S		11W		
					2960C-8PC-L		17W		
					2960C-12PC-L		18W		
Measured 100% throughput power consumption (with maximum possible PoE loads)	Cisco Catalyst 3560-C		Switch Power Consumption Watts		Cisco Catalyst 2960-C		Switch Power Consumption Watts		
	3560CPD-8PC-S		40W		2960CPD-8PT-L		43W		
	3560CG-8PC-S		165W		2960C-8PC-L		157W		
	3560C-8PC-S		158W		2960C-12PC-L		158W		
	3560C-12PC-S		159W						
AC/DC input voltage and current	Cisco Catalyst 3560-C			Cisco Catalyst 2960-C					
		I/P Voltage	I/P Current		I/P voltage	I/P Current			
	3560CPD-8PT-S	37-57VDC	.01-.6A	2960CPD-8PT-L	37-57VDC	.01-.6A			
	3560CG-8PC-S	100-240 VAC	1.7-.8A	2960CPD-8TT-L	37-57VDC	.01-.3A			
	3560CG-8TC-S	100-240 VAC	.37-.2A	2960CG-8TC-L	100-240 VAC	.34-.2A			
	3560C-8PC-S	100-240 VAC	1.6-.8A	2960C-8TC-L	100-240 VAC	.21-.1A			
	3560C-12PC-S	100-240 VAC	1.6-.8A	2960C-8TC-S	100-240 VAC	.21-.1A			
				2960C-8PC-L	100-240 VAC	1.6-.8A			
				2960C-12PC-L	100-240 VAC	1.6-.8A			
	Note: For the AC values of the 3560CPD and 2960CPD SKUs see Hardware Installation Guide.								
Power rating	Cisco Catalyst 3560-C				Cisco Catalyst 2960-C				
		Watts	KVA	BTU		Watts	KVA	BTU	
	3560CPD-8PT-S	51	.05	170.6	2960CPD-8PT-L	15	0.04	136	
	3560CG-8PC-S	165	.17	580 ¹	2960CPD-8TT-L	15	0.04	136	
	3560CG-8TC-S	20	.05	170.6	2960CG-8TC-L	18	0.04	136	
	3560C-8PC-S	158	.16	546 ¹	2960C-8TC-L	11	.03	102	
	3560C-12PC-S	159	.16	546 ¹	2960C-8TC-S	11	.03	102	
					2960C-8PC-L	157	.16	546 ¹	
					2960C-12PC-L	158	.16	546 ¹	
¹ Switch dissipation only (excludes PoE which is dissipated at the end device). Power measurement are best and worst case. Best Case is 1 PoE Connection. Worst case is 2 PoE+ connections.									
PoE and PoE+	<ul style="list-style-type: none"> • Maximum power supplied per Port for PoE+ is 30W • Maximum power supplied per port for PoE: 15.4W 								

Table 5 shows switch management and standards support.

Table 5. Management and Standards Support for Cisco Catalyst 3560-C and 2960-C Series Compact Switch

Description	Specification
Management	<ul style="list-style-type: none"> • BRIDGE-MIB • CISCO-CABLE-DIAG-MIB • CISCO-CDP-MIB • CISCO-CLUSTER-MIB • CISCO-CONFIG-COPY-MIB • CISCO-CONFIG-MAN-MIB • CISCO-DHCP-SNOOPING-MIB • CISCO-ENTITY-VENDORTYPE-OID-MIB • CISCO-ENVMON-MIB • CISCO-ERR-DISABLE-MIB • CISCO-FLASH-MIB • CISCO-FTP-CLIENT-MIB • CISCO-IGMP-FILTER-MIB • CISCO-IMAGE-MIB • CISCO-IP-STAT-MIB • CISCO-LAG-MIB • CISCO-MAC-NOTIFICATION-MIB • CISCO-MEMORY-POOL-MIB • CISCO-PAGP-MIB • CISCO-PING-MIB • CISCO-POE-EXTENSIONS-MIB • CISCO-PORT-QOS-MIB • CISCO-PORT-SECURITY-MIB • CISCO-PORT-STORM-CONTROL-MIB • CISCO-PRODUCTS-MIB • CISCO-PROCESS-MIB • CISCO-RTTMON-MIB • CISCO-SMI-MIB • CISCO-STP-EXTENSIONS-MIB • CISCO-SYSLOG-MIB • CISCO-TC-MIB • CISCO-TCP-MIB • CISCO-UDLD-MIB • CISCO-VLAN-IFTABLE • RELATIONSHIP-MIB • CISCO-VLAN-MEMBERSHIP-MIB • CISCO-VTP-MIB • ENTITY-MIB • ETHERLIKE-MIB • IEEE8021-PAE-MIB • IEEE8023-LAG-MIB • IF-MIB • INET-ADDRESS-MIB • OLD-CISCO-CHASSIS-MIB • OLD-CISCO-FLASH-MIB • OLD-CISCO-INTERFACES-MIB • OLD-CISCO-IP-MIB • OLD-CISCO-SYS-MIB • OLD-CISCO-TCP-MIB • OLD-CISCO-TS-MIB • RFC1213-MIB • RMON-MIB • RMON2-MIB • SNMP-FRAMEWORK-MIB • SNMP-MPD-MIB • SNMP-NOTIFICATION-MIB • SNMP-TARGET-MIB • SNMPv2-MIB • TCP-MIB • UDP-MIB • ePM MIB
Standards	<ul style="list-style-type: none"> • IEEE 802.1D Spanning Tree Protocol • IEEE 802.1p CoS Prioritization • IEEE 802.1Q VLAN • IEEE 802.1s • IEEE 802.1w • IEEE 802.1x • IEEE 802.1AB (LLDP) • IEEE 802.3ad • IEEE 802.3af • IEEE 802.3ah (100BASE-X single/multimode fiber only) • IEEE 802.3x full duplex on 10BASE-T, 100BASE-TX, and 1000BASE-T ports • IEEE 802.3 10BASE-T specification • IEEE 802.3u 100BASE-TX specification • IEEE 802.3ab 1000BASE-T specification • IEEE 802.3z 1000BASE-X specification • 100BASE-BX (SFP) • 100BASE-FX (SFP) • 100BASE-LX (SFP) • 1000BASE-BX (SFP) • 1000BASE-SX (SFP) • 1000BASE-LX/LH (SFP) • 1000BASE-ZX (SFP) • 1000BASE-CWDM SFP 1470 nm • 1000BASE-CWDM SFP 1490 nm • 1000BASE-CWDM SFP 1510 nm • 1000BASE-CWDM SFP 1530 nm • 1000BASE-CWDM SFP 1550 nm • 1000BASE-CWDM SFP 1570 nm • 1000BASE-CWDM SFP 1590 nm • 1000BASE-CWDM SFP 1610 nm • RMON I and II standards • SNMPv1, SNMPv2c, and SNMPv3

Description	Specification
RFC compliance	<ul style="list-style-type: none"> • RFC 768: UDP • RFC 783: TFTP • RFC 791: IP • RFC 792: ICMP • RFC 793: TCP • RFC 826: ARP • RFC 854: Telnet • RFC 951: Bootstrap Protocol • RFC 1542: BOOTP Extensions • RFC 959: FTP • RFC 1058: RIP Routing • RFC 1112: IP Multicast and IGMP • RFC 1157: SNMPv1 • RFC 1166: IP Addresses • RFC 1253: OSPF Routing • RFC 1256: ICMP Router Discovery • RFC 1305: NTP • RFC 1492: TACACS+ • RFC 1493: Bridge MIB • RFC 1542: Bootstrap Protocol • RFC 1583: OSPFv2 • RFC 1643: Ethernet Interface MIB • RFC 1723: RIPv2 Routing • RFC 1757: RMON • RFC 1812: IP Routing • RFC 1901: SNMPv2C • RFC 1902-1907: SNMPv2 • RFC 1981: MTU Path Discovery IPv6 • RFC 2068: HTTP • RFC 2080: RIP for IPv6 • RFC 2131: DHCP • RFC 2138: RADIUS • RFC 2233: IF MIB • RFC 2236: IP Multicast • RFC 2328: OSPFv2 • RFC 2273-2275: SNMPv3 • RFC 2373: IPv6 Aggregatable Addr • RFC 2453: RIPv2 Routing • RFC 2460: IPv6 protocol • RFC 2461: IPv6 Neighbor Discovery • RFC 2462: IPv6 Autoconfiguration • RFC 2463: ICMP IPv6 • RFC 2474: DiffServ Precedence • RFC 2597: Assured Forwarding • RFC 2598: Expedited Forwarding • RFC 2571: SNMP Management • RFC 2740: OSPF for IPv6 • RFC 3046: DHCP Relay Agent Information Option • RFC 3101, 1587: NSSAs • RFC 3376: IGMPv3 • RFC 3580: 802.1x RADIUS
Note: RFC, MIB and Standards compliance is dependant on IOS Level	

Table 6 shows switch safety and compliance information.

Table 6. Safety and Compliance

Description	Specification
Safety standards	<ul style="list-style-type: none"> • UL 60950-1 • CAN/CSA 22.2 No. 60950-1 • EN 60950-1 • IEC 60950-1 • CE Marking • GB 4943 • IEC 60825
Electromagnetic emissions certifications	<ul style="list-style-type: none"> • FCC Part 15, CFR 47, Class A, North America • EN 55022 (CISPR22) and EN 55024 (CISPR24), CE marking, European Union • AS/NZS, Class A, CISPR22:2004 or EN55022, Australia and New Zealand • VCCI Class A, V-3/2007.04, Japan • KCC (Formerly MIC, GB17625.1-1998) Class A, KN24/KN22, Korea • ANATEL, Brazil • CCC, China • GOST, Russia
Environmental	Reduction of Hazardous Substances (ROHS) 6
Telco	Common Language Equipment Identifier (CLEI) code

Safety Compliance and Product Approval Status

For further information on safety and compliance documentation, visit the Product Approval Status tool at http://tools.cisco.com/cse/prdapp/jsp/externalsearch.do?action=externalsearch&page=EXTERNAL_SEARCH.

Cisco Enhanced Limited Lifetime Hardware Warranty

Cisco Catalyst 2960-C and 3560-C Series Switches come with an enhanced limited lifetime hardware warranty (E-LLW) that includes 90 days of Cisco Technical Assistance Center (TAC) support and next-business-day hardware replacement free of charge. (See Table 7.)

Your formal warranty statement, including the warranty applicable to Cisco software, appears in the Cisco information packet that accompanies your Cisco product. We encourage you to review carefully the warranty statement shipped with your specific product before use. Cisco reserves the right to refund the purchase price as its exclusive warranty remedy. For additional information on warranty terms, visit <http://www.cisco.com/go/warranty>.

Adding a Cisco technical services contract to your device coverage provides access to the Cisco TAC beyond the 90-day period allowed by the E-LLW. It also can provide a variety of hardware replacement options to meet critical business needs, as well as updates for licensed premium Cisco IOS Software, and registered access to the extensive Cisco.com knowledge base and support tools.

Footnotes

- ¹. Cisco operating system updates include the following: maintenance releases, minor updates, and major updates within the licensed feature set.
- ². Advance hardware replacement is available in various service-level combinations. For example, 8x5xNBD indicates that shipment will be initiated during the standard 8-hour business day, 5 days a week (the generally accepted business days within the relevant region), with next business day (NBD) delivery. Where NBD is not available, same day ship is provided. Restrictions apply; review the appropriate service descriptions for details.

Table 7. Enhanced Limited Lifetime Hardware Warranty

	Cisco Enhanced Limited Lifetime Hardware Warranty
Device covered	Applies to Cisco Catalyst 2960-C and 3560-C Series compact switches.
Warranty duration	As long as the original customer owns the product.
EoL policy	In the event of discontinuance of product manufacture, Cisco warranty support is limited to 5 years from the announcement of discontinuance.
Hardware replacement	Cisco or its service center will use commercially reasonable efforts to ship a replacement for next business day delivery, where available. Otherwise, a replacement will be shipped within 10 working days after receipt of the RMA request. Actual delivery times might vary depending on customer location.
Effective date	Hardware warranty commences from the date of shipment to customer (and in case of resale by a Cisco reseller, not more than 90 days after original shipment by Cisco).
TAC support	Cisco will provide during business hours, 8 hours per day, 5 days per week basic configuration, diagnosis, and troubleshooting of device-level problems for up to a 90-day period from the date of shipment of the originally purchased Cisco Catalyst 2960 and 3560 product. This support does not include solution or network-level support beyond the specific device under consideration.
Cisco.com access	Warranty allows guest access only to Cisco.com.

Software Policy for Cisco Catalyst 3560-C and 2960-C Series Compact Switches

Customers with Cisco Catalyst LAN Base and IP Base software feature sets will be provided with updates and bug fixes designed to maintain the compliance of the software with published specifications, release notes, and industry standards compliance as long as the original end user continues to own or use the product or up to one year from the end-of-sale date for this product, whichever occurs earlier. This policy supersedes any previous warranty or software statement and is subject to change without notice.

Cisco and Partner Services for Next-Generation Cisco Catalyst Compact Switches

Enable the innovative, secure, intelligent edge in the Borderless Network Architecture using personalized services from Cisco and our partners. Through a discovery process that begins with understanding your business objectives, we help you integrate the next-generation Cisco Catalyst fixed switches into your architecture and incorporate network services onto that platform. Sharing knowledge and leading practices, we support your success every step of the way as you deploy, absorb, manage, and scale new technology. Choose from a flexible suite of support services designed to meet your business needs and help you maintain high-quality network performance while controlling operational costs. (See Table 8.)

Table 8. Technical Services Available for Cisco Catalyst 3560-C and 2960-C Series Compact Switches

Technical Services
<p>Cisco SMARTnet[®] Service</p> <ul style="list-style-type: none">• Around-the-clock, global access to the Cisco Technical Assistance Center (TAC)• Unrestricted access to the extensive Cisco.com knowledge base and tools• Next-business-day, 8x5x4, 24x7x4, and 24x7x2 advance hardware replacement and onsite parts replacement and installation available• Ongoing operating system software updates within the licensed feature set• Proactive diagnostics and real-time alerts on Smart Call Home enabled devices
<p>Cisco Smart Foundation Service</p> <ul style="list-style-type: none">• Next business day advance hardware replacement as available• Business hours access to SMB TAC (access levels vary by region)• Access to Cisco.com SMB knowledge base• Online technical resources through Smart Foundation Portal• Operating system software bug fixes and patches
<p>Cisco Focused Technical Support Services</p> <ul style="list-style-type: none">• 3 levels of premium, high-touch services are available:• Cisco High-Touch Operations Management Service• Cisco High-Touch Technical Support Service• Cisco High-Touch Engineering Service• Valid Cisco SMARTnet or SP Base contracts on all network equipment are required

Ordering Information

Tables 9 and 10 give ordering information for the Cisco Catalyst 3560-C and 2960-C Series compact switches and accessories.

To place an order, visit the Cisco Ordering homepage at

http://www.cisco.com/en/US/ordering/or13/or8/order_customer_help_how_to_order_listing.html.

Table 9. Ordering Information for Cisco Catalyst 3560-C and 2960-C Series Compact Switches

Cisco Catalyst 3560-C Compact Switches	
WS-C3560CG-8TC-S	3560C Switch 8 GE, 2 x Dual Purpose Uplink, IP Base
WS-C3560CG-8PC-S	3560C Switch 8 GE PoE+, 2 x Dual Purpose, IP Base
WS-C3560CPD-8PT-S	3560C PD PSE Switch 8 GE PoE, 2 x 1G Copper Uplink, IP Base
WS-C3560C-8PC-S	3560C Switch 8 FE PoE+, 2 x Dual Purpose Uplink, IP Base
WS-C3560C-12PC-S	3560C Switch 12 FE PoE+, 2 x Dual Purpose Uplink, IP Base
Cisco Catalyst 2960-C Compact Switches	
WS-C2960CPD-8TT-L	2960C PD Switch 8 FE, 2 x 1G, PoE+ LAN Base
WS-C2960CPD-8PT-L	2960C PD PSE Switch 8 FE PoE, 2 x 1G, PoE+ LAN Base
WS-C2960CG-8TC-L	2960C Switch 8 GE, 2 x Dual Purpose Uplink, LAN Base
WS-C2960C-8TC-L	2960C Switch 8 FE, 2 x Dual Purpose Uplink, LAN Base
WS-C2960C-8TC-S	2960C Switch 8 FE, 2 x Dual Purpose Uplink, LAN Lite
WS-C2960C-8PC-L	2960C PoE Switch 8 FE PoE, 2 x Dual Purpose Uplink, LAN Base
WS-C2960C-12PC-L	2960C PoE Switch 12 FE PoE, 2 x Dual Purpose Uplink, LAN Base

Table 10. Ordering Information for Cisco Catalyst 3560-C and 2960-C Series Compact Switch Accessories

Part Number	Description
CMP-CBLE-GRD=	Cable guard for the 3560-C and 2960-C compact switches
CMP-MGNT-TRAY =	Magnet and Mounting Tray for 3560-C and 2960-C compact switches
PWR-ADPT=	Power Adapter for the 3560-C and 2960-C compact switches
PWR-CLP	Power Clip for the 3560-C and 2960-C compact switches
CMP-DIN-MNT=	DIN Rail Mount for 3560-C and 2960-C compact switches
RCKMNT-19-CMPCT=	19-Inch Rack Mounting Brackets
RCKMNT-23-CMPCT=	23- and 24-Inch Rack Mounting Brackets

For more information about Cisco products, contact:

- United States and Canada: (toll free) 800 553-NETS (6387)
- Europe: 32 2 778 4242
- Australia: 612 9935 4107
- Other: 408 526-7209
- Internet: <http://www.cisco.com>